

Corning® Generic Bar Coded Microplates

Generic Bar Coded Polystyrene Microplates

Corning now offers a line of generic bar coded plates to better meet the demands of your screening needs (see list of available plates on back).

- ▶ No lead time: Plates are in stock and ready to ship
- ▶ Surface identification: The surface treatment of the microplate is identified in the human readable portion of the bar code:

NT = Not treated

TC = Tissue culture treated

NB = Corning Nonbinding Surface (NBS™)

CB = Corning CellBIND® Surface

- ▶ Labels applied to all 4 sides of the microplate to ensure usability regardless of scanner location
- ▶ Each microplate is specially treated to reduce the impact of static build-up
- ▶ Code 128 bar code format ensures compatibility with most bar code scanning and software systems
- ▶ No sequence number duplicates
- ▶ Repeatable ANSI grading of B or better
- ▶ Exceptional print quality and resolution



CORNING

Corning® Generic Bar Coded Microplates – Dependable and Durable

Corning bar code labels have been quality tested for optimal readability, chemical resistance and temperature variation. Bar code sequence reports verifying sequences in your order are available upon request.

Expert Advice

Many Corning microplates are suitable for bar code customization. Contact Corning Life Sciences or your local representative for more information or recommendations.

Generic Bar Coded Microplates Currently Available:

Cat. No.	Description	Qty/Cs
96 Well Microplates		
3628BC	Clear, flat bottom, tissue culture treated, with lid	100
 3897BC	Black, V-bottom, polystyrene, no lid	100
 3904BC	Black, clear flat bottom, tissue culture treated, with lid, sterile	100
384 Well Microplates		
3574BC	White, solid, NBS, [™] no lid	50
3575BC	Black, solid, NBS, no lid	50
3640BC	Clear, NBS, no lid	100
3683BC	Black, clear bottom, Corning CellBIND® Surface, with lid	50
3702BC	Clear, not treated, no lid	100
3821BC	Black, solid, low volume, not treated, no lid	50
3824BC	White, solid, Low volume, NBS, no lid	50
3826BC	White, solid, Low volume, tissue culture treated, with lid	50
 3712BC	Black, clear bottom, tissue culture treated, with lid, sterile	100
1536 Well Microplates		
3724BC	Black, solid, not treated, no lid	50
3725BC	White, solid, not treated, no lid	50
3727BC	White, solid, tissue culture treated, with lid	50
3728BC	Black, solid, NBS, no lid	50
3729BC	White, solid, NBS, no lid	50
3832BC	Black, clear bottom, low base, Corning CellBIND Surface, with lid	50
3838BC	Black, clear bottom, low base, tissue culture treated, with lid	50
3891BC	Black, clear bottom, not treated, no lid	50
3893BC	Black, clear bottom, tissue culture treated, with lid	50
3895BC	Black, clear bottom, NBS, no lid	50
 3839BC	Black, clear bottom, low base, Poly-D-Lysine, with lid	50

CHEMICAL RESISTANCE

100% DMSO
Methanol
Ethanol
Ethyl Acetate
Methylene Chloride
Isopropanol
Acetonitrile
Ethanol/Water/TFA
Sodium Hydroxide
Hydrochloric Acid

TEMPERATURE RESISTANCE

-80°C to +52°C
37°C Humid
37°C Dry
100°C Dry

BAR CODE/LABEL SPECIFICATIONS

2.75" x 0.25" label size
Linear (1-D) bar codes
Code 128
Code 3 of 9
ITF 2 of 5
10 mL narrow bar element
(x-dimension = 0.010")



www.corning.com/lifesciences/solutions

Corning Incorporated Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

Worldwide Support Offices

ASIA/PACIFIC

Australia/New Zealand
t 0402-794-347

China
t 86 21 2215 2888
f 86 21 6215 2988

India
t 91 124 4604000
f 91 124 4604099

Japan

t 81 3-3586 1996
f 81 3-3586 1291

Korea

t 82 2-796-9500
f 82 2-796-9300

Singapore

t 65 6733-6511
f 65 6861-2913

Taiwan

t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France

t 0800 916 882
f 0800 918 636

Germany

t 0800 101 1153
f 0800 101 2427

The Netherlands

t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom

t 0800 376 8660
f 0800 279 1117

All Other European Countries

t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA

Brasil

t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico

t (52-81) 8158-8400
f (52-81) 8313-8589

The Corning Family of Brands

CORNING costar cellgro PYREX AXYGEM GOSSELIN™

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks.
Corning Incorporated, One Riverfront Plaza, Corning, NY 14831-0001