

Description	Oxygen Part Name	Well Volume (uL)	Well Depth (mm)	Well Diameter (top)(mm)	Well Diameter (bottom) (mm)	Plate Length (mm)	Plate Width (mm)	Plate Height (mm)	A1 Column Offset (mm)	A1 Row Offset (mm)	Well center to well center (mm) X	Flange or skirt height (mm)	Well Bottom Elevation (mm)	Stack Height	Well Bottom Thickness (mm)	Well Bottom Area (cm <sup>2</sup> )
<b>96 Well PCR Microplates Compatible to Applied Biosystems</b>																
<b>Solid black, white, and clear polystyrene plates</b>																
96 Well PCR Microplate, Flat bottom, no skirt Applied Biosystems 7000,7300,7500,7700,Veriti,9600,9700, 2720	PCR-96-FLT	200	19.771	5.3340	2.4130	119.5832	79.62392	20.467	10.401	8.191	9.001298182	N/A	N/A	N/A	0.7162	0.3607
96 Well PCR Microplate, No skirt, elevated walls Applied Biosystems Veriti,9600,9700, 2720	PCR-96	200	20.510	5.3340	2.2860	118.5774	77.84084	21.143	9.956	7.696	8.99	N/A	N/A	N/A	0.6172	0.3226
96 Well PCR Microplate, Segmented Applied Biosystems Veriti,9600,9700, 2720	PCR-96-SG	200	20.231	5.3340	2.4892	114.9858	78.96606	20.891	7.962	7.759	8.987	7.366	N/A	N/A	0.6172	0.3835
96 Well PCR Microplate, Half Skirt Applied Biosystems 7000,7300,7500,7700,7900 Veriti,9600,9700, 2720	PCR-96-M2-4HS	200	20.231	5.5880	2.2606	125.7986	85.45576	21.005	12.992	10.845	8.994	7.62	N/A	N/A	0.6172	0.3150
96 Well PCR Microplate, elevated skirt Applied Biosystems 7000,7300,7500,7700,7900 Veriti,9600,9700, 2720	PCR-96-AB	100	19.781	5.3340	2.2606	125.7960	85.48116	22.862	13.589	11.595	8.988	10.464	N/A	N/A	0.6019	0.3150
96 Well PCR Microplate, low profile, half skirt Applied Biosystems 7500,7900,Step One, Veriti, 9800 FAST	PCR-96-LP-AB	100	15.044	5.3340	2.2606	127.6782	85.32114	16.87	14.516	11.176	8.981	7.416	N/A	N/A	0.639	0.3150
<b>384 Well PCR Microplates Compatible to Applied Biosystems</b>																
384 Well PCR Microplate,skirted,double notch Applied Biosystems Veriti,9700, 2720	PCR-384	50	8.729	3.175	1.397	127.53086	85.56244	9.245	11.734	8.686	4.502	8.636	N/A	N/A	0.5207	0.11938
384 Well PCR Microplate,skirted ,single notch Applied Biosystems 7900HT,Veriti,9700, 2720	PCR-384M2	55	8.669	3.2004	1.0922	127.6096	85.33638	9.702	11.734	9.169	4.506	9.042	N/A	N/A	0.5181	0.07366
384 Well PCR Microplate,skirted, elevated walls, single notch Applied Biosystems Veriti,9700, 2720	PCR-384-55	55	10.563	3.2004	1.1938	127.56388	85.27288	11.049	11.938	9.296	4.507	9.144	N/A	N/A	0.5156	0.0889
384 Well PCR Microplate,skirted, rigid, single notch Applied Biosystems Veriti,9700, 2720	PCR-384-RGD	50	8.595	2.9718	1.2192	127.60198	85.1535	9.575	12.065	8.890	4.506	9.194	N/A	N/A	0.7442	0.09144