

# PYREX® Wide Mouth Storage Bottles

These new PYREX wide mouth storage bottles are designed as heavy duty storage bottles as well as mixing and sampling. The extra wide mouth (69 mm inner diameter) gives easier access for pouring and removing pastes, powders and larger items. They include a linerless, one-piece autoclavable orange polypropylene plug seal GLS80 threaded cap with a drip-free pouring ring.

## Bottle Features

- ▶ Available in three sizes: 500mL, 1L and 2L
- ▶ Neck opening is 5 times larger than on GL45 threaded bottles – much easier to add or remove powders and easier to clean
- ▶ Easily holds wide mouth funnels
- ▶ High thermal shock resistance; useable up to 500°C and in microwave ovens
- ▶ PYREX bottles can be sterilized by autoclaving or dry heat; polypropylene caps can be autoclaved
- ▶ Permanent white enamel graduations and marking spot
- ▶ Traceability Code for easier documentation

## Cap Features

- ▶ Easy on-off quick release cap
- ▶ One piece cap seal using an integral plug designed to mold against the inside rim on the bottle
- ▶ Audible click when cap is sealed on bottle



CORNING

## PYREX® Wide Mouth Storage Bottles Technical Information

Visit the Technical Information section of our website at <http://www.corning.com/lifesciences> for these and other technical resources:

- ▶ Description of Glasses Used in Corning Labware
- ▶ Safety Features and Benefits of Corning Glassware
- ▶ Suggestions for Cleaning Thermal Properties
- ▶ Properties of Plastic Components Used in Corning Glassware



## PYREX Wide Mouth Storage Bottles Ordering Information

Cat No.	Capacity (mL)	Thread Size	Diameter x Height	Grad. Range (mL)	Grad. Interval (mL)	Qty/ Cs
			(mm) Approx.			
1397-500	500	GLS80	101 x 148	100-500	100	10
1397-1L	1000	GLS80	101 x 218	100-1000	100	10
1397-2L	2000	GLS80	136 x 248	400-2000	200	10

### Optional Cap

Cat No.	Description	Thread Size	Qty/ Cs
1397-80LTC*	Orange Cap	GLS80	20

\*Available July 2007.

For additional Corning product, technical, or distributor information, please e-mail us at [CLStechserv@corning.com](mailto:CLStechserv@corning.com), visit our website [www.corning.com/lifesciences](http://www.corning.com/lifesciences) or call 1.800.492.1110. Outside the United States, call 978.442.2200.

# CORNING

## Corning Incorporated Life Sciences

Tower 2, 4th Floor  
900 Chelmsford St.  
Lowell, MA 01851  
t 800.492.1110  
t 978.442.2200  
f 978.442.2476

[www.corning.com/lifesciences](http://www.corning.com/lifesciences)

## Worldwide Support Offices

### ASIA / PACIFIC

**Australia**  
t 61 2-9416-0492  
f 61 2-9416-0493

**China**  
t 86 21-3222-4666  
f 86 21-6288-1575

**Hong Kong**  
t 852-2807-2723  
f 852-2807-2152

**India**  
t 91-124-235 7850  
f 91-124-401 0207

**Japan**  
t 81 (0) 3-3586 1996/1997  
f 81 (0) 3-3586 1291/1292

**Korea**  
t 82 2-796-9500  
f 82 2-796-9300

**Singapore**  
t 65 6733-6511  
f 65 6861-2913

**Taiwan**  
t 886 2-2716-0338  
f 886 2-2716-0339

### EUROPE

**France**  
t 0800 916 882  
f 0800 918 636

**Germany**  
t 0800 101 1153  
f 0800 101 2427

**The Netherlands**  
t 31 20 655 79 28  
f 31 20 659 76 73

**United Kingdom**  
t 0800 376 8660  
f 0800 279 1117

**All Other European Countries**  
t 31 (0) 20 659 60 51  
f 31 (0) 20 659 76 73

### LATIN AMERICA

**Brasil**  
t (55-11) 3089-7419  
f (55-11) 3167-0700

**Mexico**  
t (52-81) 8158-8400  
f (52-81) 8313-8589