

Rotor Compatibility Chart for Corning® 15 mL and 50 mL Centrifuge Tubes

CORNING

Eppendorf

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
22654306	FA	7197	22654365	22654349	22654349
22639048	SW	3000/2900	022639200/022639188	N/A	N/A
22639501	SW	2800	Dedicated	N/A	N/A
22639404	FA	2750	Dedicated	N/A	N/A
22637401	SW	4200/4300/4400/4500	022637606/022637614	022637452/022637665/022637673	22637681
22638009	SW	3150/3050	22638289	022638351/022638343	22638386
22638602	SW	3100/3100/3250	22638742	022638769/022638614	22638904

Labnet

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
C0200-96	FA	4180	Dedicated	N/A	N/A
C0200-97	FA	3820	C0232-8B	Dedicated	Dedicated
C0323-81	FA	1972	Dedicated	N/A	N/A
C0300-96	FA	4185	Dedicated	N/A	N/A
C0300-97	FA	3904	C0232-8B	Dedicated	Dedicated
C0323-72	SW	2540	C0320-726	C0320-728	N/A
C0300-12	SW	3350	C0300-123	C0300-122	N/A
C0300-50	SW	2540	C0232-8B	Dedicated	Dedicated
C0300-15	SW	4165	Dedicated	N/A	N/A
C0382-91	FA	19561	N/A	Dedicated	Dedicated
C0382-91H	FA	19561	N/A	Dedicated	Dedicated
C0382-78	FA	20987	N/A	C0360-94D	N/A
C0382-78H	FA	20987	N/A	C0360-94D	N/A
C0036-19	FA	2829	Dedicated	N/A	N/A
C0326-96	FA	4185	Dedicated	N/A	N/A
C0326-97	FA	3823	C0232-8B	Dedicated	Dedicated
C0326-78	FA	13933	C0360-94X	C0360-94D	N/A
C0326-78H	FA	13933	C0360-94X	C0360-94D	N/A
C0036-18	FA	10414	C0360-94X	C0360-94D	N/A
C0036-20	FA	14811	C0360-94X	C0360-94D	N/A
C0326-72	SW	3885	C0320-726	C0320-728	N/A
C0326-72C	SW	3885	C0320-726	C0320-728	N/A
C0326-12	SW	3350	C0300-123	C0300-122	N/A
C0400-50	SW	3574	C0232-8B	Dedicated	Dedicated
C0400-15	SW	3199	Dedicated	N/A	N/A
C0036-21	FA	10017	C0036-21A	C0036-21C	N/A
C0036-75	SW	3780	C0036-75A	C0036-75C	N/A
220.96 V01	FA	6000	Dedicated	N/A	N/A
220.97 V01	FA	6000	603.001	Dedicated	Dedicated

Dedicated: No insert required for centrifuge.

N/A: Not compatible with the rotor and no adaptor/insert available to make it compatible.

FA: Fixed Angle; SW: Swinging Bucket.

Rotor Compatibility Chart for Corning® 15 mL and 50 mL Centrifuge Tubes

SIGMA Laborzentrifugen GmbH

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
11035	SW	2379	Dedicated	N/A	N/A
11031	SW	2379	Dedicated	N/A	N/A
12011	FA	1735	Dedicated	N/A	N/A
12012	FA	1735	Dedicated	N/A	N/A
12061	FA	2486	Dedicated	N/A	N/A
12062	FA	2486	Dedicated	N/A	N/A
12151	FA	8603	13060	13079	N/A
13150	SW	2558	13060	N/A	N/A
11192	SW	2558	13012	13150	N/A
12072	FA	2486	Dedicated	N/A	N/A
12073	FA	2486	Dedicated	N/A	N/A
11191	SW	3913	Dedicated	N/A	N/A
12071	FA	2254	Dedicated	Dedicated	N/A
19776	FA	20379	13060	13079	N/A
19776 H	FA	9380	N/A	Dedicated	N/A
19777 H	FA	9380	Dedicated	N/A	N/A
19776	FA	20379	N/A	13079	N/A
13104	SW	5410	17015/17019	17048/17049	N/A
13180	SW	4223	18015/18016/18018	18050/18052/18053	N/A
13190	SW	3894	17345/17359	17344/17346/17377	N/A
13194	SW	3894	18311	18309/18310	N/A
11392	SW	3750	Dedicated	N/A	N/A
12258	FA	20954	14152	14131	N/A
12505	FA	20461	14149	14150/14148	N/A
12510	FA	11285	14165	14169/14171	N/A
13450	SW	4495	17659/17660	17675/17677/17678/17649	N/A
13097	SW	3773	N/A	17950	N/A
13099	SW	2379	N/A	17950	N/A
11132	SW	5242	Dedicated	N/A	N/A
12150	FA	9391	N/A	Dedicated	N/A
12156	FA	8694	N/A	Dedicated	N/A
12166	FA	16770	N/A	Dedicated	N/A
11036	SW	2379	13035	N/A	N/A
11030	SW	2379	13038/13035	N/A	N/A
11150	SW	4120	13236	13235	N/A
13041	SW	3260	14034	14032	N/A

Beckman Coulter

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
364610	FA	41400	N/A	Dedicated	Dedicated
364640	FA	28611	N/A	Dedicated	Dedicated
364650	FA	26320	N/A	Dedicated	Dedicated
369735	FA	11400	N/A	Dedicated	Dedicated
368303	FA	21100	N/A	Dedicated	Dedicated
368293	FA	15300	N/A	Dedicated	Dedicated
364680	FA	10400	Dedicated	N/A	N/A
392243	SW	3901	392257	N/A	N/A
369702	SW	5250	N/A	Dedicated	Dedicated
369704	SW	5250	N/A	Dedicated	Dedicated

Dedicated: No insert required for centrifuge.

N/A: Not compatible with the rotor and no adaptor/insert available to make it compatible.

FA: Fixed Angle; SW: Swinging Bucket.

Thermo Fisher Scientific

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
75003667 with 75003668	SW	2739	75003673	75003674	75003692 only with 75006533 adapter
75003607 with 75003608	SW	4816	75003639	75003638	75006533
75003607 with 75003614	SW	4816	75003684	75003685	75006461
75003603	SW	7164	75003642	75003643	75006461
75003629	SW	4696	75003682	75003683	N/A
75003658	SW	5580	75003771	75003803	75003803 (without cushion)
75003621	SW	7188	75003678	75003677	N/A
75003623	FA	15090	Dedicated	N/A	N/A
75003662	FA	18533	75101073	75100136	N/A
75003698	FA	24652	75003095	75003103	N/A
75003661	FA	17105	010-0378	Dedicated	N/A
75003663	FA	24446	010-0378	N/A	N/A
75003694	FA	7177	N/A	Dedicated	N/A
75003620/75003057/ 75005600/75007588	FA	15090	75003095	75003103	N/A
75003000	SW	7068	75007306	75003674	75003824 with 75007304
75003000	SW	7068	N/A	Double biocontainment with 75004254 and 75003787	N/A
75003002	SW	10,025	75005394	75005393	75005393 (without cushion)
75003002	SW	10,025	N/A	Double biocontainment with 75004256 and 75003787	N/A
75003010	SW	30,314	50134721 with 010-0378	50134721	N/A
096-061075	FA	17,568	010-1079	010-0180	N/A
096-041075/096-041053	FA	20,584	010-1079	010-0180	N/A
096-062375/096-062185	FA	24,471	010-1099	010-1102	N/A
096-062075/78500	FA	30,240	010-1073	010-0136	N/A
096-145075	FA	33,746	010-0378	Dedicated	N/A
75003004	FA	62532	Dedicated	N/A	N/A
096-124375	FA	51428	010-1123	N/A	N/A
096-084275/46923	FA	47850	010-1123	N/A	N/A
096-064025	FA	43,900	N/A	N/A	N/A
096-124022	FA	38,700	010-1123	N/A	N/A
46922	FA	29,000	010-0378	Dedicated	N/A
75003006	FA	62,976	75003095	75003103	N/A
77050/77080	SW	7340	75007056 with 75007065	75007055 with 75007065	N/A
11250	SW	7277	447	00436/00445	00436/00445 (without cushions)
75006606 with 75008165	SW	4248	75008137	11210826	N/A
75006606 with 76008078	SW	4984	75005387	75002261/75005386	N/A
75006476 with 75006477	SW	5480	75008137	11210826	75006533
75006476 with 75006478	SW	4650	75006456 or 75006468	75006461/75006491	N/A
75006475 with 75006477	SW	5480	75008137	11210826	75006533
75006475 with 75006478	SW	4650	75006456/75006468	75006461/75006491	N/A

Dedicated: No insert required for centrifuge.

N/A: Not compatible with the rotor and no adaptor/insert available to make it compatible.

FA: Fixed Angle; SW: Swinging Bucket.

Rotor Compatibility Chart for Corning® 15 mL and 50 mL Centrifuge Tubes

Thermo Fisher Scientific (Continued)

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
75006435	SW	6963	75006456	75006461	N/A
11178252 with 11178135	SW	5735	11178304	11178308	N/A
11178252 with 11178216	SW	5392	11175348	11175354	N/A
11178254	SW	5623	11178304	11178308	N/A
78560	FA	7900	010-1079	010-0180	N/A
75006483	FA	15,344	010-1073	010-0136	N/A
523670F	SW	1950	02092SF	02091SF	N/A
522120F	SW	1890	Dedicated	N/A	N/A
580120F	FA	2050	N/A	Dedicated	N/A
580920F	FA	2150	Dedicated	N/A	N/A
00804SF	FA	2270	N/A	Dedicated	N/A
521510F	SW	1750	003230F/011060F/005710F	003200F	N/A
11210014	SB	2647	11210676	11210675	N/A
11210018	FA	3661	11210532	11210577	N/A
11210019	FA	2380	Dedicated	N/A	N/A
75007591	SW	2590	75007557	75007556	N/A

Hettich

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
EBA 20	FA	3461	Dedicated	N/A	N/A
EBA 20S	FA	6153	Dedicated	N/A	N/A
1116	FA	4025	1631	1641	N/A
1416	FA	4146	Dedicated	N/A	N/A
1016	FA	4025	1631	1641	N/A
1015	FA	4146	Dedicated	N/A	N/A
1624	SW	2665	1347	1384	6318
1324	SW	2630	1347/1356/1483A	1384/1484	6318/1484
1619	SW	2,701	1462-A	Dedicated	N/A
1418	FA	2594	1467	1468	1468
1613	FA	4146	Dedicated	N/A	N/A
1620A	FA	4226	1466	1646	N/A
1494	SW	4193	1442/5275/1347	1443/5276/1384	1737/5233/6318
1617	SW	3857	1462-A	Dedicated	N/A
1615	FA	16,582	1647	N/A	N/A
1754	SW	4863	1771-A	1772-A	1774-A
1798	SW	3095	6306/5129	5259/5123	5243/5135
1717	SW	2916	1462-A	Dedicated	N/A
1720	FA	16,369	1466	1454	N/A
1792	FA	16,504	1466	1454	N/A
1721	FA	3283	1467	1468	1468
4723	SW	4166	4769	4770	4770
4753	SW	3095	1	5259/5123	5243/5135
4754	SW	3832	1347/1356	1384	6318
4794	FA	16,504	1466	1454	N/A
5624	SW	5063	4739/4839/4469	4740/5647/4468	4468/4840/4740
5654	SW	3196	5683	5686	N/A

Dedicated: No insert required for centrifuge.

N/A: Not compatible with the rotor and no adaptor/insert available to make it compatible.

FA: Fixed Angle; SW: Swinging Bucket.

Hettich (Continued)

Rotor Cat. No.	Rotor Type	Rotor Speed (MAX RCF)	15 mL Conical Tube Insert	50 mL Conical Tube Insert	Self Standing 50 mL Conical Tube Insert
5694	SW	3095	1	5259/5123	5243/5135
4446	SW	3631	1	5259/5123	5243/5135
5615	FA	18038	1466	1454	N/A
4294	SW	5252	4232/4437	4245-A/4441	4249
4296	SW	3631	6306/5129	5259/5123	5243/5135
4176	SW	6520	4437/4232/4437	4441/4245-A/4441	4249
4174	SW	5705	4437/4232/4437	4441/4245-A/4441	4249

Dedicated: No insert required for centrifuge.

N/A: Not compatible with the rotor and no adaptor/insert available to make it compatible.

FA: Fixed Angle; SW: Swinging Bucket.

For additional product or technical information, please call 800.492.1110 or visit www.corning.com/lifesciences. Customers outside the United States, call +1.978.442.2200 or contact your local Corning sales office listed below.

Corning Incorporated Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

Worldwide Support Offices

ASIA/PACIFIC

Australia/New Zealand
t 0402-794-347

China
t 86 21 2215 2888
f 86 21 6215 2988

India
t 91 124 4604000
f 91 124 4604099

Japan

t 81 3-3586 1996
f 81 3-3586 1291

Korea

t 82 2-796-9500
f 82 2-796-9300

Singapore

t 65 6733-6511
f 65 6861-2913

Taiwan

t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France

t 0800 916 882
f 0800 918 636

Germany

t 0800 101 1153
f 0800 101 2427

The Netherlands

t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom

t 0800 376 8660
f 0800 279 1117

All Other European Countries

t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA

Brasil

t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico

t (52-81) 8158-8400
f (52-81) 8313-8589

The Corning Family of Brands

CORNING **costar** cellgro® PYREX® **ALXYGEN** GOSSELIN™

For additional product or technical information, please call 800.492.1110 or visit www.corning.com/lifesciences. Customers outside the United States, call +1.978.442.2200 or contact your local Corning sales office listed below.

Corning Incorporated
Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

**Worldwide
Support Offices**

ASIA/PACIFIC

Australia/New Zealand
t 0402-794-347

China
t 86 21 2215 2888
f 86 21 6215 2988

India
t 91 124 4604000
f 91 124 4604099

Japan

t 81 3-3586 1996
f 81 3-3586 1291

Korea

t 82 2-796-9500
f 82 2-796-9300

Singapore

t 65 6733-6511
f 65 6861-2913

Taiwan

t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France

t 0800 916 882
f 0800 918 636

Germany

t 0800 101 1153
f 0800 101 2427

The Netherlands

t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom

t 0800 376 8660
f 0800 279 1117

**All Other European
Countries**

t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA

Brasil
t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico
t (52-81) 8158-8400
f (52-81) 8313-8589

The Corning Family of Brands

CORNING **costar** **cellgro** **PYREX** **ALXYGEN** **GOSSELIN**