

Corning® Transport Medium

CORNING

Corning Transport Medium is an isotonic solution at neutral pH containing protective proteins, an antibiotic to prevent microbial growth, and an anti-mycotic to prevent contamination by yeast and fungi.

It has been formulated using the final ingredient concentrations outlined in CDC's SOP#: DSR-052-01: Preparation of Viral Transport Medium.

- ▶ Sizes: 100 mL, 500 mL, and 1L
- ▶ Shipping and storage: 2°C to 8°C
- ▶ Shelf life: 12 months
- ▶ Sterility Assurance Level (SAL) of 10⁻³ by aseptic sterile filtration

Manufactured under a quality system that conforms with the current ISO 13485 standard and Quality System Regulation (QSR) per 21 CFR 820, also known as current Good Manufacturing Practices (cGMP).

Ordering Information

Cat. No.	Description	Qty/Cs
25-500-CI	Corning Transport medium, 100 mL	6
25-500-CV	Corning Transport medium, 500 mL	6
25-500-CM	Corning Transport medium, 1L	6



For more specific information on claims, visit the Certificates page at www.corning.com/lifesciences.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

Corning's products are not specifically designed and tested for COVID-19 testing. Many Corning products, though not specific to the COVID-19 test, can be used in the workflow and preparation of the test at the customer's discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for COVID-19 test either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of your intended application.

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110. Outside the United States, call +1.978.442.2200 or contact your local Corning sales office.

CORNING

Corning Incorporated
Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

ASIA/PACIFIC
Australia/New Zealand
t 61 427286832

Chinese Mainland
t 86 21 3338 4338
f 86 21 3338 4300

India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291

Korea
t 82 2-796-9500
f 82 2-796-9300

Singapore
t 65 6572-9740
f 65 6735-2913

Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE
CSEurope@corning.com

France
t 0800 916 882
f 0800 918 636

Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 020 655 79 28
f 020 659 76 73

United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European
Countries
t +31 (0) 206 59 60 51
f +31 (0) 206 59 76 73

LATIN AMERICA
grupoLA@corning.com

Brazil
t 55 (11) 3089-7400
Mexico
t (52-81) 8158-8400