

PYREX® Reusable Media Bottles

PYREX®

A Corning Brand

PYREX reusable laboratory bottles are designed as storage vessels for reagents, sterile tissue culture media and components, biological fluids, aqueous and nonaqueous solutions. Choose Low Actinic bottles for light sensitive materials or PYREXPLUS bottles for the added protection of a PVC coating.

Materials

PYREX bottles are made from 7740 glass type, a chemically resistant, low expansion, borosilicate glass. The bottles are supplied with clear Polypropylene pouring rings, and orange caps and are fully autoclavable. A wide range of optional closures are available for the Corning® bottles including:

- ▶ Plug seal, GL45 color-coded caps to aid in sorting and identification
- ▶ High temperature, PBT caps (Polybutylene-teraphthalate GL45 high temperature caps) with PTFE (Polytetrafluoroethylene) coated liners (Cat. No. 1395-45HTC), ETFE (Ethylenetetrafluoroethylene) copolymer rings (Cat. No. 1395-45HTR), and Silicone septa (Cat. No. 1395-45SS) are suitable for dry heat sterilization (180°C).
- ▶ Vented, GL45 caps with 0.22 µm PTFE hydrophobic membranes (Cat. No. 1395-45LTMC)
- ▶ Open Top, PBT caps in GL25, GL32, and GL45 sizes
- ▶ Silicone or PTFE-faced Silicone Septa for the open-top caps.



PYREX reusable laboratory bottles are designed as storage vessels for reagents, sterile tissue culture media and components, biological fluids, and aqueous and non-aqueous solutions.

Ordering Information

1395 PYREX Laboratory Storage Bottle

Cat. No.	Capacity (mL)	Approx. Diameter x Height (mm)	Grad. Range (mL)	Grad. Interval (mL)	Qty/ Cs
1395-25	25	36.5 x 70	10-25	5	10
1395-50	50	46 x 88	20-50	10	10
1395-100	100	56 x 100	40-80	20	10
New 1395-150	150	50 x 125	62-110	25	10
1395-250	250	70 x 138	50-200	50	10
1395-500	500	86 x 176	100-400	100	10
New 1395-750	750	95 x 203	100-600	100	10
1395-1L	1000	101 x 225	100-900	100	10
1395-2L	2000	136 x 262	400-1800	200	10
New 1395-3X	3000	160 x 295	500-3000	500	10
1395-5L	5000	186 x 335	500-4500	500	1
1395-10L	10000	234 x 410	2000-9000	1000	1



Ordering Information (Continued)



1396 PYREX® Square Laboratory Storage Bottle

Cat. No.	Capacity (mL)	Thread Size	Approx. Diameter x Height (mm)	Grad. Range (mL)	Grad. Interval (mL)	Qty/Cs
1396-100	100	GL32	50 x 105	40-80	20	10
1396-250	250	GL45	64 x 138	50-200	50	10
1396-500	500	GL45	78 x 176	100-400	100	10
1396-1L	1000	GL45	94 x 217	100-900	100	10



1397 PYREX GLS 80 Wide Mouth Bottle

Cat. No.	Capacity (mL)	Thread Size	Approx. Diameter x Height (mm)	Grad. Range (mL)	Grad. Interval (mL)	Qty/Cs
1397-500	500	GLS80	101 x 148	100-500	100	10
1397-1L	1000	GLS80	101 x 218	100-1000	100	10
1397-2L	2000	GLS80	136 x 248	400-2000	200	10



51395 PYREX Low Actinic Bottle

Cat. No.	Capacity (mL)	Thread Size	Approx. Diameter x Height (mm)	Grad. Range (mL)	Grad. Interval (mL)	Qty/Cs
51395-25	25	GL25	36.5 x 70	10-25	5	4
51395-50	50	GL32	46 x 88	20-50	10	4
51395-100	100	GL45	56 x 100	40-80	20	4
51395-250	250	GL45	70 x 138	50-200	50	4
51395-500	500	GL45	86 x 176	100-400	100	4
51395-1L	1000	GL45	101 x 225	100-900	100	4
51395-2L	2000	GL45	136 x 262	400-1800	200	4
51395-5L	5000	GL45	186 x 335	500-4500	500	1
51395-10L	10,000	GL45	234 x 410	2000-9000	1000	1

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures.

For additional product or technical information, please call 800.492.1110 or visit www.corning.com/lifesciences. Customers outside the United States, call +1.978.442.2200 or contact your local Corning sales office listed below.

Corning Incorporated Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

Worldwide Support Offices

ASIA/PACIFIC
Australia/New Zealand
t 0402-794-347

China
t 86 21 2215 2888
f 86 21 6215 2988

India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291

Korea
t 82 2-796-9500
f 82 2-796-9300

Singapore
t 65 6733-6511
f 65 6861-2913

Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France
t 0800 916 882
f 0800 918 636

Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries

t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA Brasil

t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico

t (52-81) 8158-8400
f (52-81) 8313-8589

CORNING | **FALCON®** **cellgro®** **AXYGEN®** **PYREX®** **GOSSELIN®**

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks. All other trademarks are the property of their respective owners.