

Axygen[®] Universal Pipette Tips

Redesigned for the modern researcher.













For more than 20 years, Axygen Universal pipette tips have set the standard for quality, accuracy, and precision in laboratories worldwide. Now redesigned to meet every researchers needs, the next generation of Axygen Universal pipette tips deliver improved pipettor compatibility, durable hinged racks, and a complete offering from 10 μ L to 1200 μ L. Featuring tips with extended length, wide bore designs for viscous solutions, and our proprietary Axygen MaxRecovery+™ technology, Axygen Universal pipette tips are sure to meet and exceed your liquid handling expectations.





- ▶ RNase-/DNase-free
- ▶ Nonpyrogenic
- ▶ Human gDNA-free
- ▶ USP Class VI polypropylene

Axygen Universal Filter Pipette Tips

Racked, Filtered

	Standard Surface Cat. No.	MaxRecovery+ Cat. No.	Volume (μ L)	Pack Type	Sterile	Quantity
	PTF-300-R-S	PTF-300-L-R-S	0.5 - 10	Fine point	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTXLF-10-R-S	PTXLF-10-L-R-S	0.5 - 10	Extended length, graduated, fine point	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTF-20-R-S	PTF-20-L-R-S	1 - 20	Beveled	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTF-100-R-S	PTF-100-L-R-S	1 - 100	Beveled	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTF-200-R-S	PTF-200-L-R-S	1 - 200	Graduated, fine point	Yes	96/rack, 10 racks/pack, 5 packs/case
	--	PTF-205-WB-L-R-S	1 - 200	Wide bore	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTF-350-R-S	PTF-350-L-R-S	1 - 300	Graduated, fine point	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTF-1000-R-S	PTF-1000-L-R-S	100 - 1000	Beveled, graduated	Yes	96/rack, 10 racks/pack, 5 packs/case
	--	PTF-1005-WB-L-R-S	100 - 1000	Wide bore	Yes	96/rack, 10 racks/pack, 5 packs/case
	PTF-1200-C-R-S	PTF-1200-L-R-S	100 - 1200	Fine point	Yes	96/rack, 8 racks/pack, 4 packs/case

Reload, Filtered

	PRFLF-300-C-S	PRFLF-300-C-L-S	0.5 - 10	Fine point	Yes	96/deck, 5 decks/pack, 10 packs/case
	PRFLTFLF-10-C-S	PRFLTFLF-10-C-L-S	0.5 - 10	Extended length, graduated, fine point	Yes	96/deck, 5 decks/pack, 10 packs/case
	PRFLF-200-C-S	PRFLF-200-C-L-S	1 - 200	Graduated, fine point	Yes	96/deck, 5 decks/pack, 10 packs/case
	PRFLF-1000-C-S	PRFLF-1000-C-L-S	100 - 1000	Beveled, graduated	Yes	96/deck, 5 decks/pack, 10 packs/case

Axygen® Universal Pipette Tips

10 µL Fine Point



Standard Surface Cat. No.	MaxRecovery+™ Cat. No.	Volume (µL)	Pack Type	Sterile	Quantity
PT-300	PT-300-L	0.5 - 10	Bulk	No	1,000/pack, 10 packs/case
PT-300-R	PT-300-L-R	0.5 - 10	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PT-300-R-S	PT-300-L-R-S	0.5 - 10	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case
PRFL-300-C	PRFL-300-C-L	0.5 - 10	Reload	No	96 tips/deck, 10 decks/pack, 5 packs/case

10 µL Extended Length, Graduated, Fine Point



PTXL-10	PTXL-10-L	0.5 - 20	Bulk	No	1,000/pack, 10 packs/case
PTXL-10-R	PTXL-10-L-R	0.5 - 20	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PTXL-10-R-S	PTXL-10-L-R-S	0.5 - 20	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case
PRFL-TXL-10-C	PRFL-TXL-10-C-L	0.5 - 20	Reload	No	96/rack, 10 racks/pack, 5 packs/case

200 µL Clear



PT-200-C	PT-200-C-L	1 - 200	Bulk	No	1,000/pack, 10 packs/case
PT-200-C-R	PT-200-C-L-R	1 - 200	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PT-200-C-R-S	PT-200-C-L-R-S	1 - 200	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case
PT-200-C-STK	PT-200-C-L-STK	1 - 200	Stack rack	No	200/deck, 5 decks/pack, 10 packs/case
PT-200-C-STK-S	PT-200-C-L-STK-S	1 - 200	Stack rack	Yes	200/deck, 5 decks/pack, 10 packs/case
PRFL-200-C	PRFL-200-C-L	1 - 200	Reload	No	96 deck, 10 decks/pack, 5 packs/case

200 µL Beveled, Yellow



PT-200-Y	PT-200-Y-L	1 - 200	Bulk	No	1,000/pack, 10 packs/case
PT-200-Y-R	PT-200-Y-L-R	1 - 200	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PT-200-Y-R-S	PT-200-Y-L-R-S	1 - 200	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case
PT-200-Y-STK	PT-200-Y-STK	1 - 200	Stack rack	No	200/deck, 5 decks/pack, 10 packs/case

200 µL Wide Bore



--	PT-205-WB-C-L	1-200	Bulk	No	1,000/pack, 10 packs/case
--	PT-205-WB-L-R	1-200	Racked	No	96/rack, 10 racks/pack, 5 packs/case
--	PT-205-WB-L-R-S	1-200	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case

Axygen® Universal Pipette Tips

300 µL Graduated, Fine Point



Standard Surface Cat. No.	MaxRecovery+™ Cat. No.	Volume (µL)	Pack Type	Sterile	Quantity
PT-350-C	PT-350-C-L	1 - 300	Bulk	No	1,000/pack, 10 packs/case
PT-350-C-R	PT-350-C-L-R	1 - 300	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PT-350-C-R-S	PT-350-C-L-R-S	1 - 300	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case

1000 µL Graduated, Beveled, Clear



PT-1000-C	PT-1000-C-L	100 - 1000	Bulk	No	1,000/pack, 10 packs/case
PT-1000-C-R	PT-1000-C-L-R	100 - 1000	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PT-1000-C-R-S	PT-1000-C-L-R-S	100 - 1000	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case
PRFL-1000-C	PRFL-1000-C-L	100 - 1000	Reload	No	96/deck, 10 decks/pack, 5 packs/case

1000 µL Graduated, Beveled, Blue



PT-1000-B	PT-1000-B-L	100 - 1000	Bulk	No	1,000/pack, 10 packs/case
PT-1000-B-R	PT-1000-B-L-R	100 - 1000	Racked	No	96/rack, 10 racks/pack, 5 packs/case
PT-1000-B-R-S	PT-1000-B-L-R-S	100 - 1000	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case

1000 µL Wide Bore



--	PT-1005-WB-C-L	100 - 1000	Bulk	No	1,000/pack, 10 packs/case
--	PT-1005-WB-C-L-R	100 - 1000	Racked	No	96/rack, 10 racks/pack, 5 packs/case
--	PT-1005-WB-L-R-S	100 - 1000	Racked	Yes	96/rack, 10 racks/pack, 5 packs/case

1200 µL Fine point



PT-1200-C	PT-1200-C-L	1 - 1200	Bulk	No	1,000/pack, 10 packs/case
PT-1200-R	PT-1200-L-R	1 - 1200	Racked	No	96/rack, 8 racks/pack, 4 packs/case
PT-1200-R-S	PT-1200-L-R-S	1 - 1200	Racked	Yes	96/rack, 8 racks/pack, 4 packs/case

Empty Racks for Reloads

Cat. No.	Description	Sterile	Quantity
PRFL-R-300	Empty Rack for 10 µL	No	10/pack, 5/case
PRFL-R-200	Empty Rack for 200 µL	No	10/pack, 5/case
PRFL-R-1000	Empty Rack for 1000 µL	No	10/pack, 5/case

Axygen Macrovolume Pipette Tips

Cat. No.	Description	Pack Type	Sterile	Quantity
T-5000-C	5 mL, clear	Bulk	No	250 tips/pack, 10 packs/case
T-10ML-C	10 mL, clear	Bulk	No	100 tips/pack, 20 packs/case

How to Purchase: For specific availability in your region and purchasing options, terms and conditions of sale, customer/product support, and certificates, visit www.corning.com/how-to-buy.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.

CORNING

Corning Incorporated
Life Sciences

www.corning.com/lifesciences

NORTH AMERICA

t 800.492.1110
t 978.442.2200

ASIA/PACIFIC

Australia/New Zealand

t 61 427286832

Chinese Mainland

t 86 21 3338 4338

India

t 91 124 4604000

Japan

t 81 3-3586 1996

Korea

t 82 2-796-9500

Singapore

t 65 6572-9740

Taiwan

t 886 2-2716-0338

EUROPE

CSEurope@corning.com

France

t 0800 916 882

Germany

t 0800 101 1153

The Netherlands

t 020 655 79 28

United Kingdom

t 0800 376 8660

All Other European Countries

t +31 (0) 206 59 60 51

LATIN AMERICA

grupoLA@corning.com

Brazil

t 55 (11) 3089-7400

Mexico

t (52-81) 8158-8400

The information contained within is accurate as of the date of publication and subject to change without notice.

For a listing of trademarks, visit www.corning.com/trademarks. All other trademarks are the property of their respective owners.

© 2024, 2026 Corning Incorporated. All rights reserved. 2/26 CLS-LH-389 REV2