

CORNING



**Central Office  
Solutions**

						
	Centrix™	Centrix XL	EDGE™	EDGE8®	PasMAX™	Unisub HD
Main Attribute	Density		Density		Link Protection	Simplicity
HD – 3000+ Links (ports) per Frame	✓		✓			✓
Single-Circuit Management					✓	
Patch Cord Management in Frame	✓		✓		✓	✓
Left-to-Right Cross-Connect (central patch cord management)	✓		✓			✓
Splices Separated From Patches	✓				✓	✓
All-Front Access (wall/back-to-back)	✓				✓	✓
Mounting in 19-in Frame	✓		✓		✓	✓
Stubbed Hardware	✓		✓			✓
Rotating Trays					✓	✓
Port and Patch Cord Protection Cover	✓		✓		✓	✓
Plug & Play™ Pre-Terminated Option	✓		✓			
LC	✓		✓		✓	✓
SC	✓				✓	✓
LSH	✓				✓	
MPO	✓		✓			
Scaling Increment (fiber ports)	12		8	12	96	24
Ports in 2,200 mm Frame	4,320 LC	5,760 LC	5,760 LC		960 SC	3,840 LC
LC Ports per m²	16,000	18,300	11,520		2,666	14,222
Optical Device Integration	✓		✓		✓	✓
Zone 4 Rating (earthquake)	Special Frame Construction					
GR-449 Footprint	✓					
300 mm Depth	✓		*		✓	✓
Panel Material	Plastic		Plastic		Metal	Metal

\*special 300 mm housing required

# CORNING

Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, GERMANY  
+00 800 2676 4641 • FAX: +49 30 5303 2335 • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019, 2025 Corning Optical Communications. All rights reserved. CRR-947-A4-BEN / July 2025