



CORNING

Central Office Solutions

# CORNING



	Centrix™	EDGE™/EDGE8®	PasMAX™	RFO NG
Main Attribute	Density	Density	Link Protection	Rotation
HD – 3000+ Links (ports) per Frame	✓	✓		
Single-Circuit Management			✓	
Patch Cord Management in Frame	✓	✓	✓	
Left-to-Right Cross-Connect (central patch cord management)	✓	✓		
Splices Separated From Patches	✓		✓	✓
All-Front Access (wall/back-to-back)	✓		✓	
Mounting in 19-in Frame	✓	✓	✓	
Stubbed Hardware	✓	✓		✓
Rotating Trays			✓	✓
Port and Patch Cord Protection Cover	✓	✓	✓	✓
Plug & Play™ Pre-Terminated Option	✓	✓		✓
LC	✓	✓	✓	✓
SC	✓		✓	✓
LSH	✓		✓	
MPO	✓	✓		
Scaling Increment (fiber ports)	12	8/12	72	12
Ports in 2,200 mm Frame	4,320 LC	5,760 LC	1,440 LC	1,008
LC Ports per m <sup>2</sup>	17,280	11,520	4,000	4,032
Optical Device Integration	✓	✓	✓	✓
Zone 4 Rating (earthquake)	Special Frame Construction			
GR-449 Footprint	✓			
300 mm Depth	✓	✓	✓	✓
Panel Material	Plastic	Plastic	Metal	Plastic



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, GERMANY

+00 800 2676 4641 • FAX: +49 30 5303 2335 • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks).

All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019 Corning Optical Communications.

All rights reserved. CRR-947-A4-BEN / February 2019