

FastShip: Everon® copper solutions

Product availability is critical to your installations. Our FastShip programme for Everon® copper solutions quickly supports your day-to-day work, like moves, adds, and changes. The references listed in this document allow you to create end-to-end connections ready for shipment within 72 hours of purchase order confirmation.



Everon® Copper Solution, Cat.6_A,
Class EA Shielded Jack

Jacks to power your LAN and Data Center networks!

- Integrated, self-closing dust shutters, fail-safe connectivity.
- Three-way cable entry for flexibility.
- Compatibility with solid and stranded conductors, cross talk protection, and compatibility with Power over Ethernet applications.
- Environmentally friendly bulk packaging.

Everon Copper Datacom Jacks					
Part Number	Material Description	Legacy Part Number	Footprint	Jack Colour	Quantity in Pack
Cat.6 Unshielded					
XF500006424	V250U 3-Way Jack	VOLOCK6UHV	VOL	White	480
FQ100031241	E250U 2-Way Jack	OCK6UV	VOL	White	480
KAXVSM-00101-C001-BP	KS250U 3-Way Jack		Keystone	White	24
Cat.6 Shielded					
KAXESM-00101-C001-BP	KS250S 3-Way Jack		Keystone	White	24
XF500006028	V250S 3-Way Jack	VOLOCK6SHV	VOL	Silver	480
UU001520582	E250F 2-Way Jack	OCK6FV	VOL	White	480
Cat. 6 _A Unshielded					
KAXKSM-00104-C001-BP	KS500U 3-Way Jack		Keystone	White	24
XF500006440	V500U 3-Way Jack, Cat. 6 _A , Unshielded	VOLOCK6AUNV	VOL	White	480
Cat. 6 _A Shielded					
CAXASS-00100-C001	Field-Installable Shielded RJ45 Connector, Cat. 6 _A , 4 pairs				
CAXXSM-00104-C011-BP	xs500 1-Way Jack		Keystone	Silver	24
XF500003553	V500S 3-Way Jack	VOLOCK6ASN8	VOL	Silver	8
XF500003546	V500S 3-Way Jack	VOLOCK6ASNV	VOL	Silver	480
MAXBSM-00101-V001-BP	V500S 3-Way Jack	VOLOCK6ASNV	VOL	White	24
KAXBSM-00104-C001-BP	KS500S 3-Way Jack		Keystone	Silver	24



Cat. 6_A Shielded Copper Patch Cord (RJ45-RJ45)

Copper patch cords for office and industrial applications

Our copper patch cords can be used to connect to ports on a patch panel, switch, hub, or router or for bridging short distances between connection points. They are also suitable for connecting terminal devices to a data outlet.

Everon® Cat. 6 and Cat. 6_A Copper Patch Cords

Part Number	Material Description	Length	Jacket	Wire Diameter	Colour
Cat.6 Unshielded PVC Copper Patch Cords					
CCAVNE-D1002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	PVC	26 AWG	Grey
CCAVNE-D1002-A030-C0	U/UTP Patch Cord 2xRJ45	3 m	PVC	26 AWG	Grey
CCAVME-D2002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	PVC	24 AWG	Blue
Cat.6 Unshielded LSZH™ Copper Patch Cords					
CCAVGE-D1002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	LSZH	26 AWG	Grey
CCAVGE-D1002-A030-C0	U/UTP Patch Cord 2xRJ45	3 m	LSZH	26 AWG	Grey
CCAVGE-D1002-A050-C0	U/UTP Patch Cord 2xRJ45	5 m	LSZH	26 AWG	Grey
CCAVGE-D1002-A100-C0	U/UTP Patch Cord 2xRJ45	10 m	LSZH	26 AWG	Grey
Cat. 6 _A Unshielded LSZH Copper Patch Cords					
CCAKYE-G1002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	LSZH	24 AWG	Grey
CCAKYE-G1002-A030-C0	U/UTP Patch Cord 2xRJ45	3 m	LSZH	24 AWG	Grey
CCAKGE-G1002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	LSZH	26 AWG	Grey
CCAKGE-G1002-A030-C0	U/UTP Patch Cord 2xRJ45	3 m	LSZH	26 AWG	Grey
CCAKGE-G1002-A050-C0	U/UTP Patch Cord 2xRJ45	5 m	LSZH	26 AWG	Grey
CCAKGE-G1002-A100-C0	U/UTP Patch Cord 2xRJ45	10 m	LSZH	26 AWG	Grey
CCAKGE-G9002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	LSZH	26 AWG	White
CCAKGE-G9002-A030-C0	U/UTP Patch Cord 2xRJ45	3 m	LSZH	26 AWG	White
CCAKGE-G9002-A050-C0	U/UTP Patch Cord 2xRJ45	5 m	LSZH	26 AWG	White
CCAKGE-G9002-A100-C0	U/UTP Patch Cord 2xRJ45	10 m	LSZH	26 AWG	White
CCAKGE-G6002-A010-C0	U/UTP Patch Cord 2xRJ45	1 m	LSZH	26 AWG	Black
CCAKGE-G6002-A030-C0	U/UTP Patch Cord 2xRJ45	3 m	LSZH	26 AWG	Black
CCAKGE-G6002-A050-C0	U/UTP Patch Cord 2xRJ45	5 m	LSZH	26 AWG	Black
CCAKGE-G6002-A100-C0	U/UTP Patch Cord 2xRJ45	10 m	LSZH	26 AWG	Black
Cat. 6 _A Shielded LSZH Copper Patch Cords					
CCAAGB-G1002-A010-C0	S/FTP Patch Cord 2xRJ45	1 m	LSZH	26 AWG	Grey
CCAAGB-G1002-A020-C0	S/FTP Patch Cord 2xRJ45	2 m	LSZH	26 AWG	Grey
CCAAGB-G1002-A030-C0	S/FTP Patch Cord 2xRJ45	3 m	LSZH	26 AWG	Grey
CCAAGB-G1002-A050-C0	S/FTP Patch Cord 2xRJ45	5 m	LSZH	26 AWG	Grey



Everon Copper Datacom –
Keystone 24 Port Patch Panel

Patch panels for all configurations

Corning Everon® patch panels are universally applicable for all 19-inch racks. This allows the creation of user-specific building and floor distribution configurations. Patch panels offer rear wire management and are compatible with shielded and unshielded modules.

Everon® Copper Datacom Patch Panels

Part Number	Material Description	Colour	Footprint	Legacy Part Number
FQ100080610	1U 19-inch Patch Panel, 24 Ports (no cage nuts required)	Black	VOL	VOLSPK24
UU001622826	1U 19-inch Patch Panel, flat, 24 Ports with 24x E500S Jacks	Silver	VOL	PPCA1UF24 and VOLOCK6ASE
UU001622909	2U 19-inch Patch Panel, 48 Ports	Black	VOL	VOLPPCBF48K
KAXCSV-02408-C001	1U Copper Patch Panel (24x Keystone), flat	Black	Keystone	
MAXCSV-02408-C001	1U 19-inch Patch Panel, 24 Ports	Black	VOL	
KAXCSV-02400-C001	Patch Panel 19-inch Plus, 24 Ports	Silver	Keystone	
MAXCSV-02400-C001	Patch Panel 19-inch Plus, 24 Ports	Silver	VOL	
KAXCSV-02401-C001	Patch Panel 19-inch Plus, 24 Ports	White	Keystone	
UU009535251E	HD Patch Panel 19-inch Straight, 1U, 48 Ports	Silver		



Everon Copper Datacom Terminal Outlet VOL
and Keystone Combination Faceplate

Faceplates for smart presentation of your jacks

Everon copper faceplates ensure easy fitting and smart presentation of the RJ45 outlet. A label holder and white application icon give it a clean, functional appearance.

Everon Copper Faceplates and Outlets

Part Number	Material Description	Colour	Footprint	Quantity in Pack
Faceplate - UK - EUROMOD Standard				
UAXCSE-V0101-C010-BP	50x25 Inclined EUROMOD Adapter for 1 RJ45 Module	White	Keystone / VOL	24
CAXCSE-00001-C010-BP	50x12.5 EUROMOD Flat Blank Cover	White	Keystone / VOL	50
CAXCSE-00101-C010-BP	50x25 EUROMOD Flat Blank Cover	White	Keystone / VOL	50
CAXCSE-00201-C010-BP	50x50 EUROMOD Flat Full Blank Cover	White	Keystone / VOL	50
CAXCSE-00201-C011-BP	86x86 Single Gang EUROMOD Terminal Outlet - 2 Adapters	White	Keystone / VOL	12
CAXCSE-00401-C011-BP	146x86 Double Gang EUROMOD Terminal Outlet - 4 Adapters	White	Keystone / VOL	12
Faceplate - UK - LJ6C Standard				
UAXCSE-V0101-C020-BP	38x25 Inclined LJ6C Adapter for 1 RJ45 Module	White	Keystone / VOL	24
CAXCSE-00101-C020-BP	38x25 LJ6C Flat Blank Cover	White	Keystone / VOL	50
CAXCSE-00101-C021-BP	86x86 Single Gang LJ6C Terminal Outlet - 1 Adapter	White	Keystone / VOL	12
CAXCSE-00201-C021-BP	86x86 Single Gang LJ6C Terminal Outlet - 2 Adapters	White	Keystone / VOL	12
CAXCSE-00401-C021-BP	146x86 Double Gang LJ6C Terminal Outlet - 4 Adapters	White	Keystone / VOL	12
Faceplate - Middle East - Terminal Outlets Design				
XE005316874	VOL-FPUK-1K Faceplate White For 1 Jack	White	Keystone / VOL	200
Faceplate - France - 45x45 Standard				
UAXCSE-V0101-C030-BP	45x45 mm Inclined adapter for 1 RJ45 Module	White	Keystone / VOL	24
UAXCSE-V0201-C030-BP	45x45 mm Inclined adapter for 21 RJ45 Modules	White	Keystone / VOL	24
UAXCSE-V0101-C031-BP	25.5x45 mm Inclined adapter for 1 RJ45 Module	White	Keystone / VOL	24
Faceplate - DACH - 50x50 Standard				
UAXCSE-S0101-C040-BP	80x80 mm Inclined Terminal Outlet for 1 RJ45 Module	White	Keystone / VOL	12
UAXCSE-S0201-C040-BP	80x80 mm Inclined Terminal Outlet for 2 RJ45 Modules	White	Keystone / VOL	12
CAXCSE-00101-C041-BP	80x80 mm Faceplate for 1 x 50x50 Terminal Outlet	White	Keystone / VOL	12
CAXCSE-00001-C040	80x80 mm Surface Mounting Box for Faceplates	White	Keystone / VOL	1



Everon® Copper Datacom Cables

A comprehensive selection of Everon® Copper Cables

With this FastShip programme, Corning offers indoor, outdoor, and industrial data cables in a variety of categories, including Cat.6, Cat.6_A, Cat.7, and Cat.7_A. Multiple lengths are available with a variety of CPR categories, including the highest, B2Ca. The maximum length for the FastShip programme is 6 km and the minimum order is indicated for each cable in the table below.

Everon Copper Cables

Part Number	Material Description	Colour	Pairs	Jacket	MOQ* (Metres)	Design	CPR	AWG
Cat.6								
XE005319605	VOL6UP4305 UTP24, 4P, Cat.6, PVC	Light grey	4	PVC	305	U/UTP	Eca	24
DE010024334	VOL6UP4305 UTP/24, 4P, Cat.6, PVC	Green	4	PVC	305	U/UTP	Eca	24
UU009175397	VOL6UL4500 UTP24, 4P, Cat.6, LSZH	Green	4	LSZH™	500	U/UTP	B2ca-s1a, d0, a1	24
UU009120245	VOL6FL4500 F/UTP24, 4P, Cat.6, LSZH	Green	4	LSZH	500	F/UTP	Cca-s1a, d0, a1	24
UU009161587	VOL6UL4305 UTP24, 4P, Cat.6, LSZH	Green	4	LSZH	305	U/UTP	Cca-s1a, d0, a1	24
UU009175405	VOL6UL4500 UTP24,4P, Cat.6, LSZH	Green	4	LSZH	500	U/UTP	Cca-s1a, d0, a1	24
DE010024342	VOL6UL4305 UTP24, 4P, Cat.6, LSZH	Green	4	LSZH	305	U/UTP	Dca-s2, d2, a1	24
DE010024359	VOL6UL41000 UTP24,4P, Cat 6, LSZH	Green	4	LSZH	1000	U/UTP	Dca-s2, d2, a1	24
CCXDDA-D0047-C001-L7	F/FTP 450/23, 4P, Cat.6, LSZH	Blue	4	LSZH/FRNC	1000	F/FTP	Dca-s1, d1, a1	23
CCXEDE-DD047-V004-L6	F/UTP 450/23, 4P, Cat.6, LSZH	Green	4	LSZH	500	F/UTP	Dca-s2, d2, a1	23
Cat.6_A								
CCXEDR-D0047-C003-L7	S/FTP 550/23s, 4P, Cat.6 _A , LSZH	Blue	4	LSZH	1000	S/FTP	Dca-s1, d1, a1	23
CCXEDA-D0047-C001-L7	F/FTP 550/23,4P, Cat.6 _A , LSZH	Blue	4	LSZH/FRNC	1000	F/FTP	Dca-s1, d1, a1	23
CCXEDA-D0047-C001-L6	F/FTP 550/23, 4P, Cat.6 _A , LSZH	Blue	4	LSZH/FRNC	500	F/FTP	Dca-s1, d1, a1	23
CCXEDR-D0047-C003-L6	S/FTP 550/23s, 4P, Cat.6 _A , LSZH	Blue	4	LSZH	500	S/FTP	Dca-s1, d1, a1	23
CCXEDA-D0087-C001-L6	F/FTP 550/23, 2x4P, Cat.6 _A , LSZH	Blue	8	LSZH/FRNC	3000	F/FTP	Dca-s1, d1, a1	23
CCXEAA-D0047-C001-L7	F/FTP 550/23, 4P, Outdoor, Cat.6 _A , PE	Black	4	PE	3000	F/FTP	Fca	23
CCXEDB-DC047-C001-L7	S/FTP 550/23, 4P, Cat.6 _A , LSZH	Blue	4	LSZH/FRNC	1000	S/FTP	Cca-s1a, d1, a1	23
CCXEDB-DC047-C001-L6	S/FTP 550/23, 4P, Cat.6 _A , LSZH	Blue	4	LSZH/FRNC	500	S/FTP	Cca-s1a, d1, a1	23
UU009161595	VOL6AUL4500 UTP/24,4P, Cat.6 _A , LSZH	Green	4	LSZH	500	U/UTP	Cca-s1a, d0, a1	24
UU009175728	VOL6AFL4500 F/UTP24, 4P, Cat.6 _A , LSZH	Green	4	LSZH	500	F/UTP	B2ca-s1a, d0, a1	24
UU009175736	VOL6AFL4500 F/UTP24, 4P, Cat.6 _A , LSZH	Green	4	LSZH	500	F/UTP	Cca-s1a, d0, a1	24
UU004891568	VOL6AUL4500 UTP/24, 4P, Cat.6 _A , LSZH	Green	4	LSZH	500	U/UTP	Eca	24
MCXEDA-DD047-V004-L7	VOL6AUFL41000 U/FTP23, 4P, Cat.6 _A , LSZH	Green	4	LSZH	1000	U/FTP	Dca-s1, d1, a1	23
CCXEDA-DC047-C001-L6	F/FTP 550/23, 4P, Cat.6 _A , LSZH	Blue	4	LSZH/FRNC	500	F/FTP	Cca-s1, d1, a1	23
CCXEDA-DC087-C001-L6	F/FTP 550/23, 2x4P, Cat.6 _A , LSZH	Blue	8	LSZH/FRNC	500	F/FTP	Cca-s1, d1, a1	23
MCXEDA-DD047-V001-L7	U/FTP23, 4P, Cat.6 _A , LSZH	Blue	4	LSZH	3000	U/FTP	Dca-s1, d1, a1	23
CCXADE-DD047-V004-L6	F/UTP 550/23, 4P, Cat.6 _A , LSZH	Green	4	LSZH	500	F/UTP	Dca-s2, d2, a1	23
Cat.7								
CCXEDB-F0047-C001-L7	S/FTP 800/23, 4P, Cat.7, LSZH	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s1, d1, a1	23
CCXSDB-F0047-C001-L7	S/FTP 800/23, 4P, Outdoor	Black	4	PE	1000	S/FTP Outdoor	Fca	23
CCXEDR-F0047-C001-L7	S/FTP 800/23s, 4P, Cat.7, LSZH	Blue	4	LSZH	1000	S/FTP	Dca-s2, d2, a1	23
MCXEDB-FC047-V004-L7	VOL10SFL41000 S/FTP23, 4P, Cat.7, LSZH	Green	4	LSZH	1000	S/FTP	Cca-s1a, d1, a1	23
UU009120229	VOL10SFL4500 S/FTP23, 4P, Cat.7, LSZH	Green	4	LSZH	500	S/FTP	Cca-s1a, d1, a1	23
UU008185157	VOL10SFL41000 S/FTP23,4P, Cat.7, LSZH	Green	4	LSZH	1000	S/FTP	Dca-s2, d2, a1	23

*MOQ: Minimum Order quantity

Everon® Copper Cables (continued)

Part Number	Material Description	Colour	Pairs	Jacket	MOQ* (Metres)	Design	CPR	AWG
Cat. 7 _A								
CCXEDB-I0047-C001-L7	S/FTP 1000/23, 4P, Cat.7 _A , LSZH	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s1, d1, a1	23
CCXEDB-I0087-C001-L6	S/FTP1000/23, 2x4P, Cat.7 _A , LSZH	Blue	8	LSZH/FRNC	3000	S/FTP	Dca-s1, d1, a1	23
CCXFCB-L0047-C001-L7	S/FTP 1200/22, 4P, Cat.7 _A ⁺ , LSZH	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s2, d2, a1	22
CCXFCB-L0087-C001-L6	S/FTP1200/22, 2x4P, Cat.7 _A ⁺ , LSZH	Blue	8	LSZH/FRNC	1500	S/FTP	Dca-s1, d1, a1	22
CCXFCB-M0047-C001-L7	S/FTP1500/22, 4P, Cat.7 _A ⁺ , LSZH, BL	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s2, d2, a1	22
CCXFCB-I0047-C001-L7	S/FTP 1000/22, 4P, Cat.7 _A , LSZH, BL	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s1, d1, a1	22
CCXFCB-L0047-C002-L7	S/FTP1200/22, A-XR, 4P, Cat.7 _A ⁺ , LSZH	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s2, d2, a1	22
CCXFCR-I0047-C003-L7	S/FTP 1200/22s, 4P, Cat.7 _A ⁺ , LSZH	Blue	4	LSZH/FRNC	1000	S/FTP	Dca-s1, d1, a1	22
CCXSCB-LB047-C003-L7	S/FTP1200/22, A-XR, Outdoor, Cat.7 _A 4P, LSZH	Black	4	LSZH/FRNC	1000	S/FTP Outdoor	B2ca-s1a, d1, a1	22

*MOQ: Minimum Order quantity

CORNING

Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, GERMANY
+00 800 2676 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved. LAN-3469-A4-BEN / August 2025