

2178 Splice Closure XL/XLB/XSB

CORNING

2178 Splice Closure XL/XLB/XSB

CORNING

Ordering Information

Part Number	Product Description	Units Per Delivery
2178-XL-B-04-1R-8-U	2178-XL-8G, BEAD-BABA	Piece
2178-XL-B-04-1R-NN-N-U	2178-XL, BEAD-BABA	Piece
2178-XL-FR-B4-1R-N-U	2178-XL/FR, BEAD-BABA	Piece
2178-XLB-01G-3-0N-N-U	2178-XSB, 1-Tray 2532 Single Fusion, 3-Cable kits, No Ground, BEAD-BABA	Piece
2178-XLB-1T-2-0N-0N	2178-XLB, 1-Tray 2543-D-XSB Ribbon Fiber , 3-Cable kits, 2 Ground studs	Piece
2178-XLB-1T-2-0N-1G	2178-XLB, 1-Tray 2543-D-XSB Ribbon Fiber , 3-Cable kits, 1-Cable Kit for MiniXtend cables (2x8.1-8.6mm + 1x 10.8-11.3mm), 2 Ground studs	Piece
2178-XLB-B-3-NN-N	2178-XLB-EG-0T, BEAD-BABA	Piece
2178-XSB-1T-2-0N-0N	2178-XSB, 1-Tray 2543-D-XSB Ribbon fiber, 3-Cable kits, 2 Ground studs	Piece
2178-XSB-B2-1T-2-6PGA-U	2178-XSB, 1-Tray 2532 Single Fusion, 2-Cable kits, 1 Cable Kit for 6 FLAT cables, 2 Ground studs, BEAD-BABA	Piece
2178-XSB-B2-NN-2-U	2178-XSB, No Tray, 3-Cable kits, 2 Ground studs, BEAD-BABA	Piece
2178-XSB-B2-NN-N-U	2178-XSB, BEAD-BABA	Piece
2178-XSB-B3-01G-3-U	2178-XSB-B-02-01G-30N-0N, BEAD-BABA	Piece
2178-XSB-B3-1T-2-U	2178-XSB-EG-1T, BEAD-BABA	Piece
2178-XSB-EG-2T-U	2178-XSB, 1-Tray 2532 24 Single Fusion and 72 Ribbon fiber , 3-Cable kits, 2 Ground studs, BEAD-BABA	Piece
2178-XSB-FR-B-02-U	2178-XSB/FR/0G-0T, BEAD-BABA	Piece
2178XL-B-04-6R-4-0N-0N	2178-XL, 6-trays 2543-D 288 Ribbon Fiber, 4-Cable kits, 4 Ground studs	Piece
2178XL-B-04-6R-4-0N-0N-U	2178-XL, 6-trays 2543-D 288 Ribbon Fiber, 4-Cable kits, 4 Ground studs, BEAD-BABA	Piece
2178XL-B-08-12R-4-0N-0N	2178-XL, 1-Cable addition Kit, 12-trays 2543-D 288 Ribbon Fiber, 8-Cable kits, 4 Ground studs	Piece

2178 Splice Closure XL/XLB/XSB

CORNING

Part Number	Product Description	Units Per Delivery
2178XL-B-08-12R-4-0N-0N-U	2178-XL, 1-Cable addition Kit, 12-trays 2543-D 288 Ribbon Fiber, 8-Cable kits, 4 Ground studs, BEAD-BABA	Piece
2178XL-B-08-6R-4-0N-0N	2178-XL, 1-Cable addition Kit, 6-trays 2543-D 288 Ribbon Fiber, 8-Cable kits, 4 Ground studs	Piece
2178XL-B-08-6R-4-0N-0N-U	2178-XL, 1-Cable addition Kit, 6-trays 2543-D 288 Ribbon Fiber, 8-Cable kits, 4 Ground studs, BEAD-BABA	Piece
2181-XSB-FR-U	2178-XSB/XLB Cable Addition Kit, Flame Retardant, BEAD-BABA	Piece
2181-XSB-U	2178-XSB/XLB Cable Addition Kit, BEAD-BABA	Piece
80611174717	2178-XL/FR	Piece
80611304819	2178-XSB/FR/0G-0T	Piece
80611333867	2178-XSB/XLB Cable Addition Kit, Flame Retardant	Piece
80611486665	2178-XL	Piece
80611486673	2178-XL-8G	Piece
80611486681	2178-XSB, 1-Tray 2532 Single Fusion, 3-Cable kits, No Ground	Piece
80611486699	2178-XLB-EG-0T	Piece
80611486715	2178-XSB	Piece
80611486723	2178-XSB-B-02-01G-30N-0N	Piece
80611486731	2178-XSB, No Tray, 3-Cable kits, 2 Ground studs	Piece
80611486749	2178-XSB-EG-1T	Piece
80611486756	2178-XSB, 1-Tray 2532 Single Fusion, 2-Cable kits, 1 Cable Kit for 6 FLAT cables, 2 Ground studs	Piece
80611486764	2178-XSB, 1-Tray 2532 24 Single Fusion and 72 Ribbon fiber , 3-Cable kits, 2 Ground studs	Piece
80611486848	2178-XSB/XLB Cable Addition Kit	Piece

2178 Splice Closure XL/XLB/XSB

The Corning logo consists of the word "CORNING" in a white, serif, all-caps font, centered within a solid blue square.

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.