

Boot Clip, 90 Degree



Boot Clip, 90 Degree

CORNING

Specifications

General Specifications

Product Type	Accessories
Components	Boot clips

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Ordering Information

Product Number	boot-clip-90-degree
Packaging Method	Bulk Pack

Ordering Information

Part Number	Product Description	Units Per Delivery
95-400-02-BP	SC, bulk pack, (OM1/OM2/OM3/OM4/OM4+/OS2), clear	Piece
95-400-04-BPB	LC, bulk pack, 50 µm multimode (OM2), black	Piece
95-400-04-BPC	LC, bulk pack, (OM1/OM2/OM3/OM4/OM4+/OS2) clear	Piece
95-400-04-BPG	LC APC, bulk pack, Single-mode (OS2), green	Piece
95-400-04-BPN	LC, bulk pack, Single-mode (OS2), blue	Piece
95-400-04-BPR	LC, bulk pack, (OM1/OM2/OM3/OM4/OM4+/OS2), red	Piece
95-400-04-BPW	LC, bulk pack, (OM1/OM2/OM3/OM4/OM4+/OS2), white	Piece
95-400-04-BPY	LC, Enhanced Performance, bulk pack, Single-mode (OS2), yellow	Piece
BOOTCLIP-BP100	Bulk pack, metal	Piece

Boot Clip, 90 Degree

The Corning logo consists of the word "CORNING" in a white, serif, all-caps font, centered within a solid blue square.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.