

Boot Clips



Boot Clips

CORNING

Environmental Conditions

Temperature Range, Operation	-25 °C - 70 °C (-13 °F - 158 °F)
------------------------------	----------------------------------

Ordering Information

Part Number	Units per Delivery	Package Contents	Packaging Method
95-400-02-BP	100/1	100 boot clips, clear	Bulk Pack
95-400-04-BPB	100/1	100 boot clips, black	Bulk Pack
95-400-04-BPC	100/1	100 boot clips, clear	Bulk Pack
95-400-04-BPG	100/1	100 boot clips, green	Bulk Pack
95-400-04-BPN	100/1	100 boot clips, blue	Bulk Pack
95-400-04-BPR	100/1	100 boot clips, red	Bulk Pack
95-400-04-BPW	100/1	100 boot clips, white	Bulk Pack
95-400-04-BPY	100/1	100 boot clips, yellow	Bulk Pack
95-400-05-BPB	100/1	100 boot clips, black	Bulk Pack
95-400-05-BPC	100/1	100 boot clips, clear	Bulk Pack
95-400-05-BPG	100/1	100 boot clips, green	Bulk Pack
95-400-05-BPN	100/1	100 boot clips, blue	Bulk Pack
95-400-05-BPR	100/1	100 boot clips, red	Bulk Pack
95-400-05-BPW	100/1	100 boot clips, white	Bulk Pack
95-400-05-BPY	100/1	100 boot clips, yellow	Bulk Pack
95-400-13-BPW-NL	100/1	100 boot clips, white	Bulk Pack
BOOTCLIP-BP100	100/1	100 boot clips, metal	Bulk Pack



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.