

Closet Splice Housing (CSH)

CORNING

Corning closet splice housing (CSH) provides storage and protection of fiber splices in individually accessible trays. The housings are used in equipment racks or equipment cabinets, 19 in (48 cm) or 23 in (58 cm), and in the transition splice between outdoor-rated and riser/plenum-rated cable at a building entrance. Pigtail splicing is accomplished when the CSH is used in conjunction with a rack-mount housing. The CSH is available in 3-rack-space tall and 5-rack-space models. A sliding shelf provides access to splice trays and routing guides. The housing has top and bottom rear removable access panels for vertical pigtail entry from the CLSSC-03U or CLSSC-04U housings and lockable front and rear doors (with the optional lock kits).

Features and Benefits

Universal cable clamp

Cable strain-relief

Open-side design

Easy fiber egress

Projection- or flush-mountable

Various installation options

Multiple grommated cable entry ports

Installation options and protection



Closet Splice Housing (CSH)

Closet Splice Housing (CSH)

CORNING

Specifications

General Specifications

Product Type	Housings
--------------	----------

Design

Part Number	Housing Type	Splice Tray Options
CSH-03U	Closet Splice Housing (CSH)	Up to 12 category 2R, 2S or 2M
CSH-03U-F	Closet Splice Housing (CSH)	Up to 7 category 4R, 4S or 4A
CSH-05U	Closet Splice Housing (CSH)	Up to 22 category 2R, 2S or 2M
CSH-05U-F	Closet Splice Housing (CSH)	Up to 14 category 2R, 4S or 4A

Design Adapter

Part Number	Housing Color
CSH-03U	Black
CSH-03U-F	Black
CSH-05U	Black
CSH-05U-F	Black

Dimension

Part Number	Height	Width	Depth
CSH-03U	133 mm (5.24 in)	432 mm (17.01 in)	305 mm (12.01 in)
CSH-03U-F	133 mm (5.24 in)	432 mm (17.01 in)	305 mm (12.01 in)
CSH-05U	222 mm (8.74 in)	152.4 mm (6 in)	305 mm (12.01 in)
CSH-05U-F	222 mm (8.74 in)	152.4 mm (6 in)	305 mm (12.01 in)

Closet Splice Housing (CSH)

CORNING

Ordering Information

Part Number	Package Contents	Units per Delivery
CSH-03U	Closet Splice Housing 3U; Installation guide; 4 blank panels; Installation Kit; UCC Kit; #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Spiral Wrap, Tie Wraps	1/1
CSH-03U-F	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1
CSH-05U	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1
CSH-05U-F	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1

Closet Splice Housing (CSH)

The Corning logo consists of the word "CORNING" in white, uppercase, sans-serif font, centered within a solid blue square.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.