

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Specifications

General Specifications	
Application	FTTx
Cable type	Long Span All-Dielectric
Environment	Outdoor
Mounting Type	Strand mount , Pole-mount , Pedestal mount , Handhole mount
Preconnectorized "Stubbed" hardware	No
Product type	Evolv™ Terminal
Technology	Pushlok
Splice option	No

Design				
Part Number	Fibre count	Adapter colour front	Fibres per port	Adapter type front
DMA2F1LSD1NC010M0P	2	Black	1	Pushlok
DMA2F1LSD1NC050M0P	2	Black	1	Pushlok
DMA2F1LSD1NC100M0P	2	Black	1	Pushlok
DMA2F1LSD1NC500M0P	2	Black	1	Pushlok
DMA4F1LSD1NC010M0P	4	Black	1	Pushlok
DMA4F1LSD1NC050M0P	4	Black	1	Pushlok
DMA4F1LSD1NC100M0P	4	Black	1	Pushlok
DMA4F1LSD1NC500M0P	4	Black	1	Pushlok
DMA6F1LSD1NC010M0P	6	Black	1	Pushlok
DMA6F1LSD1NC050M0P	6	Black	1	Pushlok
DMA6F1LSD1NC100M0P	6	Black	1	Pushlok

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Design				
Part Number	Fibre count	Adapter colour front	Fibres per port	Adapter type front
DMA6F1LSD1NC500M0P	6	Black	1	Pushlok
DMB3F1LSD1NC100M0P	6	Black	1	Pushlok
DMB3F1LSD1NC250M0P	6	Black	1	Pushlok
DMB3F1LSD1NC500M0P	6	Black	1	Pushlok
DMB3F1LSD1NCA00M0P	6	Black	1	Pushlok
DMA8F1LSD1NC010M0P	8	Black	1	Pushlok
DMA8F1LSD1NC050M0P	8	Black	1	Pushlok
DMA8F1LSD1NC100M0P	8	Black	1	Pushlok
DMA8F1LSD1NC500M0P	8	Black	1	Pushlok
DMB4F1LSD1NC100M0P	8	Black	1	Pushlok
DMB4F1LSD1NC250M0P	8	Black	1	Pushlok
DMB4F1LSD1NC500M0P	8	Black	1	Pushlok
DMB4F1LSD1NCA00M0P	8	Black	1	Pushlok
DMATF1LSD1NC010M0P	12	Black	1	Pushlok
DMATF1LSD1NC050M0P	12	Black	1	Pushlok
DMATF1LSD1NC100M0P	12	Black	1	Pushlok
DMATF1LSD1NC500M0P	12	Black	1	Pushlok
DMB6F1LSD1NC010M0P	12	Black	1	Pushlok
DMB6F1LSD1NC050M0P	12	Black	1	Pushlok
DMB6F1LSD1NC100M0P	12	Black	1	Pushlok
DMB6F1LSD1NC500M0P	12	Black	1	Pushlok

Design				
Part Number	Input cable type	Housing material	Housing type	Housing colour
DMA2F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Input cable type	Housing material	Housing type	Housing colour
DMA2F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC250M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NCA00M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Design				
Part Number	Input cable type	Housing material	Housing type	Housing colour
DMB4F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC250M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NCA00M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Design			
Part Number	Number of ports	Input fibre count	Number of single-fibre ports, SC APC connector
DMA2F1LSD1NC010M0P	2	2	2
DMA2F1LSD1NC050M0P	2	2	2
DMA2F1LSD1NC100M0P	2	2	2
DMA2F1LSD1NC500M0P	2	2	2
DMA4F1LSD1NC010M0P	4	4	4

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Design			
Part Number	Number of ports	Input fibre count	Number of single-fibre ports, SC APC connector
DMA4F1LSD1NC050M0P	4	4	4
DMA4F1LSD1NC100M0P	4	4	4
DMA4F1LSD1NC500M0P	4	4	4
DMA6F1LSD1NC010M0P	6	6	6
DMA6F1LSD1NC050M0P	6	6	6
DMA6F1LSD1NC100M0P	6	6	6
DMA6F1LSD1NC500M0P	6	6	6
DMB3F1LSD1NC100M0P	6	6	6
DMB3F1LSD1NC250M0P	6	6	6
DMB3F1LSD1NC500M0P	6	6	6
DMB3F1LSD1NCA00M0P	6	6	6
DMA8F1LSD1NC010M0P	8	8	8
DMA8F1LSD1NC050M0P	8	8	8
DMA8F1LSD1NC100M0P	8	8	8
DMA8F1LSD1NC500M0P	8	8	8
DMB4F1LSD1NC100M0P	8	8	8
DMB4F1LSD1NC250M0P	8	8	8
DMB4F1LSD1NC500M0P	8	8	8
DMB4F1LSD1NCA00M0P	8	8	8
DMATF1LSD1NC010M0P	12	12	12
DMATF1LSD1NC050M0P	12	12	12
DMATF1LSD1NC100M0P	12	12	12
DMATF1LSD1NC500M0P	12	12	12
DMB6F1LSD1NC010M0P	12	12	12
DMB6F1LSD1NC050M0P	12	12	12
DMB6F1LSD1NC100M0P	12	12	12
DMB6F1LSD1NC500M0P	12	12	12

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design Adapter				
Part Number	Adapter housing colour	Adapter housing material	Adapter type	Adapter style
DMA2F1LSD1NC010M0P	Black	Plastic	Pushlok	SC APC
DMA2F1LSD1NC050M0P	Black	Plastic	Pushlok	SC APC
DMA2F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMA2F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC
DMA4F1LSD1NC010M0P	Black	Plastic	Pushlok	SC APC
DMA4F1LSD1NC050M0P	Black	Plastic	Pushlok	SC APC
DMA4F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMA4F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC
DMA6F1LSD1NC010M0P	Black	Plastic	Pushlok	SC APC
DMA6F1LSD1NC050M0P	Black	Plastic	Pushlok	SC APC
DMA6F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMA6F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC
DMA8F1LSD1NC010M0P	Black	Plastic	Pushlok	SC APC
DMA8F1LSD1NC050M0P	Black	Plastic	Pushlok	SC APC
DMA8F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMA8F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC
DMATF1LSD1NC010M0P	Black	Plastic	Pushlok	SC APC
DMATF1LSD1NC050M0P	Black	Plastic	Pushlok	SC APC
DMATF1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMATF1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC
DMB3F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMB3F1LSD1NC250M0P	Black	Plastic	Pushlok	SC APC
DMB3F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC
DMB3F1LSD1NCA00M0P	Black	Plastic	Pushlok	SC APC
DMB4F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMB4F1LSD1NC250M0P	Black	Plastic	Pushlok	SC APC
DMB4F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design Adapter

Part Number	Adapter housing colour	Adapter housing material	Adapter type	Adapter style
DMB4F1LSD1NCA00M0P	Black	Plastic	Pushlok	SC APC
DMB6F1LSD1NC010M0P	Black	Plastic	Pushlok	SC APC
DMB6F1LSD1NC050M0P	Black	Plastic	Pushlok	SC APC
DMB6F1LSD1NC100M0P	Black	Plastic	Pushlok	SC APC
DMB6F1LSD1NC500M0P	Black	Plastic	Pushlok	SC APC

Dimension

Part Number	Height	Width	Depth
DMA2F1LSD1NC010M0P	2997 mm	83.56 mm	154 mm
DMA2F1LSD1NC050M0P	2997 mm	83.56 mm	15392 mm
DMA2F1LSD1NC100M0P	2997 mm	83.56 mm	154 mm
DMA2F1LSD1NC500M0P	2997 mm	83.56 mm	154 mm
DMA4F1LSD1NC010M0P	2997 mm	83.56 mm	154 mm
DMA4F1LSD1NC050M0P	2997 mm	83.56 mm	154 mm
DMA4F1LSD1NC100M0P	2997 mm	83.56 mm	154 mm
DMA4F1LSD1NC500M0P	2997 mm	83.56 mm	154 mm
DMA6F1LSD1NC010M0P	2997 mm	134.36 mm	154 mm
DMA6F1LSD1NC050M0P	2997 mm	134.36 mm	154 mm
DMA6F1LSD1NC100M0P	2997 mm	134.36 mm	154 mm
DMA6F1LSD1NC500M0P	2997 mm	134.36 mm	154 mm
DMA8F1LSD1NC010M0P	2997 mm	134.36 mm	154 mm
DMA8F1LSD1NC050M0P	2997 mm	134.36 mm	154 mm
DMA8F1LSD1NC100M0P	2997 mm	134.36 mm	154 mm
DMA8F1LSD1NC500M0P	2997 mm	134.36 mm	154 mm
DMB6F1LSD1NC010M0P	5842 mm	134.36 mm	154 mm
DMB6F1LSD1NC050M0P	5842 mm	134.36 mm	154 mm
DMB6F1LSD1NC100M0P	5842 mm	134.36 mm	154 mm

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Dimension			
Part Number	Height	Width	Depth
DMB6F1LSD1NC500M0P	5842 mm	134.36 mm	15392 mm
DMB3F1LSD1NC100M0P	8356 mm	134.36 mm	15392 mm
DMB3F1LSD1NC250M0P	8356 mm	134.36 mm	154 mm
DMB3F1LSD1NC500M0P	8356 mm	134.36 mm	15392 mm
DMB3F1LSD1NCA00M0P	8356 mm	134.36 mm	154 mm
DMB4F1LSD1NC100M0P	8356 mm	134.36 mm	154 mm
DMB4F1LSD1NC250M0P	8356 mm	134.36 mm	154 mm
DMB4F1LSD1NC500M0P	8356 mm	134.36 mm	154 mm
DMB4F1LSD1NCA00M0P	8356 mm	134.36 mm	154 mm

Mechanical Specifications	
Cold mate/demate	Cable length
-40 °C	10 m
-40 °C	50 m
-40 °C	100 m
-40 °C	500 m
-40 °C	10 m
-40 °C	50 m
-40 °C	100 m
-40 °C	500 m
-40 °C	10 m
-40 °C	50 m
-40 °C	100 m
-40 °C	500 m
-40 °C	10 m
-40 °C	50 m
-40 °C	100 m

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Mechanical Specifications	
Cold mate/demate	Cable length
-40 °C	500 m
-40 °C	10 m
-40 °C	50 m
-40 °C	100 m
-40 °C	500 m
-40 °C	100 m
-40 °C	250 m
-40 °C	500 m
-40 °C	1000 m
-40 °C	100 m
-40 °C	250 m
-40 °C	500 m
-40 °C	1000 m
-40 °C	10 m
-40 °C	50 m
-40 °C	100 m
-40 °C	500 m



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
 +00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2024 Corning Optical Communications. All rights reserved.