

EDGE™ Preloaded Housings

The Corning logo is a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

Revolutionize your network infrastructure with our cutting-edge Preloaded Housing solution! Say goodbye to tedious manual module loading and embrace efficiency with our preloaded Edge and Edge8 housings. Experience seamless integration and rapid deployment, streamlining your operations while ensuring optimal performance. Plus, with an impressive 55% packaging weight reduction, you'll not only enjoy enhanced efficiency but also contribute to a greener, more sustainable future. Elevate your network capabilities with Corning's innovative solution, making the future of connectivity a reality today.

EDGE™ Preloaded Housings



Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Specifications

General Specifications	
Access Type	Front and rear access slidable
Application	Data Center , Enterprise Networks
Environment	Indoor
Product Type	Fiber Optic Hardware

Design			
Part Number	Cable entry type	Number of Panels	Panel or Module Type
EG01-UM0489G-04	Side brush entry	8	EDGE™
EG01-UM0489G-08	Side brush entry	8	EDGE™
EG01-UM0593Q-04	Side brush entry	8	EDGE™
EG01-UM0593Q-08	Side brush entry	8	EDGE™
EG02-UM0489G-12	Side brush entry	24	EDGE™
EG02-UM0489G-24	Side brush entry	24	EDGE™
EG02-UM0593Q-12	Side brush entry	24	EDGE™
EG02-UM0593Q-24	Side brush entry	24	EDGE™
EG04-UM0489G-24	Side brush entry	48	EDGE™
EG04-UM0489G-48	Side brush entry	48	EDGE™
EG04-UM0593Q-24	Side brush entry	48	EDGE™
EG04-UM0593Q-48	Side brush entry	48	EDGE™
EG1S-UM0489G-06	Side brush entry	12	EDGE™
EG1S-UM0489G-12	Side brush entry	12	EDGE™
EG1S-UM0593Q-06	Side brush entry	12	EDGE™
EG1S-UM0593Q-12	Side brush entry	12	EDGE™

EDGE™ Preloaded Housings

CORNING

Dimension	
Part Number	Height
EG01-UM0489G-04	44 mm (1.73 in)
EG01-UM0489G-08	44 mm (1.73 in)
EG01-UM0593Q-04	44 mm (1.73 in)
EG01-UM0593Q-08	44 mm (1.73 in)
EG1S-UM0489G-06	44 mm (1.73 in)
EG1S-UM0489G-12	44 mm (1.73 in)
EG1S-UM0593Q-06	44 mm (1.73 in)
EG1S-UM0593Q-12	44 mm (1.73 in)
EG02-UM0489G-12	88 mm (3.46 in)
EG02-UM0489G-24	88 mm (3.46 in)
EG02-UM0593Q-12	88 mm (3.46 in)
EG02-UM0593Q-24	88 mm (3.46 in)
EG04-UM0489G-24	177 mm (6.97 in)
EG04-UM0489G-48	177 mm (6.97 in)
EG04-UM0593Q-24	177 mm (6.97 in)
EG04-UM0593Q-48	177 mm (6.97 in)



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.