

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

The Corning logo consists of a solid blue square. Inside the square, the word "CORNING" is written in a white, serif, all-caps font, centered horizontally and vertically.

CORNING

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Application	FTTx
Cable Type	Long Span All-Dielectric
Environment	Outdoor
Mounting Type	Strand mount , Pole-mount , Pedestal mount , Handhole Mount
Preconnectorized "Stubbed" Hardware	No
Product Type	Evolv® Terminal™
Technology	Pushlok™
Splice option	No

Design

Part Number	Fiber Count	Adapter Color Front	Fibers per Port	Adapter Type Front
DMA2F1LSD1NC010M0P	2	Black	1	Pushlok™
DMA2F1LSD1NC050M0P	2	Black	1	Pushlok™
DMA2F1LSD1NC100F0P	2	Black	1	Pushlok™
DMA2F1LSD1NC100M0P	2	Black	1	Pushlok™
DMA2F1LSD1NC250F0P	2	Black	1	Pushlok™
DMA2F1LSD1NC500F0P	2	Black	1	Pushlok™
DMA2F1LSD1NC500M0P	2	Black	1	Pushlok™
DMA2F1LSD1NCA00F0P	2	Black	1	Pushlok™
DMA4F1LSD1NC010M0P	4	Black	1	Pushlok™
DMA4F1LSD1NC050M0P	4	Black	1	Pushlok™
DMA4F1LSD1NC100F0P	4	Black	1	Pushlok™

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Fiber Count	Adapter Color Front	Fibers per Port	Adapter Type Front
DMA4F1LSD1NC100M0P	4	Black	1	Pushlok™
DMA4F1LSD1NC250F0P	4	Black	1	Pushlok™
DMA4F1LSD1NC500F0P	4	Black	1	Pushlok™
DMA4F1LSD1NC500M0P	4	Black	1	Pushlok™
DMA4F1LSD1NCA00F0P	4	Black	1	Pushlok™
DMA6F1LSD1NC010M0P	6	Black	1	Pushlok™
DMA6F1LSD1NC050M0P	6	Black	1	Pushlok™
DMA6F1LSD1NC100F0P	6	Black	1	Pushlok™
DMA6F1LSD1NC100M0P	6	Black	1	Pushlok™
DMA6F1LSD1NC250F0P	6	Black	1	Pushlok™
DMA6F1LSD1NC500F0P	6	Black	1	Pushlok™
DMA6F1LSD1NC500M0P	6	Black	1	Pushlok™
DMA6F1LSD1NCA00F0P	6	Black	1	Pushlok™
DMB3F1LSD1NC100F0P	6	Black	1	Pushlok™
DMB3F1LSD1NC100M0P	6	Black	1	Pushlok™
DMB3F1LSD1NC250F0P	6	Black	1	Pushlok™
DMB3F1LSD1NC250M0P	6	Black	1	Pushlok™
DMB3F1LSD1NC500F0P	6	Black	1	Pushlok™
DMB3F1LSD1NC500M0P	6	Black	1	Pushlok™
DMB3F1LSD1NCA00F0P	6	Black	1	Pushlok™
DMB3F1LSD1NCA00M0P	6	Black	1	Pushlok™
DMA8F1LSD1NC010M0P	8	Black	1	Pushlok™
DMA8F1LSD1NC050M0P	8	Black	1	Pushlok™
DMA8F1LSD1NC100F0P	8	Black	1	Pushlok™
DMA8F1LSD1NC100M0P	8	Black	1	Pushlok™
DMA8F1LSD1NC250F0P	8	Black	1	Pushlok™
DMA8F1LSD1NC500F0P	8	Black	1	Pushlok™
DMA8F1LSD1NC500M0P	8	Black	1	Pushlok™

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Fiber Count	Adapter Color Front	Fibers per Port	Adapter Type Front
DMA8F1LSD1NCA00F0P	8	Black	1	Pushlok™
DMB4F1LSD1NC100F0P	8	Black	1	Pushlok™
DMB4F1LSD1NC100M0P	8	Black	1	Pushlok™
DMB4F1LSD1NC250F0P	8	Black	1	Pushlok™
DMB4F1LSD1NC250M0P	8	Black	1	Pushlok™
DMB4F1LSD1NC500F0P	8	Black	1	Pushlok™
DMB4F1LSD1NC500M0P	8	Black	1	Pushlok™
DMB4F1LSD1NCA00F0P	8	Black	1	Pushlok™
DMB4F1LSD1NCA00M0P	8	Black	1	Pushlok™
DMATF1LSD1NC010M0P	12	Black	1	Pushlok™
DMATF1LSD1NC050M0P	12	Black	1	Pushlok™
DMATF1LSD1NC100F0P	12	Black	1	Pushlok™
DMATF1LSD1NC100M0P	12	Black	1	Pushlok™
DMATF1LSD1NC250F0P	12	Black	1	Pushlok™
DMATF1LSD1NC500F0P	12	Black	1	Pushlok™
DMATF1LSD1NC500M0P	12	Black	1	Pushlok™
DMATF1LSD1NCA00F0P	12	Black	1	Pushlok™
DMB6F1LSD1NC010M0P	12	Black	1	Pushlok™
DMB6F1LSD1NC050M0P	12	Black	1	Pushlok™
DMB6F1LSD1NC100F0P	12	Black	1	Pushlok™
DMB6F1LSD1NC100M0P	12	Black	1	Pushlok™
DMB6F1LSD1NC250F0P	12	Black	1	Pushlok™
DMB6F1LSD1NC500F0P	12	Black	1	Pushlok™
DMB6F1LSD1NC500M0P	12	Black	1	Pushlok™
DMB6F1LSD1NCA00F0P	12	Black	1	Pushlok™

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Input Cable Type	Housing Material	Housing Type	Housing Color
DMA2F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA2F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA4F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Input Cable Type	Housing Material	Housing Type	Housing Color
DMA6F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA6F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC250M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB3F1LSD1NCA00M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Input Cable Type	Housing Material	Housing Type	Housing Color
DMA8F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMA8F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC250M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB4F1LSD1NCA00M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design				
Part Number	Input Cable Type	Housing Material	Housing Type	Housing Color
DMATF1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMATF1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC010M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC050M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC100F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC100M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC250F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC500F0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NC500M0P	Long Span All-Dielectric	Plastic	Outdoor	Black
DMB6F1LSD1NCA00F0P	Long Span All-Dielectric	Plastic	Outdoor	Black

Design			
Part Number	Number of Ports	Input Fiber Count	Number of single-fiber ports, SC APC connector
DMA2F1LSD1NC010M0P	2	2	2
DMA2F1LSD1NC050M0P	2	2	2
DMA2F1LSD1NC100F0P	2	2	2
DMA2F1LSD1NC100M0P	2	2	2
DMA2F1LSD1NC250F0P	2	2	2
DMA2F1LSD1NC500F0P	2	2	2
DMA2F1LSD1NC500M0P	2	2	2
DMA2F1LSD1NCA00F0P	2	2	2

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design			
Part Number	Number of Ports	Input Fiber Count	Number of single-fiber ports, SC APC connector
DMA4F1LSD1NC010M0P	4	4	4
DMA4F1LSD1NC050M0P	4	4	4
DMA4F1LSD1NC100F0P	4	4	4
DMA4F1LSD1NC100M0P	4	4	4
DMA4F1LSD1NC250F0P	4	4	4
DMA4F1LSD1NC500F0P	4	4	4
DMA4F1LSD1NC500M0P	4	4	4
DMA4F1LSD1NCA00F0P	4	4	4
DMA6F1LSD1NC010M0P	6	6	6
DMA6F1LSD1NC050M0P	6	6	6
DMA6F1LSD1NC100F0P	6	6	6
DMA6F1LSD1NC100M0P	6	6	6
DMA6F1LSD1NC250F0P	6	6	6
DMA6F1LSD1NC500F0P	6	6	6
DMA6F1LSD1NC500M0P	6	6	6
DMA6F1LSD1NCA00F0P	6	6	6
DMB3F1LSD1NC100F0P	6	6	6
DMB3F1LSD1NC100M0P	6	6	6
DMB3F1LSD1NC250F0P	6	6	6
DMB3F1LSD1NC250M0P	6	6	6
DMB3F1LSD1NC500F0P	6	6	6
DMB3F1LSD1NC500M0P	6	6	6
DMB3F1LSD1NCA00F0P	6	6	6
DMB3F1LSD1NCA00M0P	6	6	6
DMA8F1LSD1NC010M0P	8	8	8
DMA8F1LSD1NC050M0P	8	8	8
DMA8F1LSD1NC100F0P	8	8	8

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design			
Part Number	Number of Ports	Input Fiber Count	Number of single-fiber ports, SC APC connector
DMA8F1LSD1NC100M0P	8	8	8
DMA8F1LSD1NC250F0P	8	8	8
DMA8F1LSD1NC500F0P	8	8	8
DMA8F1LSD1NC500M0P	8	8	8
DMA8F1LSD1NCA00F0P	8	8	8
DMB4F1LSD1NC100F0P	8	8	8
DMB4F1LSD1NC100M0P	8	8	8
DMB4F1LSD1NC250F0P	8	8	8
DMB4F1LSD1NC250M0P	8	8	8
DMB4F1LSD1NC500F0P	8	8	8
DMB4F1LSD1NC500M0P	8	8	8
DMB4F1LSD1NCA00F0P	8	8	8
DMB4F1LSD1NCA00M0P	8	8	8
DMATF1LSD1NC010M0P	12	12	12
DMATF1LSD1NC050M0P	12	12	12
DMATF1LSD1NC100F0P	12	12	12
DMATF1LSD1NC100M0P	12	12	12
DMATF1LSD1NC250F0P	12	12	12
DMATF1LSD1NC500F0P	12	12	12
DMATF1LSD1NC500M0P	12	12	12
DMATF1LSD1NCA00F0P	12	12	12
DMB6F1LSD1NC010M0P	12	12	12
DMB6F1LSD1NC050M0P	12	12	12
DMB6F1LSD1NC100F0P	12	12	12
DMB6F1LSD1NC100M0P	12	12	12
DMB6F1LSD1NC250F0P	12	12	12
DMB6F1LSD1NC500F0P	12	12	12

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design

Part Number	Number of Ports	Input Fiber Count	Number of single-fiber ports, SC APC connector
DMB6F1LSD1NC500M0P	12	12	12
DMB6F1LSD1NCA00F0P	12	12	12

Design Adapter

Part Number	Housing Color	Housing Material	Adapter Type	Adapter Style
DMA2F1LSD1NC010M0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NC050M0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMA2F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC010M0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC050M0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMA4F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NC010M0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NC050M0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design Adapter				
Part Number	Housing Color	Housing Material	Adapter Type	Adapter Style
DMA6F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMA6F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC010M0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC050M0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMA8F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC010M0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC050M0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMATF1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NC250M0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMB3F1LSD1NCA00M0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Design Adapter

Part Number	Housing Color	Housing Material	Adapter Type	Adapter Style
DMB4F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NC250M0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC
DMB4F1LSD1NCA00M0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC010M0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC050M0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC100F0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC100M0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC250F0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC500F0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NC500M0P	Black	Plastic	Pushlok™	SC APC
DMB6F1LSD1NCA00F0P	Black	Plastic	Pushlok™	SC APC

Dimension

Part Number	Height	Width	Depth
DMATF1LSD1NC100F0P		100 ft	
DMATF1LSD1NC250F0P		250 ft	
DMATF1LSD1NC500F0P		500 ft	
DMATF1LSD1NCA00F0P		1000 ft	
DMA2F1LSD1NC010M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA2F1LSD1NC050M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	15392 mm (605.98 in)
DMA2F1LSD1NC100F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA2F1LSD1NC100M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA2F1LSD1NC250F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Dimension			
Part Number	Height	Width	Depth
DMA2F1LSD1NC500F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA2F1LSD1NC500M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA2F1LSD1NCA00F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC010M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC050M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC100F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC100M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC250F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC500F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NC500M0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA4F1LSD1NCA00F0P	2997 mm (117.99 in)	83.56 mm (3.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC010M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC050M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC100F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC100M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC250F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC500F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NC500M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA6F1LSD1NCA00F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC010M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC050M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC100F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC100M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC250F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC500F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NC500M0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMA8F1LSD1NCA00F0P	2997 mm (117.99 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB6F1LSD1NC010M0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed

CORNING

Dimension			
Part Number	Height	Width	Depth
DMB6F1LSD1NC050M0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB6F1LSD1NC100F0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB6F1LSD1NC100M0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB6F1LSD1NC250F0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB6F1LSD1NC500F0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB6F1LSD1NC500M0P	5842 mm (230 in)	134.36 mm (5.29 in)	15392 mm (605.98 in)
DMB6F1LSD1NCA00F0P	5842 mm (230 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB3F1LSD1NC100F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB3F1LSD1NC100M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	15392 mm (605.98 in)
DMB3F1LSD1NC250F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB3F1LSD1NC250M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB3F1LSD1NC500F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB3F1LSD1NC500M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	15392 mm (605.98 in)
DMB3F1LSD1NCA00F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB3F1LSD1NCA00M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NC100F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NC100M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NC250F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NC250M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NC500F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NC500M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NCA00F0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)
DMB4F1LSD1NCA00M0P	8356 mm (328.98 in)	134.36 mm (5.29 in)	154 mm (6.06 in)

Mechanical Specifications

Cold Mate/Demate	Cable Length
-40 °C (-40 °F)	10 m (32.8 ft)

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Mechanical Specifications	
Cold Mate/Demate	Cable Length
-40 °C (-40 °F)	50 m (164 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	10 m (32.8 ft)
-40 °C (-40 °F)	50 m (164 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	10 m (32.8 ft)
-40 °C (-40 °F)	50 m (164 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	10 m (32.8 ft)
-40 °C (-40 °F)	50 m (164 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Mechanical Specifications	
Cold Mate/Demate	Cable Length
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	10 m (32.8 ft)
-40 °C (-40 °F)	50 m (164 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	250 m (820 ft)
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	1000 m (3280 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	250 m (820 ft)
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft
-40 °C (-40 °F)	1000 m (3280 ft)
-40 °C (-40 °F)	10 m (32.8 ft)

Evolv® Terminals with Pushlok™ Technology, Long Span, Stubbed



Mechanical Specifications	
Cold Mate/Demate	Cable Length
-40 °C (-40 °F)	50 m (164 ft)
-40 °C (-40 °F)	100 ft
-40 °C (-40 °F)	100 m (328 ft)
-40 °C (-40 °F)	250 ft
-40 °C (-40 °F)	500 ft
-40 °C (-40 °F)	500 m (1640 ft)
-40 °C (-40 °F)	1000 ft



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.