

EDGE8® MTP® Extender Trunk

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Los troncales extensores MTP EDGE8 proporcionan distancia adicional para la red troncal de la solución EDGE8. Con un conector MTP sin patillas en un extremo del cable, un conector MTP con patillas en el otro extremo y una polaridad TIA-568 Tipo-A, estos troncales están diseñados para interactuar con un módulo universal de soluciones EDGE8 y un troncal MTP EDGE8. Todos los troncales se suministran con clips de alivio de tensión que permiten la instalación sin herramientas en carcasas de sistemas de soluciones EDGE8. Los troncales de extensión MTP se utilizan con mayor frecuencia en un área de distribución de zonas (ZDA).

Características y beneficios

Snap-in strain-relief clips

Provide easier cable management

Small outer diameter

Improves cable tray fill ratio and allows for imported airflow

Low-loss connectivity

Enables system design flexibility

Bend-improved fibre

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables

Tecnología Corning® CleanAdvantage™ y tapa antipolvo optimizada

Elimina la necesidad de examinar y de limpieza antes de la conexión inicial en el campo

Especificaciones

Normas

RoHS

Libre de sustancias peligrosas según RoHS 2011/65/EU

Ordering Information

Part Number	Product Description	Units Per Delivery
GE5E608QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E608TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E616QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E616TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E624QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E624TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E632QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece

EDGE8® MTP® Extender Trunk

CORNING

Part Number	Product Description	Units Per Delivery
GE5E632TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E648QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E648TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E672QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E672TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E696QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E696TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E808GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E816GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece

EDGE8® MTP® Extender Trunk

CORNING

Part Number	Product Description	Units Per Delivery
GE7E824GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E832GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E848GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E872GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E896GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

Una lista completa de las marcas registradas de Corning Comunicacoes Opticas se encuentra disponible en www.corning.com/opcomm/trademarks. Todas las otras marcas comerciales son propiedad de sus respectivos dueños. Corning Comunicacoes Opticas posee la certificación ISO 9001. © 2025 Corning Comunicacoes Opticas. Todos los derechos reservados.