

En tant que leader en connectivité optique, Corning conçoit et produit le câble ROC™ avec des connecteurs préterminés en usine, renforcés et étanches pour réduire le temps et le coût de déploiement. Les connecteurs renforcés Corning offrent une fiabilité et solidité durables dans la partie branchement du réseau. Cet assemblage offre aussi des améliorations significatives en gestion des câbles.

Avec le concept de câble ROC, les questions de capacité en stockage de câble sont inexistantes. Les câbles ROC sont plus flexibles, permettent un routage plus facile vers l'ONT. Les installateurs verront une réduction de la quantité d'espace nécessaire grâce à ce nouveau design.

Caractéristiques et Avantages

Connectique renforcée

Connecteur Pushlok au diamètre miniaturisé

Câ

Smaller profile and bend radius, flexibility allows for increased slack storage capacity in existing optical network terminals (ONTs), pedestals and handholes

Design renforcé

Large choix de connectique

hybrid assemblies with hardened connector (terminal) to SC APC (ONT)

Offre pour tous les types d'usage

Aerial: dielectric, self-supporting at 40 lbs installation tension at 150 ft (NESC Heavy), 255 ft (NESC Medium) or 330 ft (NESC Light) Direct-buried: toneable for easy locating Duct: integral pulling eye/connector cap designed for 100 lb maximum pulling tension

Spécifications

Spécifications générales

Solution	Evolv®
----------	--------

Normes

RoHS	Ne contient aucune substance dangereuse au sens de la directive RoHS 2011/65/EU
------	---

Ordering Information

Référence du produit	Product Description	Units Per Delivery
00D101JB49R010M	Pushlok® Pigtail, dielectric, 10 m, bulk packaging	Piece
00D101JB49R020M	Pushlok® Pigtail, dielectric, 20 m, bulk packaging	Piece
00D101JB49R040M	Pushlok® Pigtail, dielectric, 40 m, bulk packaging	Piece
00D101JB49R050M	Pushlok® Pigtail, dielectric, 50 m, bulk packaging	Piece
00D101JB49R060M	Pushlok® Pigtail, dielectric, 60 m, bulk packaging	Piece
00D101JB49R065M	Pushlok® Pigtail, dielectric, 65 m, bulk packaging	Piece
00D101JB49R075M	Pushlok® Pigtail, dielectric, 75 m, bulk packaging	Piece
00D101JB49R085M	Pushlok® Pigtail, dielectric, 85 m, bulk packaging	Piece
00D101JB49R100M	Pushlok® Pigtail, dielectric, 100 m, bulk packaging	Piece
00D101JB49R110M	Pushlok® Pigtail, dielectric, 110 m, bulk packaging	Piece
00D101JB49R150M	Pushlok® Pigtail, dielectric, 150 m, bulk packaging	Piece
00D101JB49R200M	Pushlok® Pigtail, dielectric, 200 m, bulk packaging	Piece

Evolv® ROC™ cordons pour câbles drop

CORNING

Référence du produit	Product Description	Units Per Delivery
00D101JB49R300M	Pushlok® Pigtail, dielectric, 300 m, bulk packaging	Piece
D1D101JB49R008M	Pushlok® dielectric, 8 m, bulk packaging	Piece
D1D101JB49R010M	Pushlok® dielectric, 10 m, bulk packaging	Piece
D1D101JB49R012M	Pushlok® dielectric, 12 m, bulk packaging	Piece
D1D101JB49R014M	Pushlok® dielectric, 14 m, bulk packaging	Piece
D1D101JB49R016M	Pushlok® dielectric, 16 m, bulk packaging	Piece
D1D101JB49R018M	Pushlok® dielectric, 18 m, bulk packaging	Piece
D1D101JB49R020M	Pushlok® dielectric, 20 m, bulk packaging	Piece
D1D101JB49R022M	Pushlok® dielectric, 22 m, bulk packaging	Piece
D1D101JB49R024M	Pushlok® dielectric, 24 m, bulk packaging	Piece
D1D101JB49R026M	Pushlok® dielectric, 26 m, bulk packaging	Piece
D1D101JB49R028M	Pushlok® dielectric, 28 m, bulk packaging	Piece
D1D101JB49R030M	Pushlok® dielectric, 30 m, bulk packaging	Piece
D1D101JB49R035M	Pushlok® dielectric, 35 m, bulk packaging	Piece
D1D101JB49R040M	Pushlok® dielectric, 40 m, bulk packaging	Piece
D1D101JB49R045M	Pushlok® dielectric, 45 m, bulk packaging	Piece
D1D101JB49R050M	Pushlok® dielectric, 50 m, bulk packaging	Piece
D1D101JB49R055M	Pushlok® dielectric, 55 m, bulk packaging	Piece
D1D101JB49R060M	Pushlok® dielectric, 60 m, bulk packaging	Piece
D1D101JB49R065M	Pushlok® dielectric, 65 m, bulk packaging	Piece

Evolv® ROC™ cordons pour câbles drop

CORNING

Référence du produit	Product Description	Units Per Delivery
D1D101JB49R070M	Pushlok® dielectric, 70 m, bulk packaging	Piece
D1D101JB49R075M	Pushlok® dielectric, 75 m, bulk packaging	Piece
D1D101JB49R080M	Pushlok® dielectric, 80 m, bulk packaging	Piece
D1D101JB49R085M	Pushlok® dielectric, 85 m, bulk packaging	Piece
D1D101JB49R100M	Pushlok® dielectric, 100 m, bulk packaging	Piece
D1D101JB49R110M	Pushlok® dielectric, 110 m, bulk packaging	Piece
D1D101JB49R150M	Pushlok® dielectric, 150 m, bulk packaging	Piece
D1D101JB49R200M	Pushlok® dielectric, 200 m, bulk packaging	Piece
D1D101JB49R300M	Pushlok® dielectric, 300 m, bulk packaging	Piece



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Allemagne
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea

Une liste complète des marques déposées de Corning Optical Communications est disponible à www.corning.com/opcomm/emea/trademarks. Corning Optical Communications est certifié selon la norme ISO 9001 et ISO 14001. © 2025 Corning Optical Communications. Tous droits réservés.