

EDGE8™ MTP® Extender Trunk



EDGE8® MTP® extender trunks provide additional distance for the backbone of the EDGE8 solution. With a non-pinned MTP connector on one end, a pinned MTP connector on the other, and TIA-568 Type-A polarity, these trunks are designed to interface with an EDGE8 solutions universal module and an EDGE8 MTP trunk. All extender trunks are manufactured with Corning® CleanAdvantage™ and shipped with strain-relief clips to allow easy tool-less installation. MTP extender trunks are most often used in a zone distribution area (ZDA).

Features and Benefits

Snap-in strain-relief clips


Provide easier cable management

Small outer diameter

Improves cable tray fill ratio and allows for imported airflow

Low-loss connectivity


Enables system design flexibility



Corning® CleanAdvantage™ technology and optimized dust cap

Eliminates the need for scoping and cleaning prior to initial field connection

Specifications

	
RoHS	 RoHS 2011/65/EU

Ordering Information

Part Number	Product Description	Units Per Delivery
GE5E608QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E608TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E616QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E616TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E624QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E624TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 feet	Piece
GE5E632QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece

EDGE8™ MTP® Extender Trunk

CORNING

Part Number	Product Description	Units Per Delivery
GE5E632TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E648QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E648TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E672QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E672TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E696QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E696TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E808GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E816GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece

EDGE8™ MTP® Extender Trunk

CORNING

Part Number	Product Description	Units Per Delivery
GE7E824GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E832GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E848GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E872GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E896GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 •  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.