

Fibre Optic Cleavers

CORNING



Fibre Optic Cleavers

Fibre Optic Cleavers

CORNING

Optical Specifications Connector

Part Number	Insertion loss, typical
80610755896	0.1 dB
80611494396	0.1 dB

Mechanical Specifications Fanout Kit

Depth
381 mm

Ordering Information

Part Number	Units per delivery	Package contents
80611323769	1/1	Includes the Fibrlok™ Assembly Tool 2501 for use with the Fibrlok™ Splice 2529, the Fibrlok™ Assembly Tool 2504G for use with the Fibrlok™ Splice 2540G, fiber cleaver, fiber stripping tool, snips, lint-free cloths, a cleaning alcohol bottle and splice holders
FBC-14-15-16-BLADE	1/1	Blade replacement kit
80610755896	6/1	
80611494396	60/1	



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.