

# Fiber Dome Stubbed Terminal



# Fiber Dome Stubbed Terminal



## Specifications

### General Specifications

|              |                  |
|--------------|------------------|
| Application  | Carrier Networks |
| Cable Type   | Flat Dielectric  |
| Environment  | Outdoor          |
| Product Type | Terminals        |

### Dimension

|             |        |
|-------------|--------|
| Part Number | Height |
| 80611497043 | 216 in |



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.