

High-Fiber-Count Furcation Kits

The CORNING logo is a dark blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

Features and Benefits

Bend-radius design consideration

Fiber protection

Fiber routing capabilities

Better fiber management

High-Fiber-Count Furcation Kits



Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Flame Test Method	Non-corrosive according to IEC 60754-2

Specifications

General Specifications

Product Type	Fan-out Kits
Compatibility	Ribbon Cable
Environment	Indoor

Mechanical Specifications Fanout Kit

Furcation Length	Tubing Outer Diameter
121.9 mm - 76.2 mm	0.25 mm - 6.35 mm

Ordering Information

Part Number	Units per Delivery	Package Contents
HFC-FURC-KIT-A	1/1	Braided tubing, vinyl tubing, adhesive aluminum foil, syringe, sandpaper, epoxy, transport tubing, grounding clamp, heat-shrink material
HFC-FURC-KIT-C	1/1	Braided tubing, vinyl tubing, adhesive aluminum foil, syringe, sandpaper, silicone sealant, transport tubing, grounding clamp, heat-shrink material, ribbon funnel kit
HFC-FURC-KIT-E	1/1	Braided tubing, vinyl tubing, adhesive aluminum foil, transport tubing, heat-shrink material, ribbon funnel kit

High-Fiber-Count Furcation Kits

The CORNING logo is displayed in white, uppercase letters within a solid blue square.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.