

Universal Routing Kit

CORNING

Universal Routing Kit for 24 and 36 Fiber Loose Tube Cable.
Examples: ALTOS HD and MiniXtend

Features and Benefits

Snap-together furcation

Eliminates epoxy

Fiber routing capabilities

Fusion Splicing

Direct Termination



Universal Routing Kit

Universal Routing Kit



RoHS			RoHS 2011/65/EU
------	--	--	-----------------

Specifications

Loose Tube Cable	
Loose Tube Cable	

-40 °C - 70 °C (-40 °F - 158 °F)	
-40 °C - 70 °C (-40 °F - 158 °F)	

Mechanical Specifications Fanout Kit	
Furcation Length	Tubing Length
59 in	1499 mm

Design Fanout Kits		
Part Number		
FUR-24F		24
FUR-36F		36

Ordering Information

Part Number		
FUR-24F	1/1	Fan-out top, fan-out bottom, fan-out tubing

Universal Routing Kit



Part Number	◆◆◆◆◆◆◆◆	◆◆◆◆◆
FUR-36F	1/1	Fan-out top, fan-out bottom, fan-out tubing



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • ◆◆
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.