

Features and Benefits

Universally applicable for all 19" rack

Suitable for all LANscape modules (FO and Copper)

Quick mount feature for easy one-person installation

Conductive front panel

Integrated cable strain relief

Two standardised grounding lashes for flat plugs

Integrated earthing points on the back side

Port numbering above and below ports

Space above ports can be used for customised labelling



Specifications

Environmental Conditions

Environmental Compatibility	Recyclable
-----------------------------	------------

Design

Housing Material	High-grade steel
Height Unit	1.5 U
Color	High-grade steel
Number of Ports	48

Mechanical Specifications

Cut Out	LANscape®
Housing Material	High-grade steel

General Specifications

Environment	Indoor
-------------	--------



Dimensions	
Height	152
Width	66
Depth	483

Ordering Information	
Units per Delivery	1/1

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Ordering Information

Part Number	WAXWSV-04800-C002
Product Description	The FutureCom™ patch panel is universally applicable for all 19-in racks and LAN-cabinets. This allows the free user-specific configuration of building and floor distributors. The front panel is electrically leading. Integrated grounding points are available at the back. Likewise for grounding 2 latches are available for flat connectors. Particularly to emphasize is the simple and fast installation and clicking of the modules into the patch panel.

**Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA • 800-743-2675
 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm**

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.

All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.