

ピペットチップ互換性チャート

ピペッターブランド	Capp Aero												Eppendorf®																									
ピペッターモデル	Capp Aero						Capp Aero 384 format 16/48/64			Electronic			Reference						Research																			
チャンネル	single/multi-channel						multi-channel			single/multi-channel			single/multi-channel						single channel																			
容量範囲	0.2-2 µL	0.5-10 µL	5-50 µL	10-100 µL	25-200 µL	50-300 µL	100-1000 µL	0.2-2 µL	0.5-10 µL	5-50 µL	0.5-10 µL	5-100 µL	2-200 µL	50-1000 µL	0.1-2.5 µL	0.1-10 µL	0.5-10 µL	2-20 µL 'UltraMicro'	2-20 µL	10-100 µL	20-200 µL	50-200 µL	100-1000 µL	0.1-2.5 µL	0.5-10 µL	2-20 µL	10-100 µL	20-200 µL	100-1000 µL	0.5-10 µL								
容量 / Axygenチップ	フィルターなし																																					
0.1-60 µL, T-384								●	●	●																												
0.1-30 µL, T-1536								●	●	●																												
0.1-10 µL, T-300	●	●									●					●	●	●								●	●								●			
0.1-10 µL, TXL-10	●	●									●					●	●	●								●	●								●			
0.1-20 µL, T-400																		●																				
1-200 µL, T-200			●	●	●	●						●	●						●	●	●	●										●	●	●				
1-200 µL, T-205-WB			●	●	●	●						●	●						●	●	●	●										●	●	●				
1-200 µL, TR-222			●	●	●	●						●	●						●	●	●	●										●	●	●				
1-300 µL, T-350				●	●	●						●	●							●	●	●										●	●					
100-1000 µL, T-1000							●							●											●										●			
100-1000 µL, T-1005-WB							●							●											●											●		
15-1250 µL, MTX-1250																																						
	フィルター付き																																					
0.1-10 µL, TF-300	●	●									●					●	●	●									●	●								●		
0.1-10 µL, TXLF-10	●	●									●					●	●	●									●	●									●	
0.1-10 µL, TF-400																		●																				
0.1-20 µL, TF-420																		●																				
0.5-20 µL, TF-20																		●																				
0.5-50 µL, TF-50			●																																			
1-100 µL, TF-100				●								●															●											
1-150 µL, TF-150																																						
1-200 µL, TF-200					●	●						●															●	●								●		
1-200 µL, TF-205-WB					●	●						●														●	●									●		
1-300 µL, TF-350						●																																
100-1000 µL, TF-1000							●							●												●											●	
100-1000 µL, TF-1005-WB							●							●												●											●	
100-1100 µL, TF-1200							●							●												●											●	
15-1250 µL, MTXF-1250																																						
1-10 µL, GEN3-10-L-R-S																●	●	●									●	●									●	
1-20 µL, GEN3-20-L-R-S																			●	●	●	●										●	●	●				
20-200 µL, GEN3-200-L-R-S																											●	●									●	
100-1000 µL, GEN3-1000-L-R-S																																						●

省略記号

m/ch = multi-channel

s/ch = single channel

ピペットチップ互換性チャート

ピベッターブランド	Socorex												VWR												
ピベッターモデル	Calibra/Accura												VWR and VWR Signature												
チャンネル	single channel						multi-channel						single channel						multi-channel						
容量範囲	0.1-2 µL	0.2-2 µL	0.5-10 µL	1-10 µL	2-20 µL	10-100 µL	20-200 µL	100-1000 µL	1-10 µL	5-50 µL	10-100 µL	20-200 µL	50-200 µL	0.1-2 µL	0.5-10 µL	2-20 µL	5-50 µL	10-100 µL	20-200 µL	50-250 µL	100-1000 µL	1-10 µL	5-50 µL	20-200 µL	50-300 µL
容量 / Axygenチップ	フィルターなし																								
0.1-60 µL, T-384																									
0.1-30 µL, T-1536																									
0.1-10 µL, T-300	●	●	●	●					●					●	●							●			
0.1-10 µL, TXL-10	●	●	●	●					●					●	●							●			
0.1-20 µL, T-400																									
1-200 µL, T-200					●	●	●			●	●	●	●		●	●	●	●	●	●			●	●	●
1-200 µL, T-205-WB					●	●	●			●	●	●	●		●	●	●	●	●	●			●	●	●
1-200 µL, TR-222					●	●	●			●	●	●	●		●	●	●	●	●	●			●	●	●
1-300 µL, T-350						●	●			●	●	●						●	●	●			●	●	●
100-1000 µL, T-1000								●													●				
100-1000 µL, T-1005-WB								●													●				
15-1250 µL, MTX-1250																									
	フィルター付き																								
0.1-10 µL, TF-300	●	●	●	●					●					●	●							●			
0.1-10 µL, TXLF-10	●	●	●	●					●					●	●							●			
0.1-10 µL, TF-400																									
0.1-20 µL, TF-420																									
0.5-20 µL, TF-20					●										●										
0.5-50 µL, TF-50									●							●						●			
1-100 µL, TF-100						●				●								●							
1-150 µL, TF-150																									
1-200 µL, TF-200							●				●	●						●	●				●	●	
1-200 µL, TF-205-WB							●				●	●						●	●				●	●	
1-300 µL, TF-350																				●					●
100-1000 µL, TF-1000								●													●				
100-1000 µL, TF-1005-WB								●													●				
100-1100 µL, TF-1200								●													●				
15-1250 µL, MTXF-1250																									
1-10 µL, GEN3-10-L-R-S																									
1-20 µL, GEN3-20-L-R-S						●									●				●				●		
20-200 µL, GEN3-200-L-R-S																		●	●						
100-1000 µL, GEN3-1000-L-R-S																					●				

省略記号

m/ch = multi-channel

s/ch = single channel