

# Corning® 5L Erlenmeyer Flasks

Efficient scale-up of suspension cultures

CORNING

The Corning 5L Erlenmeyer flask is designed to help scale-up suspension culture with space efficiency in mind. The flasks are sterile and ready-to-use, ideal for shaker culture applications, and storage.

## Materials

- ▶ Vessels are constructed from polycarbonate that is free of heavy metals. This USP Class VI material provides excellent optical clarity and mechanical strength.
- ▶ Caps are constructed from USP Class VI polypropylene that is free from heavy metals.

## Features

- ▶ Available with both baffled or plain bottom
- ▶ Molded-in graduations for accuracy
- ▶ Large vent cap for continuous gas exchange while ensuring sterility and preventing leakage
- ▶ Highest Sterility Assurance Level (SAL) of  $10^{-6}$
- ▶ Certified nonpyrogenic and RNase-/DNase-free
- ▶ Erlenmeyer flasks are autoclavable once at 121°C, 15 psi for 20 minutes. Repeated autoclaving weakens the flask and is not recommended. Vent cap is not autoclavable.

New!




## Corning® 5L Erlenmeyer Flasks Ordering Information

Cat. No.	Description	Qty/Pk	Qty/Cs
431684	5L Erlenmeyer flask, vent cap, baffled bottom	1	4
431685	5L Erlenmeyer, vent cap, plain bottom	1	4
431682	Vent cap for 5L Erlenmeyer flasks	1	24



For information on Corning's full range of Erlenmeyer flasks and other scale-up products including Corning HYPERStack® vessels and Corning microcarriers, please visit [www.corning.com/lifesciences](http://www.corning.com/lifesciences).



[www.corning.com/lifesciences/solutions](http://www.corning.com/lifesciences/solutions)

Corning single-use adhesion and suspension cell culture products enable scale-up in bioprocess manufacturing. From cell line development and process development to GMP manufacturing, our vessels provide the necessary platform to accomplish your goals. Supporting products such as Closed System Solutions, media, and advanced surfaces round out the product offering, providing a complete solution.

For additional product or technical information, please visit [www.corning.com/lifesciences](http://www.corning.com/lifesciences) or call 800.492.1110. Customers outside the United States, please call +1.978.442.2200 or contact your local Corning sales office.

### Corning Incorporated Life Sciences

836 North St.  
Building 300, Suite 3401  
Tewksbury, MA 01876  
t 800.492.1110  
t 978.442.2200  
f 978.442.2476

[www.corning.com/lifesciences](http://www.corning.com/lifesciences)

### Worldwide Support Offices

#### ASIA/PACIFIC

**Australia/New Zealand**  
t 0402-794-347

**China**  
t 86 21 2215 2888  
f 86 21 6215 2988

**India**  
t 91 124 4604000  
f 91 124 4604099

**Japan**  
t 81 3-3586 1996  
f 81 3-3586 1291

**Korea**  
t 82 2-796-9500  
f 82 2-796-9300

**Singapore**  
t 65 6733-6511  
f 65 6861-2913

**Taiwan**  
t 886 2-2716-0338  
f 886 2-2516-7500

### EUROPE

**France**  
t 0800 916 882  
f 0800 918 636

**Germany**  
t 0800 101 1153  
f 0800 101 2427

**The Netherlands**  
t 31 20 655 79 28  
f 31 20 659 76 73

**United Kingdom**  
t 0800 376 8660  
f 0800 279 1117

### All Other European Countries

t 31 (0) 20 659 60 51  
f 31 (0) 20 659 76 73

### LATIN AMERICA

**Brasil**  
t (55-11) 3089-7419  
f (55-11) 3167-0700

**Mexico**  
t (52-81) 8158-8400  
f (52-81) 8313-8589

**CORNING** | **FALCON**® **AXYGEN**® **GOSELIN**™ **PYREX**®

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For a listing of trademarks, visit us at [www.corning.com/lifesciences/trademarks](http://www.corning.com/lifesciences/trademarks). All other trademarks are the property of their respective owners.