


Axygen® Horizontal Gel Boxes



Axygen horizontal gel boxes are high-quality, full-featured units designed for exceptional durability and efficiency. The gel boxes feature leak-free external gel casting, which allows you to cast one gel outside of the box while another gel is running inside. The units are available in four different sizes, and each unit comes with two sizes of gel trays. In addition, they have easy to replace electrodes that are recessed to reduce potential damage. These gel boxes are an excellent value that will provide years of reliable service.

Features

- ▶ Flexibility – Each unit comes with 2 sizes of gel trays to optimize applications
- ▶ External gel casting to gel box allows for running gels while casting the next one.
- ▶ Ease of use – the Axygen contrast enhancer makes loading gels easier.
- ▶ Rugged injection molding is supported by a 3-year warranty.
- ▶ Larger units come with recirculation ports allowing for buffer exchange.



Axygen® Horizontal Gel Boxes

Four sizes of horizontal tanks. Each comes with 2 sizes of gel trays which allow for external gel casting. Three larger sizes come with recirculation ports for use as needed.



HGB-7

Tray sizes 7 x 7 cm, 7 x 10 cm

Recirculation ports No

Combs 2 x 8 well, 1.5 mm thickness




HGB-10

Tray sizes 10 x 10 cm, 10 x 12 cm

Recirculation ports Yes

Combs 2 x 10 multi-channel compatible well, 1.5 mm thickness




HGB-15

Tray sizes 15 x 10 cm, 15 x 15 cm

Recirculation ports Yes

Combs 1 x 16 multi-channel compatible well, 1.5 mm thick
1 x 20 well, 1.5 mm thickness



HGB-20

Tray sizes 20 x 20 cm, 20 x 25 cm

Recirculation ports Yes

Combs 2 x 20 multi-channel compatible well, 1.5 mm thickness
2 x 40 multi-channel compatible well, 1.5 mm thickness

Ordering Information

Combs and Accessories

Axygen Horizontal Gel Box, 7 cm

Corning Cat. No.	Description	Qty/Cs
HGB-7	Axygen horizontal gel box, 7 cm	1
HGB7-5-15	5-well comb for use with 7 cm gel box, 1.5 mm thickness	1
HGB7-8-075	8-well comb for use with 7 cm gel box, 0.75 mm thickness	1
HGB7-8-1	8-well comb for use with 7 cm gel box, 1.0 mm thickness	1
HGB7-10-1	10-well comb for use with 7 cm gel box, 1.0 mm thickness	1
HGB7-10-15	10-well comb for use with 7 cm gel box, 1.5 mm thickness	1
HGB7-12MC-1	12-well multi-channel compatible comb for use with 7 cm gel box, 1.0 mm thickness	1
HGB7-12MC-15	12-well multi-channel compatible comb for use with 7 cm gel box, 1.5 mm thickness	1
HGB7-16-1	16-well comb for use with 7 cm gel box, 1.0 mm thickness	1
HGB7-16-15	16-well comb for use with 7 cm gel box, 1.5 mm thickness	1

Axygen Horizontal Gel Box, 10 cm

Corning Cat. No.	Description	Qty/Cs
HGB-10	Axygen horizontal gel box, 10 cm	1
HGB10-8-1	8-well comb for use with 10 cm gel box, 1.0 mm thickness	1
HGB10-10MC-1	10-well multi-channel compatible comb for use with 10 cm gel box, 1.0 mm thickness	1
HGB10-10MC-15	10-well multi-channel compatible comb for use with 10 cm gel box, 1.5 mm thickness	1
HGB10-12-075	12-well comb for use with 10 cm gel box, 0.75 mm thickness	1
HGB10-12-1	12-well comb for use with 10 cm gel box, 1.0 mm thickness	1
HGB10-12-15	12-well comb for use with 10 cm gel box, 1.5 mm thickness	1
HGB10-16-075	16-well comb for use with 10 cm gel box, 0.75 mm thickness	1
HGB10-16-1	16-well comb for use with 10 cm gel box, 1.0 mm thickness	1
HGB10-16-15	16-well comb for use with 10 cm gel box, 1.5 mm thickness	1
HGB10-16-2	16-well comb for use with 10 cm gel box, 2.0 mm thickness	1
HGB10-20MC-1	20-well multi-channel compatible comb for use with 10 cm gel box, 1.0 mm thickness	1
HGB10-20MC-15	20-well multi-channel compatible comb for use with 10 cm gel box, 1.5 mm thickness	1
HGB10-25-1	25-well comb for use with 10 cm gel box, 1.0 mm thickness	1
HGB10-25-2	25-well comb for use with 10 cm gel box, 2.0 mm thickness	1

Axygen® Horizontal Gel Box, 15 cm

Corning Cat. No.	Description	Qty/Cs
HGB-15	Axygen horizontal gel box, 15 cm	1
HGB15-8-15	8-well comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-10-1	10-well comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-10-15	10-well comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-12-1	12-well comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-12-15	12-well comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-14MC-1	14-well multi-channel compatible comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-14MC-15	14-well multi-channel compatible comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-14MC-2	14-well multi-channel compatible comb for use with 15 cm gel box, 2.0 mm thickness	1
HGB15-16-1	16-well comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-16MC-1	16-well multi-channel compatible comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-16MC-15	16-well multi-channel compatible comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-16MC-2	16-well multi-channel compatible comb for use with 15 cm gel box, 2.0 mm thickness	1
HGB15-18MC-1	18-well multi-channel compatible comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-18MC-15	18-well multi-channel compatible comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-20-075	20-well comb for use with 15 cm gel box, 0.75 mm thickness	1
HGB15-20-1	20-well comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-20-15	20-well comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-20-2	20-well comb for use with 15 cm gel box, 2.0 mm thickness	1
HGB15-28MC-075	28-well multi-channel compatible comb for use with 15 cm gel box, 0.75 mm thickness	1
HGB15-28MC-1	28-well multi-channel compatible comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-28MC-15	28-well multi-channel compatible comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-30MC-1	30-well multi-channel compatible comb for use with 15 cm gel box, 1.0 mm thickness	1
HGB15-30MC-15	30-well multi-channel compatible comb for use with 15 cm gel box, 1.5 mm thickness	1
HGB15-35-15	35-well comb for use with 15 cm gel box, 1.5 mm thickness	1

Axygen Horizontal Gel Box, 20 cm

Corning Cat. No.	Description	Qty/Cs
HGB-20	Axygen horizontal gel box, 20 cm	1
HGB20-16-075	16-well comb for use with 20 cm gel box, 0.75 mm thickness	1
HGB20-20MC-075	20-well comb for use with 20 cm gel box, 0.75 mm thickness	1
HGB20-20MC-1	20-well multi-channel compatible comb for use with 20 cm gel box, 1.0 mm thickness	1
HGB20-20MC-15	20-well multi-channel compatible comb for use with 20 cm gel box, 1.5 mm thickness	1
HGB20-25-1	25-well comb for use with 20 cm gel box, 1.0 mm thickness	1
HGB20-30-1	30-well comb for use with 20 cm gel box, 1.0 mm thickness	1
HGB20-40MC-1	40-well multi-channel compatible comb for use with 20 cm gel box, 1.0 mm thickness	1
HGB20-40MC-15	40-well multi-channel compatible comb for use with 20 cm gel box, 1.5 mm thickness	1
HGB20-40MC-2	40-well multi-channel compatible comb for use with 20 cm gel box, 2.0 mm thickness	1
HGB20-50-2	50-well comb for use with 20 cm gel box, 2.0 mm thickness	1

Gel Trays

HGB7-7-GT	Gel tray 7 x 7 cm for use with 7 cm gel box, UV transparent	1
HGB7-10-GT	Gel tray 7 x 10 cm for use with 7 cm gel box, UV transparent	1
HGB10-10-GT	Gel tray 10 x 10 cm for use with 10 cm gel box, UV transparent	1
HGB15-10-GT	Gel tray 15 x 10 cm for use with 15 cm gel box, UV transparent	1
HGB15-15-GT	Gel tray 15 x 15 cm for use with 15 cm gel box, UV transparent	1
HGB20-20-GT	Gel tray 20 x 20 cm for use with 20 cm gel box, UV transparent	1

Replacement Electrodes

HGB7-NE	Replacement negative electrode, 7 cm	1
HGB7-PE	Replacement positive electrode, 7 cm	1
HGB10-NE	Replacement negative electrode, 10 cm	1
HGB10-PE	Replacement positive electrode, 10 cm	1
HGB15-NE	Replacement negative electrode, 15 cm	1
HGB15-PE	Replacement positive electrode, 15 cm	1
HGB20-NE	Replacement negative electrode, 20 cm	1
HGB20-PE	Replacement positive electrode, 20 cm	1

Rubber Casting Dams

HGB7-CD	Casting dams for use with 7 cm gel box, set of 2	1
HGB10-CD	Casting dams for use with 10 cm gel box, set of 2	1
HGB15-CD	Casting dams for use with 15 cm gel box, set of 2	1
HGB20-CD	Casting dams for use with 20 cm gel box, set of 2	1

Accessories

HGB7-AD	Power supply adapters, 4 mm to 4 mm, 2/pk	1
HGB7-AD2	Power supply adapters, 4 mm to 2 mm, 2/pk	1
HGB-EL	Electrical leads (1 pair)	1

Related Products



Axygen® Gel Documentation Systems

Corning Cat. No.	Description	Qty/Pk	Qty/Cs
GD-1000	Gel Documentation System	1	1
GDBL-1000	Gel Documentation System-BL	1	1

Axygen Gel Cutting Pipet Tips

TGL-1165-R	1.1 x 6.5 mm racked gel cutting pipet tip	480	2,400
TGL-1165	1.1 x 6.5 mm gel cutting pipet tip	250	2,500
TGL-1140-R	1.1 x 4 mm racked gel cutting pipet tip	480	2,400
TGL-1140	1.1 x 4 mm gel cutting pipet tip	250	2,500

Axygen Gel Loading Pipet Tips

TGL-10FT-17-R	0.17 mm, 10 µL racked flat gel loading pipet tip	400	400
TGL-200FT-37-R-S	0.37 mm, 200 µL racked flat gel loading pipet tip, sterile	400	400
TGL-200FT-37-R	0.37 mm, 200 µL racked flat gel loading pipet tip	400	400
TGL-200RD-57-R-S	0.57 mm, 200 µL racked round gel loading tip, sterile	400	400
TGL-200RD-57-R	0.57 mm, 200 µL racked round gel loading tip	400	400

Axygen DNA Markers

M-DNA-100BP	100 bp DNA ladder	500 µL	500 µL
M-DNA-1KB	1 kb DNA ladder	500 µL	500 µL

Axygen Agarose

AGR-LE-100	Agarose LE, low EEO, molecular biology grade, 100 g	1	1
AGR-LE-1001	Agarose LE, low EEO, molecular biology grade, 100 g	10	10
AGR-LE-500	Agarose LE, low EEO, molecular biology grade, 500 g	1	1
AGR-LE-5001	Agarose LE, low EEO, molecular biology grade, 500 g	10	10
AGR-LM-50	Agarose LM, low melting, molecular biology grade, 50 g	1	1
AGR-LM-501	Agarose LM, low melting, molecular biology grade, 50 g	10	10
AGR-LM-100	Agarose LM, low melting, molecular biology grade, 100 g	1	1
AGR-LM-1001	Agarose LM, low melting, molecular biology grade, 100 g	10	10
AGR-MS-50	Agarose MS, PCR screening, molecular biology grade, 50 g	1	1
AGR-MS-501	Agarose MS, PCR screening, molecular biology grade, 50 g	10	10
AGR-MS-100	Agarose MS, PCR screening, molecular biology grade, 100 g	1	1
AGR-MS-1001	Agarose MS, PCR screening, molecular biology grade, 100 g	10	10

Corning® Buffers

46-011-CM	10X TBE buffer, liquid	6 x 1L	6 x 1L
46-010-CM	10X TAE buffer, liquid	6 x 1L	6 x 1L

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For additional product or technical information, visit www.corning.com/lifesciences, or contact our Scientific Support Team at ScientificSupportEMEA@corning.com.

Corning Incorporated Life Sciences Europe

Corning BV
Fogostaat 12
1060 LJ Amsterdam
The Netherlands
Phone: +31 (0) 20 659 60 51
Fax: +31 (0) 20 659 76 73
CEurope@corning.com
www.corning.com/lifesciences

Support Offices

EUROPE

France
t 0800 916 882
f 0800 918 636
Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 31 20 655 79 28
f 31 20 659 76 73
United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries
t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

CORNING | **FALCON** | **AXYGEN** | **GOSSELIN**

For a listing of trademarks, visit www.corning.com/clstrademarks.
All other trademarks are the property of their respective owners.