

CORNING

Special Offer

Precision Meets Savings -- Automate Your Lab for Less

Buy 3 Cases of Participating* Products, Get 1 Case at No Additional Cost

For purchases from August 1, 2025 through December 31, 2025

*Participating Products

Axygen® Automation Tips for Tecan Automation Systems

Cat. No.	Description	Qty/Pk	Qty/Cs
TT-200-C-HTR-S	200 µL, clear, non-filtered, sterile	96	2,304
TT-200-C-HTR	200 µL, clear, non-filtered, nonsterile	96	2,304
TT-200-CBK-HTR-S	200 µL, Liquid level sensing, non-filtered, sterile	96	2,304
TT-200-CBK-HTR	200 µL, Liquid level sensing, non-filtered, nonsterile	96	2,304
TT-1000-C-HTR-S	1000 µL, clear, non-filtered, sterile	96	1,536
TT-1000-C-HTR	1000 µL, clear, non-filtered, nonsterile	96	1,536
TT-1000-CBK-HTR-S	1000 µL, Liquid level sensing, non-filtered, sterile	96	1,536
TT-1000-CBK-HTR	1000 µL, Liquid level sensing, non-filtered, nonsterile	96	1,536

Axygen Automation Tips for Beckman Coulter Automation Systems

FXF-384-XL-R-S	30 µL, clear, filtered, sterile	384	19,200
FX-384-R-S	30 µL, clear, non-filtered, sterile	384	19,200
FX-384-30FP-R-S	30 µL, clear, non-filtered, sterile	384	19,200
FX-384-R	30 µL, clear, non-filtered, nonsterile	384	19,200
FX-384-45FP-R	45 µL, clear, non-filtered, nonsterile	384	19,200
FX-384-XL-R-S	50 µL, clear, non-filtered, sterile	384	19,200
FX-384-XL-R	50 µL, clear, non-filtered, nonsterile	384	19,200

Axygen Single Well Reagent Reservoirs

RES-SW96-LP	96-bottom, troughs, low profile, nonsterile	1	25
RES-SW384-HP-SI	384-bottom, troughs, high profile, individually wrapped, sterile	1	25
RES-SW384-LP	384-bottom, troughs, low profile, nonsterile	1	25
RES-SW384-LP-SI	384-bottom, troughs, low profile, individually wrapped, sterile	1	25

Axygen Maxyclear Snaplock Microcentrifuge Tubes

MCT-060-C	0.6 mL, Polypropylene, clear, non-sterile	1000	10,000
MCT-060-A	0.6 mL, Polypropylene, assorted, non-sterile	1000	10,000
MCT-150-C	1.5 mL, Polypropylene, clear, non-sterile	500	5,000
MCT-175-C	1.7 mL, Polypropylene, clear, non-sterile	500	5,000
MCT-175-A	1.7 mL, Polypropylene, assorted, non-sterile	500	5,000
MCT-200-C	2.0 mL, Polypropylene, clear, non-sterile	500	5,000
MCT-200-A	2.0 mL, Polypropylene, assorted, non-sterile	500	5,000

Axygen PCR Microplates

PCR-96-FS-C	96-well clear Polypropylene frame, full skirt, nonsterile	10	50
P-DW-500-C	96-well clear V-bottom, 600 µL deep well Polypropylene, nonsterile	5	50
PCR-96-EPF-B-C	96-well, blue Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, full skirt, compatible with Eppendorf pipettors	10	50
PCR-96-EPF-C-C	96-well, clear Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, full skirt, compatible with Eppendorf pipettors	10	50
PCR-96-BRF-C-C	96-well, clear Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, compatible with Bio-Rad pipettors	10	50
PCR-96-BRF-B-C	96-well, blue Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, compatible with Bio-Rad pipettors	10	50
PCR-96-EPF-B-C	96-well, blue Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, half skirt, compatible with Eppendorf pipettors	10	50
PCR-96-EPF-C-C	96-well, clear Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, half skirt, compatible with Eppendorf pipettors	10	50
PCR-384-FS-C-C	384-well, clear Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, universal fit	10	50
PCR-384-FS-B-C	384-well, blue Polycarbonate frame, clear Polypropylene tubes, ANSI footprint, universal fit	10	50

Continued on next page

Axygen® Sealing Film

Cat. No.	Description	Qty/Pk	Qty/Cs
PCR-SP	80 µm AxySeal for tissue culture, short-term storage and transportation, nonsterile	100	500
UC-500	70 µm Ultra clear pressure sensitive for real time PCR, nonsterile	100	500

Corning® Flat bottom, TC-treated Microplates

3603	96-well black/clear flat bottom, Polystyrene, individually wrapped, with lid, sterile	1	48
3610	96-well white/clear flat bottom, Polystyrene, individually wrapped, with lid, sterile	1	48
3596	Costar® 96-well clear flat bottom, Polystyrene, individually wrapped, with lid, sterile	1	50
3917	96-well white flat bottom, Polystyrene, with lid, sterile	20	100
3916	96-well black flat bottom, Polystyrene, with lid, sterile	20	100
3701	384-well clear flat bottom, Polystyrene, with lid, sterile	20	100
3764	384-well black/clear flat bottom, black Polystyrene, low flange, with lid, sterile	20	100
3765	384-well white/clear flat bottom, white Polystyrene, low flange, with lid, sterile	20	100
3570	384-well white flat bottom, Polystyrene, low flange, with lid, sterile	10	50
3571	384-well black flat bottom, Polystyrene, low flange, with lid, sterile	10	50

For purchases August 1, 2025 through December 31, 2025

To redeem this promotion:

- ▶ Redeem this promotion by visiting www.corning.com/promotions.
- ▶ Complete the web form, and use promotional code “**PRO-CLS3083**”.

Terms and Conditions: Offer valid in the U.S. and Canada only and void where prohibited by government, law, or company policy. Offer valid for end-user customers only for purchases from August 1, 2025 through December 31, 2025 or while supplies last. Redemption information must be received by January 15, 2026. Please allow 4 to 8 weeks for delivery of free product. ***Redeemed goods limited to 10 cases per lab and will be of lesser or equal value of the purchased product(s).**

How to Purchase: For specific availability in your region and purchasing options, terms and conditions of sale, customer/product support, and certificates, visit www.corning.com/how-to-buy.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only. Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

CORNING

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110.
Outside the United States, call +1.978.442.2200.

The information contained within is accurate as of the date of publication and subject to change without notice.
For a listing of trademarks, visit www.corning.com/trademarks. All other trademarks are the property of their respective owners.
© 2025 Corning Incorporated. All rights reserved. 8/25 PRO-CLS3083