

CORNING

Back to School Savings Limited Time Offers

BUY 5 cases of select Corning® media products and GET 2 cases of select Corning media products at no additional cost.

For purchases September 15, 2025, through December 31, 2025.

OFFER 1

BUY 5 cases of any of select* 500 mL media products listed below...

*Participating Products

Cat. No.	Description	Qty/Cs
15-012-CV	MEM (Minimum Essential Medium) Alpha medium, 500 mL	6
10-010-CV	MEM (Minimum Essential Medium) with Earle's salts, L-glutamine, 500 mL	
10-013-CV	DMEM (Dulbecco's Modified Eagle's Medium) with L-glutamine, high glucose, pyruvate, 500 mL	6
10-017-CV	DMEM, with L-glutamine, high glucose, 500 mL	6
10-090-CV	DMEM/Hams F-12 50/50 mix with L-glutamine, 500 mL	6
10-092-CV	DMEM/Hams F-12 50/50 mix with L-glutamine, 15 mM HEPES, 500 mL	6
10-080-CV	Hams F-12 medium with L-glutamine, 500 mL	6
10-050-CV	McCoy's 5A (Iwakata & Grace Modification) with L-glutamine, 500 mL	6
10-060-CV	Medium 199 (Mod.) with Earle's salts, L-glutamine, 500 mL	6
10-045-CV	Leibovitz's L-15 with L-glutamine, 500 mL	6
10-040-CV	RPMI 1640 with L-glutamine, 500 mL	6
10-041-CV	RPMI 1640 with L-glutamine, 25 mM HEPES, 500 mL	6
10-010-CV	MEM (Minimum Essential Medium) with Earle's salts, L-glutamine, 500 mL	6
10-016-CV	Iscove's Modification of DMEM with L-glutamine, 25 mM HEPES, 500 mL	6

OR

OFFER 2

BUY 5 cases of any of the select* 1L media products listed below...

*Participating Products

Cat. No.	Description	Qty/Cs
10-013-CM	DMEM, with L-glutamine, high glucose, pyruvate, 1L	6
10-017-CM	DMEM, with L-glutamine, high glucose, 1L	6
10-040-CM	RPMI 1640 with L-glutamine, 1L	6
10-010-CM	MEM with Earle's salts, L-glutamine, 1L	6

...GET 2 cases of select* 500 mL media products at no additional cost

*Participating Products

(Select 2 from below)

Cat. No.	Description	Qty/Cs
21-030-CV	Dulbecco's Phosphate-Buffered Saline, 1X with calcium and magnesium, 500 mL	6
21-031-CV	Dulbecco's Phosphate-Buffered Saline, 1X without calcium and magnesium, 500 mL	
21-040-CV	Phosphate-Buffered Saline, 1X without calcium and magnesium, PH 7.4 ± 0.1, 500 mL	6
21-022-CV	Hank's Balanced Salt Solution, 1X without calcium, magnesium and phenol red, 500 mL	6
25-055-CV	Cell culture grade water tested to USP sterile water for injection specifications, 500 mL	6
46-000-CV	Molecular biology grade water tested to USP sterile purified water specifications, 500 mL	6
10-016-CV	Iscove's Modification of DMEM with L-glutamine, 25 mM HEPES, 500 mL	6

...GET 2 cases of select* 1L media products at no additional cost.

*Participating Products

(Select 2 from below)

Cat. No.	Description	Qty/Cs
21-030-CM	Dulbecco's Phosphate-Buffered Saline, 1X with calcium and magnesium, 1L	6
21-031-CM	Dulbecco's Phosphate-Buffered Saline, 1X without calcium and magnesium, 1L	6
21-040-CM	Phosphate-Buffered Saline, 1X without calcium and magnesium, PH 7.4 ± 0.1, 1L	6
21-022-CM	Hank's Balanced Salt Solution, 1X without calcium, magnesium and phenol red, 1L	6
25-055-CM	Cell culture grade water tested to USP sterile water for injection specifications, 1L	6
46-000-CM	Molecular biology grade water tested to USP sterile purified water specifications, 1L	6

Continued on next page



For purchases September 15, 2025, through December 31, 2025

To redeem this promotion:

- ▶ Redeem this promotion by visiting www.corning.com/promotions.
- ▶ Complete the web form, and use promotional code “**PRO-CLS3085**”.

Terms and Conditions: Offer valid in the U.S. and Canada only and void where prohibited by government, law, or company policy. Offer valid for end-user customers only for purchases from September 15, 2025, through December 31, 2025 or while supplies last. Redemption information must be received by January 15, 2026. Please allow 4 to 6 weeks for delivery of free product.

*Purchases must be made on a single purchase order.

How to Purchase: For specific availability in your region and purchasing options, terms and conditions of sale, customer/product support, and certificates, visit www.corning.com/how-to-buy.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only. Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

CORNING

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110.
Outside the United States, call +1.978.442.2200.

The information contained within is accurate as of the date of publication and subject to change without notice.
For a listing of trademarks, visit www.corning.com/trademarks. All other trademarks are the property of their respective owners.
© 2025 Corning Incorporated. All rights reserved. 9/25 PRO-CLS3085