

# Purchase 3 Cases of Participating\* Corning® Media and Get 1 Case at No Additional Cost

For purchases from March 15, 2026 through June 30, 2026



CORNING

## Participating Products\*

### Corning Cell Culture Media

Cat. No.	Description	Size	Qty/Cs
10-013-CV	DMEM [+] 4.5 g/L glucose, L-glutamine, sodium pyruvate	500 mL	6
10-017-CV	DMEM [+] 4.5 g/L glucose, L-glutamine [-] sodium pyruvate	500 mL	6
10-014-CV	DMEM [+] 1.0 g/L glucose, sodium pyruvate, L-glutamine	500 mL	6
10-090-CV	DMEM/Ham's F-12 50/50 mix, (modified)	500 mL	6
10-092-CV	DMEM/Ham's F-12 50/50 mix, L-glutamine, 15 mM HEPES	500 mL	6
10-010-CV	MEM [+] Earle's salts, L-glutamine	500 mL	6
10-040-CV	RPMI 1640	500 mL	6
10-080-CV	Ham's F-12 Medium [+] L-glutamine	500 mL	6

### Corning Salt Solutions

Cat. No.	Description	Size	Qty/Cs
21-030-CV	DPBS, 1X with calcium and magnesium*	500 mL	6
21-031-CV	DPBS, 1X without calcium and magnesium*	500 mL	6
20-030-CV	DPBS, 10X with calcium and magnesium	500 mL	6
20-031-CV	DPBS, 10X without calcium and magnesium	500 mL	6
21-040-CV	PBS, 1X without calcium and magnesium*	500 mL	6
21-020-CV	HBSS, 1X with calcium and magnesium*	500 mL	6
21-023-CV	HBSS, 1X with calcium and magnesium without phenol red*	500 mL	6
21-022-CV	HBSS, 1X without calcium, magnesium and phenol red*	500 mL	6
20-023-CV	HBSS, 10X with calcium and magnesium without phenol red and sodium bicarbonate	500 mL	6
20-021-CV	HBSS, 10X without sodium bicarbonate, calcium and magnesium	500 mL	6

\*Available in 1L sizes as well

### Molecular Biology Grade Products

Cat. No.	Description	Size	Qty/Cs
46-000-CI	Water, molecular biology grade	100 mL	6
46-000-CV	Water, molecular biology grade	500 mL	6
46-000-CM	Water, molecular biology grade	1L	6
46-013-CM	PBS 10X, pH 7.4 ± 0.1, liquid without calcium and magnesium, RNase-/DNase- and protease-free	1L	6
46-050-CM	Millers LB Broth	1L	6
46-010-CM	TAE buffer 10X, liquid, pH 8.3 ± 0.1 RNase-/DNase- and protease-free	1L	6
46-011-CM	TBE buffer 10X, liquid, pH 8.4 ± 0.1 RNase-/DNase- and protease-free	1L	6
46-012-CM	TBS (Tris buffered saline) 10X, liquid, pH 7.4 ± 0.1 RNase-/DNase- and protease-free	500 mL	6

### Supplements

Cat. No.	Description	Size	Qty/Cs
25-055-CI	Water, cell culture grade, tested to USP sterile water for injection specifications	100 mL	6
25-055-CV	Water, cell culture grade, tested to USP sterile water for injection specifications	500 mL	6
25-055-CM	Water, cell culture grade, to USP sterile water for injection specifications	1L	6
25-005-CI	L-glutamine 200 mM solution, 29.23 mg/mL	100 mL	6
25-000-CI	Sodium pyruvate, liquid 100 mM solution [+] 8.5 g/L NaCl	100 mL	6
25-025-CI	MEM nonessential amino acids	100 mL	6
25-052-CI	Trypsin EDTA 1X, 0.05% Trypsin/0.53 mM EDTA in HBSS [-] sodium bicarbonate	100 mL	6
25-053-CI	Trypsin EDTA 1X, 0.25% Trypsin/2.21 mM EDTA in HBSS	100 mL	6
25-015-CI	Corning glutagro™ supplement 200 mM solution	100 mL	1
25-950-CQC	DMSO	250 mL	1

Continued on next page.

## Antibiotics

Cat. No.	Description	Size	Qty/Cs
30-001-CI	Penicillin-Streptomycin solution, 50X	100 mL	6
30-002-CI	Penicillin-Streptomycin solution, 100X	100 mL	6
30-003-CF	Amphotericin B, liquid	50 mL	6
30-004-CI	Antibiotic-Antimycotic solution	50 mL	6
30-005-CR	Gentamicin sulfate, liquid	10 mL	10
30-234-CR	G418 sulfate, liquid, 50 mg/mL solution	20 mL	1
61-234-RG	G418 sulfate, powder	5 g	1
30-240-CR	Hygromycin B solution	20 mL	1

(Other Supplements and Antibiotics available)

**For purchases from March 15, 2026 through June 30, 2026**

### To redeem this promotion:

- Redeem this promotion by visiting [www.corning.com/promotions](http://www.corning.com/promotions).
- Complete the web form, and use promotional code “**CLS3088**”.

**Terms and Conditions:** Offer valid in the U.S. and Canada only and void where prohibited by government, law, or company policy. Offer valid for end-user customers only for purchases from March 15, 2026 through June 30, 2026 or while supplies last. Redemption information must be received by July 15, 2026. Corning has the right to substitute products if required. Please allow 4 to 6 weeks for delivery. **Redemption limit of 10 free cases per lab. \*Products must be made on a single Purchase Order.**

**How to Purchase:** For specific availability in your region and purchasing options, terms and conditions of sale, customer/product support, and certificates, visit [www.corning.com/how-to-buy](http://www.corning.com/how-to-buy).

**Warranty/Disclaimer:** Unless otherwise specified, all products are for research use or general laboratory use only.\* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. \*For a listing of US medical devices, regulatory classifications or specific information on claims, visit [www.corning.com/resources](http://www.corning.com/resources).

*Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.*

# CORNING

For additional product or technical information, visit [www.corning.com/lifesciences](http://www.corning.com/lifesciences) or call 800.492.1110.  
Outside the United States, call +1.978.442.2200.

The information contained within is accurate as of the date of publication and subject to change without notice.  
For a listing of trademarks, visit [www.corning.com/trademarks](http://www.corning.com/trademarks). All other trademarks are the property of their respective owners.  
© 2026 Corning Incorporated. All rights reserved. 3/26 PRO-CLS3088