



CORNING



Charter-Approved Corning IP68 Rated CATV Node Assembly

Corning offers a full line of node service cables meeting IP68 performance. A broad range of approved configurations provide simple ordering with straight or 90-degree access connectors. For specialized applications, custom configurations can quickly be defined through our distribution partner, TVC.

Features and Benefits

- Eliminates additional splice points and hardware at the node location
- Provides protection against inside and outside water penetration
- Withstands pull-out force up to 400 lbs
- Provides maximum clearance inside the hardware
- Compact and rugged design
- Available in both straight and 90-degree access connectors
- Quick and easy to install
- IP68 rated

90-Degree Cable TV Node Assembly

SAP	Part Number	Product Description (90-degree CATV Node Assembly, 2 Connectors)
	2C9H2E0000-0F0100	2 F, 2 connectors (2 SC APC), ALTOS® gel-free cable, 25-in (3 mm) leg, 100 ft

SAP	Part Number	Product Description (90-degree CATV Node Assembly, 4 Connectors)
	4C9E4A0000-0F0080	4 F, 4 connectors (4 FC APC), ALTOS gel-free cable, 25-in (3 mm) leg, 80 ft

SAP	Part Number	Product Description (90-Degree CATV Node Assembly, 6 Connectors)
	6C9E6E0000-0F0100	6 F, 6 connectors (6 SC APC), ALTOS gel-free cable, 25-in (3 mm) leg, 100 ft
	6C9V6D0000-0F1250	6 F, 6 connectors (6 LC UPC), ALTOS gel-free cable, 25-in (2 mm) leg, 1,250 ft
	6C9V6E0000-0F0250	6 F, 6 connectors (6 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 250 ft
	6C9V6E0000-0F0500	6 F, 6 connectors (6 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 500 ft
	6E9E6E0000-0F0100	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 100 ft
	6E9E6E0000-0F0200	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 200 ft
	6E9E6E0000-0F0500	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 500 ft
	6E9E6G0000-0F0100	6 F, 6 connectors (6 SC UPC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 100 ft
	6E9F6A0000-0F0100	6 F, 6 connectors (6 FC APC), ALTOS gel-free armored cable, 25-in (900 µm) leg, 100 ft
	6E9F6B0000-0F0100	6 F, 6 connectors (6 FC UPC), ALTOS gel-free armored cable, 25-in (900 µm) leg, 100 ft
	6E9F6G0000-0F0100	6 F, 6 connectors (6 SC UPC), ALTOS gel-free armored cable, 25-in (900 µm) leg, 100 ft
	6E9Q6A0000-0F0075	6 F, 6 connectors (6 FC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 75 ft
	6E9Q6E0000-0F0075	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 75 ft
	6E9Q6E0000-0F0200	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 200 ft

SAP	Part Number	Product Description (90-Degree CATV Node Assembly, 12 Connectors)
	CC9Q4G8D00-0F0050	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free cable, 36-in (2 mm) leg, 50 ft
	CC9Q4G8D00-0F0100	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free cable, 36-in (2 mm) leg, 100 ft
	CC9Q4G8D00-0F0150	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free cable, 36-in (2 mm) leg, 150 ft
	CC9V8E4N00-0F0100	12 F, 12 connectors (8 SC APC/4 furcated legs), ALTOS gel-free cable, 25-in (2 mm) leg, 100 ft
	CC9V8E4N00-0F0500	12 F, 12 connectors (8 SC APC/4 furcated legs), ALTOS gel-free cable, 25-in (2 mm) leg, 500 ft
	CC9VCE0000-0F0100	12 F, 12 connectors (12 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 100 ft
	CC9VCE0000-0F0500	12 F, 12 connectors (12 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 500 ft
	CE9QCE0000-0F0100	12 F, 12 connectors (12 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 100 ft
	CE9QCE0000-0F0300	12 F, 12 connectors (12 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 300 ft

Straight Cable TV Node Assembly

SAP	Part Number	Product Description (Straight CATV Node Assembly, 2 Connectors)
1020323	2CSH2E0000-0F0100	2 F, 2 connectors (2 SC APC), ALTOS® gel-free cable, 36-in (3 mm) leg, 100 ft

SAP	Part Number	Product Description (Straight CATV Node Assembly, 4 Connectors)
1020334	4CSE4A0000-0F0080	4 F, 4 connectors (4 FC APC), ALTOS gel-free cable, 25-in (3 mm) leg, 80 ft

SAP	Part Number	Product Description (Straight CATV Node Assembly, 6 Connectors)
1034462	6ASF6E0000-0F0500	6 F, 6 connectors (6 SC APC), SST flat drop cable, 25-in (900 µm) leg, 500 ft
1020416	6ASF6E0000-0F0500	6 F, 6 connectors (6 SC APC), SST flat drop cable, 25-in (900 µm) leg, 500 ft
	6ASF6E0000-0F0650	6 F, 6 connectors (6 SC APC), SST flat drop cable, 25-in (900 µm) leg, 650 ft
1030196	6CSE6E0000-0F0100	6 F, 6 connectors (6 SC APC), ALTOS gel-free cable, 25-in (3 mm) leg, 100 ft
1010463	6CSV6D0000-0F1250	6 F, 6 connectors (6 LC UPC), ALTOS gel-free cable, 25-in (2 mm) leg, 1,250 ft
1020445	6CSV6E0000-0F0250	6 F, 6 connectors (6 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 250 ft
1010222	6CSV6E0000-0F0500	6 F, 6 connectors (6 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 500 ft
	6DSV6D0000-0F0250	6 F, 6 connectors (6 LC UPC), ALTOS gel-free single-armor, double-jacket cable, 25-in (2 mm) leg, 250 ft
1030215	6DSV6D0000-0F0500	6 F, 6 connectors (6 LC UPC), ALTOS gel-free single-armor, double-jacket cable, 25-in (2 mm) leg, 500 ft
1020868	6DSV6D0000-0F0750	6 F, 6 connectors (6 LC UPC), ALTOS gel-free single-armor, double-jacket cable, 25-in (2 mm) leg, 750 ft
1020924	6DSV6D0000-0F1000	6 F, 6 connectors (6 LC UPC), ALTOS gel-free single-armor, double-jacket cable, 25-in (2 mm) leg, 1,000 ft
1010463	6DSV6D0000-0F1250	6 F, 6 connectors (6 LC UPC), ALTOS gel-free single-armor, double-jacket cable, 25-in (2 mm) leg, 1,250 ft
1020642	6ESE6E0000-0F0100	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 100 ft
	6ESE6E0000-0F0200	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 200 ft
1001289	6ESE6E0000-0F0500	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 500 ft
1033234	6ESE6G0000-0F0100	6 F, 6 connectors (6 SC UPC), ALTOS gel-free armored cable, 25-in (3 mm) leg, 100 ft
1010451	6ESF6A0000-0F0100	6 F, 6 connectors (6 FC APC), ALTOS gel-free armored cable, 25-in (900 µm) leg, 100 ft
1020903	6ESF6B0000-0F0100	6 F, 6 connectors (6 FC UPC), ALTOS gel-free armored cable, 25-in (900 µm) leg, 100 ft
	6ESF6G0000-0F0100	6 F, 6 connectors (6 SC UPC), ALTOS gel-free armored cable, 25-in (900 µm) leg, 100 ft
1010271	6ESQ6A0000-0F0075	6 F, 6 connectors (6 FC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 75 ft
1015096	6ESQ6E0000-0F0075	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 75 ft
1020541	6ESQ6E0000-0F0200	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 200 ft
1014872	6ESV6D0000-0F0250	6 F, 6 connectors (6 SC APC), ALTOS gel-free armored cable, 25-in (2 mm) leg, 250 ft

Straight Cable TV Node Assembly Continued

SAP	Part Number	Product Description (Straight CATV Node Assembly, 8 Connectors)
	8DSV8E0000-0F0200	8 F, 8 connectors (8 SC APC), ALTOS® gel-free single-armor, double-jacket cable, 25-in (2 mm) leg, 200 ft

SAP	Part Number	Product Description (Straight CATV Node Assembly, 12 Connectors)
	CCSQ4G8D00-0F0050	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free cable, 36-in (2 mm) leg, 50 ft
1033324	CCSV8E4N00-0F0100	12 F, 12 connectors (8 SC APC/4 furcated legs), ALTOS gel-free cable, 25-in (2 mm) leg, 100 ft
1020963	CCSV8E4N00-0F0500	12 F, 12 connectors (8 SC APC/4 furcated legs), ALTOS gel-free cable, 25-in (2 mm) leg, 500 ft
1001309	CCSVCE0000-0F0100	12 F, 12 connectors (12 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 100 ft
	CCSVCE0000-0F0500	12 F, 12 connectors (12 SC APC), ALTOS gel-free cable, 25-in (2 mm) leg, 500 ft
1030187	CDSV8C4N00-0F0150	12 F, 12 connectors (8 LC APC/4 furcated legs), ALTOS gel-free armored cable, 25-in (2 mm) leg, 150 ft
	CESQ4G8D00-0F0050	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 50 ft
	CESQ4G8D00-0F0100	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 100 ft
	CESQ4G8D00-0F0150	12 F, 12 connectors (4 SC UPC/8 LC UPC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 150 ft
	CESQCE0000-0F0100	12 F, 12 connectors (12 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 100 ft
	CESQCE0000-0F0300	12 F, 12 connectors (12 SC APC), ALTOS gel-free armored cable, 36-in (2 mm) leg, 300 ft



Corning and TVC thank you for your continued business.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA
 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2020 Corning Optical Communications. All rights reserved. CRR-1407-AEN / May 2020