



CORNING

Quick Connect Program: In-Region Inventory

EDGE™ Uniboot Jumpers Ship Within 48 Hours of Order Receipt Qualifying Jumpers


Description	Connector Code	Part Number	Lead Time	
			< 500 pce	> 500 pce
LC Uniboot/LC Uniboot 2.0 mm DFX® 250 Riser	OS2	787802GD120XXXM (1-10M)	2 days	10 days
	OS2	787802GD120XXXM (15-50M)	2 days	10 days
	OM3	797902TD120XXXM (1-10M)	2 days	10 days
	OM4	797902QD120XXXM (1-10M)	2 days	10 days
	OM4	797902QD120XXXM (15-50M)	2 days	10 days
	OM4	797902QD120XXXM-GR (1-5M)	2 days	10 days
	OM4	797902QD120XXXM-RD (1-5M)	2 days	10 days
	OM4	797902QD120XXXM-YL (1-5M)	2 days	10 days

No minimum order quantity! 15-50M lengths are only available in increments of 5M.

EDGE™ Uniboot Jumpers

EDGE Uniboot Jumpers allow for the quick-and-easy conversion from a TIA-568 A-B polarity to a TIA-568 A-A polarity without exposing the fibers or needing any tools. This jumper comes with a straight-through polarity from the factory, but you can convert it to a flipped jumper. This uniboot design allows one cable to carry both fibers, reducing the jumper bulk when routing.

EDGE Uniboot Jumpers are manufactured with Corning® CleanAdvantage™ Technology with Optimized Dust Caps, eliminating the need for scoping and cleaning prior to initial field connection.



Reverse Polarity Uniboot Duplex Jumpers | Photos REN6462 and REN6461



Click or scan here to
contact your preferred
distributor nearest you!