

Rotor/Adapter Selection Guide for Falcon® Tubes

FALCON®

A Corning Brand

Centrifuge	Rotor Name	Rotor Type*	Adapter for Falcon® 15 ml Conical Tube	Adapter for Falcon 50 ml Conical Tube
Beckman Coulter, Inc.				
GS-15/R	S4180	SW	361230	361234
	C0650	FA	—	Dedicated 50 ml rotor
	C1015	FA	Dedicated 15 ml rotor	—
TJ-6/R	TH-4	SW	339276	339273
			359487, aerosol, set of 2 358991, aerosol, set of 4	359488, aerosol, set of 2 358992, aerosol, set of 4
GS-6/R/K/KR	GH-3.8	SW	359151, set of 4	359154, set of 4
			359472, set of 2	359475, set of 2
			359487, aerosol, set of 2	359488, aerosol, set of 2
			358991, aerosol, set of 4	358992, aerosol, set of 4
Avanti 30	C0650	FA	—	Dedicated 50 ml rotor
	C1015	FA	Dedicated 15 ml rotor	—
J6 Large Cap.	JS-3.0, JS-4.0, JS-4.2, JS-5.2	SW	359151, set of 4 359472, set of 2	345386
J2 Series or Avanti J-25	JS-7.5	SW	356964, 4-place adapter	356966, 1-place adapter 362213 (set of buckets), 3-place
			359151, set of 4 359472, set of 2 359487, aerosol, set of 2 358991, aerosol, set of 4	359154, set of 4 359475, set of 2 359488, aerosol, set of 2 358992, aerosol, set of 4
	JA-10, JLA-10.500	FA	356960, 4-place adapter	356965, 1-place adapter
			—	Dedicated 50 ml rotor
			356964, 4-place adapter	356966, 1-place adapter
	JA-14	FA	356964, 4-place adapter	356966, 1-place adapter
	JA-18	FA	356962, 1 tube per adapter	356963, 1 tube per adapter
Sorvall, Inc.				
TC-6	H-400	SW	78033	78035
GLC-2B/3 or	M	FA	03667	—
RC-3	SP/X	FA	00363	None required
	HL-4 w/omnicarrier	SW	00565	00648
	HL-4 w/carrier 00624	SW	—	00630
	HL-4 w/carrier 00634	SW	00363	—
RT-6000B/D or T-6000B/D	A-384	FA	None required	—
	A-500	FA	00363	None required
	A/S-400	FA	11148	None required
	H-1000B	SW	00884 or 11018 with 11152	00438 or 11148 with 11152
RT-7	RTH-250	SW	00884 or 11018 with 11152	00438 or 11148 with 11152
	RTH-750	SW	00447	00436-3 places or 00445-5 places
	SL-50T	FA	00402	—
RC-3B/C or	LA/S-400	FA	11148	None required
RC-3B/C Plus	H-2000B	SW	00884 or 11018 with 11152	00438 or 11148 with 11152
	HG-4L, H-4000, H-6000A	SW	00892	00436-3 places or 00445-5 places
	—	—	—	—
Super T-21	SL-50T, SL-50RT	FA	00402	—
	SL-250T	FA	00456	03072
	STH-750	SW	00447	00436-3 places or 00445-5 places
RC-5B/C or	GSA, SLA-1000, SLA-1500	FA	00456	03072
RC-5BC/Plus or	SLA-600TC	FA	74232	None required
RC-24 or	GS-3, SLA-3000	FA	00456 and 00614	00614 and 03072
RC-26	SH-3000	SW	00447	00436-3 places or 00445-5 places
	HS-4 w/carrier 00479	SW	00456	03072
	HS-4 w/carrier 00481	SW	None required	None required
	HS-4 w/carrier 00480	SW	—	00363
RC-28S	SL-250T	FA	00456	03072
	F-16/250	FA	00456	03072

*SW: Swinging bucket; FA: Fixed angle

Corning acquired the Falcon® brand.
For information, visit www.corning.com/discoverylabware.

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks.
Corning Incorporated, One Riverfront Plaza, Corning, NY 14831-0001

CORNING

Corning Incorporated
Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences