



Corning Cable Systems Connector Compatibility Chart

Part Number	Description	SRP	Crimp Tool	3 mm Crimp Ring/Boot Color Part Numbers	1.6/2.0 mm Crimp Ring/Boot Color Part Numbers	900 µm Boot Color & Part Number
95-050-44-BP	ST Compatible (plastic), epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack	006-355	3201031-01	95-400-09-BP3	95-400-09-BP26	95-400-08-BP9A Black 95-400-08-BP9B Beige 95-400-08-BP9K Blue 95-400-08-BP9N Gray 95-400-08-BP9C*** Green 95-400-08-BP9G Red 95-400-08-BP9R White 95-400-08-BP9W Yellow 95-400-08-BP9Y
95-100-44-BP	ST Compatible (plastic), epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack					
95-250-06-BP	ST Compatible (plastic), epoxy and polish, single-mode, ceramic ferrule, bulk pack					
95-051-49-BP	ST Compatible (metal), epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack					
95-101-49-BP	ST Compatible (metal), epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack					
95-251-49-BP	ST Compatible (metal), epoxy and polish, single-mode, ceramic ferrule, bulk pack					
95-050-10-BP	FC Connector, epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack					
95-100-10-BP	FC Connector, epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack					
95-250-10-BP	FC Connector, epoxy and polish, single-mode, ceramic ferrule, bulk pack					
95-211-10-BP	FC Connector, epoxy and polish, single-mode APC, ceramic ferrule, bulk pack					
95-252-10-BP	FC Connector, epoxy and polish, single-mode, tuned ceramic ferrule, bulk pack					
95-050-48-BP	SC Connector, epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack	006-355	3201031-01	95-400-09-BP3	95-400-09-BP26	95-400-08-BP9A Black 95-400-08-BP9B Beige 95-400-08-BP9K Blue 95-400-08-BP9N Gray 95-400-08-BP9C*** Green 95-400-08-BP9G Red 95-400-08-BP9R White 95-400-08-BP9W Yellow 95-400-08-BP9Y
95-100-48-BP	SC Connector, epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack					
95-250-08-BP	SC Connector, epoxy and polish, single-mode, ceramic ferrule, bulk pack					
95-211-08-BP	SC Connector, epoxy and polish, single-mode APC, ceramic ferrule, bulk pack					
95-252-08-BP	SC Connector, epoxy and polish, single-mode, tuned ceramic ferrule, bulk pack					
95-050-LC-BP	LC Connector, epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack	006-327	For 3mm 3201032-01 For 1.6/2.0mm 3201039-01	95-400-12-BP3	95-400-12-BP26-S	95-400-11-BP9A Black 95-400-11-BP9B Beige 95-400-11-BP9K Blue 95-400-11-BP9N Gray 95-400-11-BP9C*** Green 95-400-11-BP9G Red 95-400-11-BP9R White 95-400-11-BP9W Yellow 95-400-11-BP9Y
95-100-LC-BP	LC Connector, epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack					
95-250-LC-BP	LC Connector, epoxy and polish, single-mode, ceramic ferrule, bulk pack					
95-252-LC-BP	LC Connector, epoxy and polish, single-mode, tuned ceramic ferrule, bulk pack					
95-211-LC-BP	LC Connector, epoxy and polish, single-mode APC, ceramic ferrule, bulk pack					
MT-RJ Part Number	Description	SRP	Crimp Tool	3 mm Crimp Ring/Boot Color Part Numbers	1.6/2.0 mm Crimp Ring/Boot Color Part Numbers	Pin Keeper Assembly
91-050-97-BP	MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, bulk pack	006-306	3201033-01	95-400-28-BP3	95-400-28-BP6	95-400-25-RJMM 95-400-25-RJSM
91-050-97-BP-KG***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, green keying					
91-050-97-BP-KN***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, blue keying					
91-050-97-BP-KR***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, red keying					
91-050-97-BP-KY***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, yellow keying					
91-100-97-BP	MT-RJ Connector, epoxy and polish, multimode (62.5 µm), without pins, bulk pack					
91-200-97-BP	MT-RJ Connector, epoxy and polish, single-mode (50µm), without pins, bulk pack					



*Please note the 3mm crimp band is designed for use with 2-fiber ribbon cable, not 3mm zipcord cable. **Please note the MinZip crimp band is designed for use only with 700 µm buffered fiber zipcord, not 900 µm. *** Please note that part numbers marked *** are NOT part of the 24-Hour Ship Program. To order single pack with entire solution replace BP with SP when ordering. Single Pack not included on MT-RJ.

Corning Cable Systems Connector Compatibility Chart

94-112-MM-MTBP	MTP 12 Fiber, multimode ferrule, bulk pack
94-212-SM-MTBP	MTP 12 Fiber, single-mode, ferrule, bulk pack
94-252-SME-MTBP	MTP 12 Fiber, single-mode elite ferrule, bulk pack
94-115-30-BPRB	MTP female multimode, beige kit, bare ribbon
94-115-33-BPRB	MTP-E female, mustard kit, bare ribbon
94-115-34-BPRB	MTP male multimode, beige kit, bare ribbon
94-115-37-BPRB	MTP-E male, mustard kit, bare ribbon
94-115-39-BPRB	MTP male multimode, aqua kit, bare ribbon
94-115-40-BPDC	MTP female multimode, beige kit, with DC Boot
94-115-41-BPDC	MTP female multimode, black kit, with DC Boot
94-115-42-BPDC	MTP female single-mode, green kit, with DC Boot
94-115-44-BPDC	MTP male multimode, beige kit, with DC Boot
94-115-46-BPDC	MTP male single-mode, green kit, with DC Boot
94-115-48-BPDC	MTP female multimode, aqua kit, with DC Boot
94-115-49-BPDC	MTP male multimode, aqua kit, with DC Boot
94-115-20-BPJB	MTP female multimode, beige kit, Jacket Boot
94-115-21-BPJB	MTP female multimode, black kit, Jacket Boot
94-115-22-BPJB	MTP female single-mode, green kit, Jacket Boot
94-115-23-BPJB	MTP-E male, mustard kit, Jacket Boot
94-115-24-BPJB	MTP male multimode, beige kit, Jacket Boot
94-115-25-BPJB	MTP male multimode, black kit, Jacket Boot
94-115-26-BPJB	MTP male single-mode, green kit, Jacket Boot
94-115-27-BPJB	MTP-E male, mustard kit, Jacket Boot
94-115-28-BPJB	MTP female multimode, aqua kit, Jacket Boot
94-115-29-BPJB	MTP male multimode, aqua kit, Jacket Boot
2104455-01	Tool - Housing Removal, MTP
2104488-01	Tool - Ribbonizer, MTP Termination
3201037-01	Crimp Tool - MTP USC Data Center Cable
3201038-01	Crimp Tool - MTP USC Jacketed Ribbon
95-400-03-BP	Clip, SC Duplex, Corning
TRIGGER-BP-D	Anti-Snag/Trigger, Duplex
TRIGGER-BP-S	Anti-Snag/Trigger, Simplex