

Corning® Gosselin™ Round HDPE Storage Bottles

High density polyethylene bottles with wide neck

CORNING

- ▶ HDPE storage bottles are easier to handle and are ideal for sampling and storage.
- ▶ HDPE resin is lightweight and break-resistant
- ▶ Bottles are leak-proof

Key Features

- ▶ Good for storage of liquid, semi-liquid, and solid forms
- ▶ Available in six sizes: 50 mL, 100 mL, 150 mL, 250 mL, 500 mL, and 1L
- ▶ Large neck opening provides easier access for liquid transfer
- ▶ Sterile
- ▶ Raw materials are food contact compliant



Ordering Information

Corning® Gosselin™ Round HDPE Storage Bottles

Cat. No.	Description	Qty/Cs
LR50A-18	50 mL, 27 mm red screw cap, sterile	600
LR100-12	100 mL, 37 mm red screw cap, sterile	335
LR150A-14	150 mL, 37 mm red screw cap with natural seal, sterile	250
LR250-09	250 mL, 37 mm red screw cap, sterile	145
LR500-04	500 mL, 58 mm red screw cap, sterile	140
LR1000-08	1L, 58 mm red screw cap, sterile	68
LR2000-03	2L, 57 mm red screw cap, sterile	25

For more specific information on claims, visit the Certificates page at www.corning.com/lifesciences.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110. Outside the United States, call +1.978.442.2200 or contact your local Corning sales office.

CORNING

Corning Incorporated
Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

ASIA/PACIFIC
Australia/New Zealand
t 61 427286832

China
t 86 21 3338 4338
f 86 21 3338 4300

India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291

Korea
t 82 2-796-9500
f 82 2-796-9300

Singapore
t 65 6572-9740
f 65 6735-2913

Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE
CSEurope@corning.com

France
t 0800 916 882
f 0800 918 636

Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 020 655 79 28
f 020 659 76 73

United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries
t +31 (0) 206 59 60 51
f +31 (0) 206 59 76 73

LATIN AMERICA
grupoLA@corning.com

Brasil
t 55 (11) 3089-7400

Mexico
t (52-81) 8158-8400