


Everon® Copper Datacom

CORNING

VOL Footprint V250S & E250F Shielded Cat.6/Class E, Southern Europe



1 Cables	2 Jacks	3 Panels	4 Faceplates and Outlets	5 Patch Cords
 <p>CCXDDA-D0047-C001-L6 Cat.6 FTP LSZH™, 4-Pairs, 23 AWG, Dca, blue, 500 m</p> <p>CCXERA-BC047-C001-L6 Cat.6 UFTP LSZH, 4-Pairs, 23 AWG, Cca, blue, 500 m</p>	 <p>XF500006010 RJ45 Cat.6 STP Jack, HW, white (bag of 8), V250S, VOLOCK6SH8</p> <p>XF500006028 RJ45 Cat.6 STP Jack, HW, white (bulk pack of 480), V250S, VOLOCK6SHV</p>	 <p>MAXCSV-02408-C001 Black Patch Panel, 24 ports, 1U</p> <p>MAXCSV-02400-C001 Silver Patch Panel, 24 ports, 1U</p> <p>MAXCSV-02401-C001 White Patch Panel, 24 ports, 1U</p>	 <p>UAXCSE-V0101-C031-BP 22.5 x 45 mm Inclined Adapter for one jack</p> <p>UAXCSE-V0101-C,030-BP 45 x 45 mm Inclined Adapter for one jack</p> <p>UAXCSE-V0201-C030-BP 45 x 45 mm Inclined Adapter for two jacks</p> <p>CAXCSE-00101-C031-BP 45 x 45 mm Faceplate for one adapter</p> <p>CAXCSE-00101-C030-BP 22.5 x 45 mm Blank cover</p>	 <p>CCAEBG-D1002-A005-C0 Cat.6 SSTP LSZH, grey, 0.5 m</p> <p>CCAEBG-D1002-A010-C0 Cat.6 SSTP LSZH, grey, 1 m</p> <p>CCAEBG-D1002-A020-C0 Cat.6 SSTP LSZH, grey, 2 m</p> <p>CCAEBG-D1002-A030-C0 Cat.6 SSTP LSZH, grey, 3 m</p> <p>CCAEBG-D1002-A050-C0 Cat.6 SSTP LSZH, grey, 5 m</p> <p>CCAEBG-D1002-A100-C0 Cat.6 SSTP LSZH, grey, 10 m</p> <p>Additional lengths and colours are available. Please consult your local Corning representative or alternatively Corning Customer Care at 00800-2676-4641 or email cc.emea@corning.com.</p>
 <p>UU009175389 Cat.6 FUTP LSZH, 4-Pairs, 24 AWG, B2ca, green, 500 m</p> <p>UU009120245 Cat.6 FUTP LSZH, 4-Pairs, 24 AWG, Cca, green, 500 m</p>	 <p>UU001520574 RJ45 Cat.6 FTP Jack, PL, white (bag of 8), E250FWH, OCK6-F8</p> <p>UU001520582 RJ45 Cat.6 FTP Jack, PL, white (bulk pack of 480), E250FWH, OCK6-FV</p>	 <p>UU001622909 Black Patch Panel, 48 ports, 2U VOL-PPCBF48K</p> <p>UU001622933 Silver Patch Panel, 48 ports, 2U VOL-PPCBF48K</p>		