










Everon® Copper Datacom

CORNING

VOL Footprint V250U & E250U Unshielded Cat.6/Class E, PVC, Middle East



1 Cables	2 Jacks	3 Panels	4 Faceplates and Outlets	5 Patch Cords
 <p>DE010024334 Cat.6 UUTP PVC, 4-Pairs, 24 AWG, Eca, green, 305 m</p>	 <p>XF500006432 RJ45 Cat.6 UTP Jack, HW, white (bag of 8), V250U, VOL-OCK6-UH8</p> <p>XF500006424 RJ45 Cat.6 UTP Jack, white (bulk pack of 480), V250U, VOL-OCK6-UHV</p>	 <p>MAXCSV-02408-C001 Black Patch Panel, 24 ports, 1U</p> <p>MAXCSV-02400-C001 Silver Patch Panel, 24 ports, 1U</p> <p>MAXCSV-02401-C001 White Patch Panel, 24 ports, 1U</p>	 <p>XF003849205 Single-Gang UK Faceplate, 86 x 86 mm, one jack</p> <p>XF003849213 Single-Gang UK Faceplate, 86 x 86 mm, two jacks</p>	 <p>CCAVNE-D1002-A005-C0 Cat.6 UTP PVC, grey, 0.5 m</p> <p>CCAVNE-D1002-A010-C0 Cat.6 UTP PVC, grey, 1 m</p> <p>CCAVNE-D1002-A020-C0 Cat.6 UTP PVC, grey, 2 m</p> <p>CCAVNE-D1002-A030-C0 Cat.6 UTP PVC, grey, 3 m</p> <p>CCAVNE-D1002-A050-C0 Cat.6 UTP PVC, grey, 5 m</p> <p>CCAVNE-D1002-A100-C0 Cat.6 UTP PVC grey, 10 m</p> <p>Additional lengths and colours are available. Please consult your local Corning representative or alternatively Corning Customer Care at 00800-2676-4641 or email cc.emea@corning.com.</p>
 <p>XE005319605 Cat.6 UUTP PVC, 4-Pairs, 24 AWG, Eca, grey, 305 m</p>	 <p>FQ100031258 RJ45 Cat.6 UTP Jack, PL, white (bag of 8), E250U, OCK6U-8</p> <p>FQ100031241 RJ45 Cat.6 UTP Jack, white (bulk pack of 480), E250U, OCK6U-V</p>	 <p>UU001622909 Black Patch Panel, 48 ports, 2U VOL-PPCBF48K</p> <p>UU001622933 Silver Patch Panel, 48 ports, 2U VOL-PPCBF48K</p>		