











Everon® Copper Datacom

CORNING

VOL Footprint V500S & E500S Shielded Cat.6_A/Class EA, UK



1 Cables	2 Jacks	3 Panels	4 Faceplates and Outlets	5 Patch Cords
 <p>CCXEDB-DB047-C001-L7 Cat.6_A SFTP LSZH™, 4-Pairs, 23 AWG, B2ca, blue, 1,000 m</p> <p>CCXEDB-DC047-C001-L6 Cat.6_A SFTP LSZH, 4-Pairs, 23 AWG, Cca, blue, 500 m</p> <p>CCXEDA-DC047-C001-L6 Cat.6_A FFTP LSZH, 4-Pairs, 23 AWG, Cca, blue, 500 m</p>	 <p>XF500003553 RJ45 Cat.6_A STP Jack, silver (bag of 8), V500S, VOL-OCK6A-SN8</p> <p>XF500003546 RJ45 Cat.6_A STP Jack, silver (bulk pack of 480), V500S, VOL-OCK6A-SNV</p>	 <p>MAXCSV-02408-C001 Black Patch Panel, 24 ports, 1U</p> <p>MAXCSV-02400-C001 Silver Patch Panel, 24 ports, 1U</p> <p>MAXCSV-02401-C001 White Patch Panel, 24 ports, 1U</p>	 <p>UAXCSE-V0101-C020-BP 38 x 25 mm Inclined LJ6C Adapter</p> <p>CAXCSE-00101-C021-BP 86 x 86 mm Single LJ6C Outlet - 1 Adapter</p> <p>CAXCSE-00201-C021-BP 86 x 86 mm Single LJ6C Outlet - 2 Adapters</p> <p>CAXCSE-00401-C021-BP 146 x 86 mm Double LJ6C Outlet - 4 Adapters</p>	 <p>CCAAGB-G1002-A005-C0 Cat.6_A SFTP LSZH, grey, 0.5 m</p> <p>CCAAGB-G1002-A010-C0 Cat.6_A SFTP LSZH, grey, 1 m</p> <p>CCAAGB-G1002-A020-C0 Cat.6_A SFTP LSZH, grey, 2 m</p> <p>CCAAGB-G1002-A030-C0 Cat.6_A SFTP LSZH, grey, 3 m</p> <p>CCAAGB-G1002-A050-C0 Cat.6_A SFTP LSZH, grey, 5 m</p> <p>CCAAGB-G1002-A100-C0 Cat.6_A SFTP LSZH, grey, 10 m</p> <p>Additional lengths and colours are available. Please consult your local Corning representative or alternatively Corning Customer Care at 00800-2676-4641 or email cc.emea@corning.com.</p>
 <p>UU009175728 Cat.6_A FUTP LSZH, 4-Pairs, 24 AWG, B2ca, green, 500 m</p> <p>UU009175736 Cat.6_A FUTP LSZH, 4-Pairs, 24 AWG, Cca, green, 500 m</p>	 <p>DE010022734 RJ45 Cat.6_A STP Jack, silver (bag of 8), E500S, OCK6AS-E8</p> <p>DE010022742 RJ45 Cat.6_A STP Jack, silver (bulk pack of 480), E500S, OCK6AS-EV</p>	 <p>UU001622909 Black Patch Panel, 48 ports, 2U VOL-PPCBF48K</p> <p>UU001622933 Silver Patch Panel, 48 ports, 2U VOL-PPCBF48K</p>	 <p>UAXCSE-V0101-C010-BP 50 x 25 mm Inclined EUROMOD Adapter</p> <p>CAXCSE-00201-C011-BP 86 x 86 mm EUROMOD Outlet - 2 Adapters</p> <p>CAXCSE-00401-C011-BP 146 x 86 mm EUROMOD Outlet - 4 Adapters</p> <p>CAXCSE-00001-C001 86 x 86 mm Surface mounting box. For use with LJ6C and EUROMOD Outlets</p>	