## New!

### CORNING

# Simplify Single Cell Sample Prep

with new Corning<sup>®</sup> Cell Strainers



## New Corning<sup>®</sup> Cell Strainers Fit All Major Brands of 50 mL Conical Tubes

Corning<sup>®</sup> Cell Strainers are ready-to-use devices for rapidly isolating primary cells and making uniform single-cell suspensions. You can use these versatile devices to prepare:

- Samples for flow cytometry
- Single cell suspensions of blood cells
- Specimens for primary cell cultures and immunogens
- Primary cells from tissue

You can also use them to:

- Pre-filter solutions containing particulates >40 μm
- Clean cell suspensions prior to sub-culturing, counting, analysis, or freezing

Corning Cell Strainers feature:

- $\blacktriangleright$  Strong nylon mesh with 40, 70 or 100  $\mu m$  pores for optimal performance in a variety of applications
- Noncytotoxic, sterilized by gamma irradiation
- Individually packed in easy to open bags
- Color-coded polypropylene frames
- Grip area for sterile handling with forceps

#### To request a product sample, go to www.corning.com/lifesciences/cellstrainer

See reverse side for ordering information.









#### **Ordering Information**

#### Corning<sup>®</sup> Cell Strainers

Cat. No.	Pore Size	Color	Qty/Pk	Qty/Cs	
431750	40 µm	Blue	1	50	
431751	70 µm	White	1	50	
431752	100 µm	Yellow	1	50	

#### **Corning 50 mL Centrifuge Tubes**

Cat. No.	Material	Cap Style	Max. RCF	Qty/Pk	Qty/Cs
430290	PP High Clarity	Plug Seal	15,500	25/Rack	500
430291	PP High Clarity	Plug Seal	15,500	25/Sleeve	500
430304	PET	Plug Seal	3,600	25/Rack	500
430828	PP	CentriStar™	17,000	25/Rack	500
430829	PP	CentriStar	17,000	25/Sleeve	500
4558	PP	CentriStar	17,000	25/Universal Rack	300
4365	Foam Centrifuge Tube Rack, 50 mL			-	20
4366	Foam Universal Centrifuge Tube Rack, 15/50 mL			-	20

#### Corning Self-Standing 50 mL Centrifuge Tubes

Cat. No.	Material	Cap Style	Max. RCF	Qty/Pk	Qty/Cs
430897	PP	Plug Seal	3,000	25/Sleeve	500
430921	PP	CentriStar	3,000	25/Sleeve	500

#### Falcon<sup>®</sup> 50 mL Centrifuge Tubes

Cat. No.	Material	Cap Style	Max. RCF	Qty/Pk	Qty/Cs
352070	PP	Flat top, screw cap	16,000	25/Sleeve	500
352098	PP	Flat top, screw cap	16,000	25/Rack	500

#### **Corning Incorporated** *Life Sciences*

836 North St. Building 300, Suite 3401 Tewksbury, MA 01876 t 800.492.1110 t 978.442.2200 f 978.442.2476

www.corning.com/ lifesciences Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures.

For additional product or technical information, please visit **www.corning.com/ lifesciences** or call 800.492.1110. Customers outside the United States, please call +1.978.442.2200 or contact your local Corning sales office.

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks. All other trademarks in this document are the property of their respective owners.

**PYREX**<sup>®</sup>