



Keystone Footprint xs500S Shielded Cat.6_A/Class EA, UK



1Cables	2Jacks	3Panels	4Faceplates and Outlets	5Patch Cords
 CCXEDB-DB047-C001-L7 Cat.6_A SFTP LSZH™, 4-Pairs, 23 AWG, B2ca, blue, 1,000 m CCXEDB-DC047-C001-L6 Cat.6_A SFTP LSZH, 4-Pairs, 23 AWG, Cca, blue, 500 m CCXEDA-DC047-C001-L6 Cat.6_A FFTP LSZH, 4-Pairs, 23 AWG, Cca, blue, 500 m	 CAXXSM-00104-C001 Everon Copper Datacom xs500 Keystone Cat.6_A/Class EA Copper Jack with dust cap (1x Keystone) Alternative: CAXXSM-00104-C011-BP Bulk pack of 24	 KAXCSV-02408-C001 Black Patch Panel, 24 ports, 1U KAXCSV-02400-C001 Silver Patch Panel, 24 ports, 1U KAXCSV-02401-C001 White Patch Panel, 24 ports, 1U	 UAXCSE-V0101-C020-BP 38 x 25 mm Inclined LJ6C Adapter CAXCSE-00101-C021-BP 86 x 86 mm Single LJ6C Outlet - 1 Adapter CAXCSE-00201-C021-BP 86 x 86 mm Single LJ6C Outlet - 2 Adapters CAXCSE-00401-C021-BP 146 x 86 mm Double LJ6C Outlet - 4 Adapters	 CCAAGB-G1002-A005-C0 Cat.6_A SFTP LSZH, grey, 0.5 m CCAAGB-G1002-A010-C0 Cat.6_A SFTP LSZH, grey, 1 m CCAAGB-G1002-A020-C0 Cat.6_A SFTP LSZH, grey, 2 m CCAAGB-G1002-A030-C0 Cat.6_A SFTP LSZH, grey, 3 m CCAAGB-G1002-A050-C0 Cat.6_A SFTP LSZH, grey, 5 m CCAAGB-G1002-A100-C0 Cat.6_A SFTP LSZH, grey, 10 m
 UU009175728 Cat.6_A FUTP LSZH, 4-Pairs, 24 AWG, B2ca, green, 500 m UU009175736 Cat.6_A FUTP LSZH, 4-Pairs, 24 AWG, Cca, green, 500 m	 Consumables: CAXCSN-00000-C011 Copper Conducting Tape	 UU009535251E Silver High-Density Patch Panel, 48 ports, 1U	 UAXCSE-V0101-C010-BP 50 x 25 mm Inclined EUROMOD Adapter CAXCSE-00201-C011-BP 86 x 86 mm EUROMOD Outlet - 2 Adapters CAXCSE-00401-C011-BP 146 x 86 mm EUROMOD Outlet - 4 Adapters CAXCSE-00001-C001 86 x 86 mm Surface mounting box. For use with LJ6C and EUROMOD Outlets	Additional lengths and colours are available. Please consult your local Corning representative or alternatively Corning Customer Care at 00800-2676-4641 or email cc.emea@corning.com. Recommended Tools: CAXCSN-00000-C008 Comfort Parallel Pliers, metal CAXFSN-00000-C001 Cable Preparation Tool for S/FTP or F/FTP cables