







		Part Number	Description	SRP	Crimp Tool	3mm Crimp Ring	3mm Boot Color and Part Number	1/6/2.0mm Crimp Ring	1.6/2.0mm Boot Color and Part Number	900 µm Boot Color & Part Number
	ST-Plastic	95-050-44-BP	ST Compatible (plastic), epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack							
		95-100-44-BP	ST Compatible (plastic), epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack							
		95-250-06-BP	ST Compatible (plastic), epoxy and polish, single-mode, ceramic ferrule, bulk pack							
	ST-Metal	95-051-49-BP	ST Compatible (metal), epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack	006-355	3201031-01	95-400-09-BP3	Aqua 95-400-32-BP3A Black 95-400-32-BP3B Beige 95-400-32-BP3K Blue 95-400-32-BP3N Gray 95-400-32-BP3C*** Green 95-400-32-BP3G Red 95-400-32-BP3R White 95-400-32-BP3W Yellow 95-400-32-BP3Y	95-400-09-BP26	Aqua 95-400-32-BP2A Black 95-400-32-BP2B Beige 95-400-32-BP2K Blue 95-400-32-BP2N Gray 95-400-32-BP2C*** Green 95-400-32-BP2G Red 95-400-32-BP2R White 95-400-32-BP2W Yellow 95-400-32-BP2Y	Aqua 95-400-08-BP9A Black 95-400-08-BP9B Beige 95-400-08-BP9K Blue 95-400-08-BP9N Gray 95-400-08-BP9C*** Green 95-400-08-BP9G Red 95-400-08-BP9R White 95-400-08-BP9W Yellow 95-400-08-BP9Y
		95-101-49-BP	ST Compatible (metal), epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack							
		95-251-49-BP	ST Compatible (metal), epoxy and polish, single-mode, ceramic ferrule, bulk pack							
	FC	95-050-10-BP	FC Connector, epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack							
		95-100-10-BP	FC Connector, epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack							
		95-250-10-BP	FC Connector, epoxy and polish, single-mode, ceramic ferrule, bulk pack							
		95-211-10-BP	FC Connector, epoxy and polish, single-mode APC, ceramic ferrule, bulk pack							

Connector Type	Part Number	Description	SRP	Crimp Tool	3mm Crimp Ring	3mm Boot Color and Part Number	1/6/2.0mm Crimp Ring	1.6/2.0mm Boot Color and Part Number	900um Boot Color and Part number
	95-050-48-BP	SC Connector, epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack	006-355	3201031-01	95-400-09-BP3	Aqua 95-400-31-BP3A Black 95-400-31-BP3B Beige 95-400-31-BP3K Blue 95-400-31-BP3N Gray 95-400-31-BP3C*** Green 95-400-31-BP3G Red 95-400-31-BP3R White 95-400-31-BP3W Yellow 95-400-31-BP3Y	95-400-09-BP26-S 95-400-09-BP26	Aqua 95-400-31-BP2A Black 95-400-31-BP2B Beige 95-400-31-BP2K Blue 95-400-31-BP2N Gray 95-400-31-BP2C*** Green 95-400-31-BP2G Red 95-400-31-BP2R White 95-400-31-BP2W Yellow 95-400-31-BP2Y	Aqua 95-400-08-BP9A Black 95-400-08-BP9B Beige 95-400-08-BP9K Blue 95-400-08-BP9N Gray 95-400-08-BP9C*** Green 95-400-08-BP9G Red 95-400-08-BP9R White 95-400-08-BP9W Yellow 95-400-08-BP9Y
	95-100-48-BP	SC Connector, epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack							
	95-250-08-BP	SC Connector, epoxy and polish, single-mode, ceramic ferrule, bulk pack							
	95-211-08-BP	SC Connector, epoxy and polish, single-mode APC, ceramic ferrule, bulk pack							

Connector Type	Part Number	Description	SRP	Crimp Tool	3mm Crimp Ring	3mm Boot Color and Part Number	1/6/2.0mm Crimp Ring	1.6/2.0mm Boot Color and Part Number	900um Boot Color and Part Number
	95-050-LC-BP-Z	LC Connector, epoxy and polish, multimode (50 µm), ceramic ferrule, bulk pack	006-327	3201032-01 (3MM) 3201039-01 (2MM)	95-400-12-BP3	Aqua 95-400-11-BP3A Black 95-400-11-BP3B Beige 95-400-11-BP3K Blue 95-400-11-BP3N Gray 95-400-11-BP3C*** Green 95-400-11-BP3G Red 95-400-11-BP3R White 95-400-11-BP3W Yellow 95-400-11-BP3Y	95-400-12-BP26-S 95-400-12-BP26	Aqua 95-400-11-BP2A-Z Black 95-400-11-BP2B-Z Beige 95-400-11-BP2K-Z Blue 95-400-11-BP2N-Z Gray 95-400-11-BP2C-Z*** Green 95-400-11-BP2G-Z Red 95-400-11-BP2R-Z White 95-400-11-BP2W-Z Yellow 95-400-11-BP2Y-Z	Aqua 95-400-11-BP9A-Z Black 95-400-11-BP9B-Z Beige 95-400-11-BP9K-Z Blue 95-400-11-BP9N-Z Gray 95-400-11-BP9C-Z*** Green 95-400-11-BP9G-Z Red 95-400-11-BP9R-Z White 95-400-11-BP9W-Z Yellow 95-400-11-BP9Y-Z
	95-100-LC-BP-Z	LC Connector, epoxy and polish, multimode (62.5 µm), ceramic ferrule, bulk pack							
	95-250-LC-BP-Z	LC Connector, epoxy and polish, single-mode, ceramic ferrule, bulk pack							
	95-252-LC-BP	LC Connector, epoxy and polish, single-mode, tuned ceramic ferrule, bulk pack							
	95-211-LC-BP	LC Connector, epoxy and polish, single-mode APC, ceramic ferrule, bulk pack							

	Part Number	Description	SRP	Crimp Tool	3mm Crimp Ring	3mm Boot Color and Part Number	1.6/2.0 mm Mini-Zip Crimp Ring**	1.6mm Boot Color and Part Number	Pin Keeper Assembly
	91-050-97-BP	MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, bulk pack	006-306	3201033-01	95-400-28-BP3	Aqua 95-400-29-BP3A Black 95-400-29-BP3B Beige 95-400-29-BP3K Blue 95-400-29-BP3N Green 95-400-29-BP3G Red 95-400-29-BP3R White 95-400-29-BP3W Yellow 95-400-29-BP3Y	95-400-28-BP6	Aqua 95-400-29-BP6A Black 95-400-29-BP6B Beige 95-400-29-BP6K Blue 95-400-29-BP6N Green 95-400-29-BP6G Red 95-400-29-BP6R White 95-400-29-BP6W Yellow 95-400-29-BP6Y	95-400-25-RJMM
	91-050-97-BP-KG***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, green keying							
	91-050-97-BP-KN***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, blue keying							
	91-050-97-BP-KR***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, red keying							
	91-050-97-BP-KY***	Keyed MT-RJ Connector, epoxy and polish, multimode (50µm), without pins, yellow keying							
	91-100-97-BP	MT-RJ Connector, epoxy and polish, multimode (62.5 µm), without pins, bulk pack							
	91-200-97-BP	MT-RJ Connector, epoxy and polish, single-mode, without pins, bulk pack							
*Please note the 3mm crimp band is designed for use with 2-fiber ribbon cable, not 3mm zipcord cable. **Please note the MiniZip crimp band is designed for use with 700 µm buffered fiber zipcord, not 900 µm. *** Please note that part numbers marked *** are NOT part of the 24-Hour Ship nly Program. To order single pack with entire solution replace BP with SP when ordering. Single Pack not include d on MT-RJ.									

Trigger / Clips
95-400-03-BP TRIGGER-BP-D TRIGGER-BP-S