

CORNING

Know Your FlexNAP™ System

Do you know the benefits of the Corning FlexNAP™ system? Our FlexNAP system provides the most cost-effective method of deploying optical fiber in distribution networks at speeds significantly faster than traditional field installations. The increased speed of network deployment, along with the reliability of factory testing, offers significant value to you.

Up to 5x Faster

plus 5x reduction in civil traffic/customer disruptions, when compared to traditional field installations.




Reduced Supply Chain/Installation Complexity

Fewer components to manage in the field.



Slimline Overmolds



Reduces product space requirements.

Increased Labor Efficiency

Faster subscriber turn-up using same crew.



Full Preconnectorized

Full Splice

Concentrated Fiber Splice Locations

80% fewer field splice locations and up to 70% fewer splices total, when compared to traditional field deployments.



Widespread Adoption

of homes using OptiTip® technology solutions.

>32M
Homes Passed

2.3M
OptiTip Tethers



Proven Reliability

with 99% of the buried network remaining operational during Hurricane Harvey (2017).



Factory Quality

100%

factory-tested components.



Simple Repairs

Cable repair with standard procedures and practices.

Cable cuts managed similarly to bulk cable deployments.



Plan your deployment

Standard FlexNAP for centralized split architectures

Let's get ready to start your FlexNAP™ design.

1 Pick your cable type

(Aerial is typically a 5 ft tether; Buried is typically a 15 ft tether)

- **Aerial**
RPX® or loose tube
- **Buried**
Toneable RPX or armored loose tube
- **Duct**
Toneable RPX or loose tube

2 Pick your tether locations

- **How many homes do you want to serve per location?**
2, 4, 6, 8, or 12 homes per tether loose tube
4, 8, or 12 homes per tether RPX
- **Do you need one tether or more per location?**
Once you know your tethers, you can move to your terminal selection

3 Make your terminal selection

- **Aerial**
Evolv™ terminal or MDU terminal products
- **Buried or duct**
Evolv terminal or MDU


4 Drop Style Selection

Is your drop terminating inside or outside the house?

- **Outside ONT**
ROC™ drop with home side typically SC APC or pigtail (assume connectorization or splice in field)
- **Inside ONT**
ROC drop to transition housing or indoor/outdoor
ROC drop to indoor ONT


5 Next Steps

Give us a call for product pricing, design support, or cable configuration. Contact 828-901-5000 today!



1

Distribution Cable



RPX® Cable



Loose Tube Cable

2

Tap Point/Tether



Tap



Tether

3

Terminal



Evolv Terminal



MDU

4

Drop Cable



ROC™ Drop Cable



ROC Drop Pigtail

Connect your subscribers

You have subscribers. Now what?

1 Install Cable



2 Install Terminals



3 Install Drops












Plan your deployment

Let's get ready to start your FlexNAP™ design.

- 1 Pick your cable type**
(Aerial is typically a 5 ft tether; Buried is typically a 15 ft tether)
 - **Aerial**
SST-Drop™ or loose tube
 - **Buried**
Toneable SST-Drop or armored loose tube
 - **Duct**
Toneable SST-Drop or loose tube
- 2 Pick your tether locations**
 - **How many homes do you want to serve per location?**
1 or 2 fibers per tether
 - **Do you need one tether or more per location?**
Once you know your tethers, you can move to your terminal selection
- 3 Make your terminal selection**
 - **Aerial**
Evolv™ splitter terminal or MDU terminal products
 - **Buried or duct**
Evolv splitter terminal, or LPT terminal with splitter
- 4 Drop Style Selection**
Is your drop terminating inside or outside the house?
 - **Outside ONT**
ROC™ drop with home side typically SC APC or pigtail (assume connectorization or splice in field)
 - **Inside ONT**
ROC drop to transition housing or indoor/outdoor
ROC drop to indoor ONT
- 5 Next Steps**
Give us a call for product pricing, design support, or cable configuration. Contact 828-901-5000 today!

Single-Fiber FlexNAP for distributed split architectures



1	2	3	4
Distribution Cable	Tap Point/Tether	Terminal	Drop Cable
			
SST Cable	Tap	Evolv Splitter Terminal	ROC™ Drop Cable
			
Loose Tube Cable	Tether	LPT Terminal with Splitter	ROC Drop Pigtail






Connect your subscribers

You have subscribers. Now what?

- 1 Install Cable**

- 2 Install Terminals**

- 3 Install Drops**


	Aerial Pole or Buried		Façade/Pole		
					
	Evolv™ Terminal	Evolv Splitter Terminal	MDU Terminal	Low-Profile Terminal (LPT)	Low-Profile Terminal with Splitters (LPT)
Architecture	Centralized	Distributed	Centralized, home run	Centralized, home run	Distributed
Drop Capacity	2, 4, 6, 8, 12 ports	4, 8 ports	6, 12, 24, 36, 48 fibers	4, 6, 8, 12 fibers	4, 8 fibers
Connector Type	OptiTip® multifiber hardened connector	OptiTap single-fiber hardened connector (female)	OptiTip® multifiber hardened connector	OptiTip multifiber hardened connector	Single-fiber hardened connector
FlexNAP™ System Compatibility	FlexNAP Standard System	FlexNAP Single-Fiber System	FlexNAP Standard System	FlexNAP Standard System	FlexNAP Single-Fiber System
Quick Facts	The standard multipoint terminated with an OptiTip stub is our most popular terminal choice in the OSP for centralized split architectures. Its fully sealed terminal body is suitable for all environments (rated IP-68). Available in three body sizes to accommodate 2/4, 6/8 or 12-fiber options.	The multipoint stubless splitter terminal offers split ratios of 1x4 or 1x8 in the same trusted, sealed terminal. A blue connector cap identifies the input port for fast terminal connection to OptiTap enabled tethers.	The MDU terminal equipped with OptiTip stubs support medium-density multitenant business parks or multidwelling unit buildings. With 24-, 36-, or 48-fiber capacity, these façade-mount terminals are ideal for including in standard SFU deployments in mixed-use neighborhoods and towns. The MDU has an additional slack-management housing and skirt to conceal excess drop cable length.	The standard low-profile terminal equipped with a single OptiTip stub supports small multitenant business parks or multidwelling unit buildings up to 12 units. The LPT offers an additional slack management housing and skirt to conceal excess drop cable length.	The low-profile terminal with splitter allows for a single 1x4 or 1x8 splitter or two 1x4 splitters to service small buildings up to eight units. The terminal utilizes OptiTap input ports that connect to single-fiber FlexNAP tethers directly on poles or via a tether extender for façade mounting.

“Without a doubt, one of the key things that made this project successful from the start was more than just Corning’s industry-leading products; it was their engineering expertise that helped me figure out how to be successful from planning to implementation and now to growth.”

—Mike Bosch, CEO of RG Fiber

“From a project management point of view, working with Centrix™ and FlexNAP™ systems is a dream for scheduling and coordination. We are no longer dependent on splicing contractors once the fiber goes up.”

—Brenden Griswold, Operations Coordinator, OTTC

“Since the subscriber connection is such a simple process, I can easily employ local talent to build out the final piece of the network. I don’t need to find someone outside the community with years of fusion splicing experience to guarantee fast installation and the highest transmission speeds for my customers.”

—Greg Dynek, CEO of Bluestem Fiber

We are here. We understand. We can help.

Ready to configure? Whether you are maintaining your infrastructure to stay ahead of bandwidth demand or building your network from the ground up, you have scores of decisions to make – and every one of them can impact your bottom line. Before exploring specific connectivity products, connect with us for value that extends well beyond our portfolio.

We’d be happy to discuss the details of your broadband vision and can provide you with a cost analysis that compares the speed and cost of deployment for a full-splice, semi-precon, and full-precon deployment in your community.

Learn more at www.corning.com/community-broadband/next-steps

The Corning logo is displayed in white, uppercase letters on a solid blue square background.

CORNING

To learn more about the FlexNap design tool visit:

www.corning.com/flexnap

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019, 2023 Corning Optical Communications. All rights reserved. CRR-1014-AEN / February 2023