

Test Report

CORNING INC.
ONE RIVERFRONT PLAZA, CORNING, N.Y.14831, USA

Report No. : CE/2006/68130B
Date : 2006/07/04
Page : 1 of 4



The following sample(s) was/were submitted and identified by/on behalf of the client as :

Sample Description : CORNING MULTIMODE OPTICAL FIBER
Sample Received : 2006/06/23
Testing Period : 2006/06/23 TO 2006/07/04

=====
Conclusion : The test results of Pb, Cd, Hg, Cr+6, PBB and PBDE for the submitted sample show value below the limits set in the ROHS Directive (2002/95/EC).


Daniel Yeh, M.R. / Operation Manager
Signed for and on behalf of
SGS TAIWAN LTD.

Test Report

CORNING INC.
ONE RIVERFRONT PLAZA, CORNING, N.Y.14831, USA

Report No. : CE/2006/68130B
Date : 2006/07/04
Page : 2 of 4



Test Result(s)

PART NAME NO.1 : TRANSPARENT (UNCOLORED) OPTICAL FIBER

PASS

Test Item (s):	Unit	Method	MDL	Result	Limit of ROHS
				No.1	
PBBs (Polybrominated biphenyls)	---	---	---	---	---
Monobromobiphenyl	%	With reference to USEPA3540C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.	-
Dibromobiphenyl	%		0.0005	N.D.	-
Tribromobiphenyl	%		0.0005	N.D.	-
Tetrabromobiphenyl	%		0.0005	N.D.	-
Pentabromobiphenyl	%		0.0005	N.D.	-
Hexabromobiphenyl	%		0.0005	N.D.	-
Heptabromobiphenyl	%		0.0005	N.D.	-
Octabromobiphenyl	%		0.0005	N.D.	-
Nonabromobiphenyl	%		0.0005	N.D.	-
Decabromobiphenyl	%		0.0005	N.D.	-
Total PBBs (Polybrominated biphenyls)/Sum of above	%		-	N.D.	0.1
PBBEs(PBDEs) (Polybrominated biphenyl ethers)	---	---	---	---	---
Monobromobiphenyl ether	%	With reference to USEPA3540C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.	-
Dibromobiphenyl ether	%		0.0005	N.D.	-
Tribromobiphenyl ether	%		0.0005	N.D.	-
Tetrabromobiphenyl ether	%		0.0005	N.D.	-
Pentabromobiphenyl ether	%		0.0005	N.D.	-
Hexabromobiphenyl ether	%		0.0005	N.D.	-
Heptabromobiphenyl ether	%		0.0005	N.D.	-
Octabromobiphenyl ether	%		0.0005	N.D.	-
Nonabromobiphenyl ether	%		0.0005	N.D.	-
Decabromobiphenyl ether	%		0.0005	N.D.	-
Total PBBEs(PBDEs) (Polybrominated biphenyl ethers)/Sum of above	%		-	N.D.	-
Total of Mono to Nonabrominated biphenyl ether. (Note 4)	%	-	N.D.	0.1	

Test Report

CORNING INC.
ONE RIVERFRONT PLAZA, CORNING, N.Y.14831, USA

Report No. : CE/2006/68130B
Date : 2006/07/04
Page : 3 of 4



PASS


Test Item (s):	Unit	Method	MDL	Result	Limit of ROHS
				No.1	
Chromium VI (Cr+6)	ppm	UV-VIS(US EPA 7196A) after reference to US EPA 3060A.	2	N.D.	1000
Cadmium (Cd)	ppm	ICP-AES after reference to EN 1122, method B:2001 or other acid digestion.	2	N.D.	100
Mercury (Hg)	ppm	ICP-AES after reference to US EPA 3052 or other acid digestion.	2	N.D.	1000
Lead (Pb)	ppm	ICP-AES after reference to US EPA 3050B or other acid digestion.	2	N.D.	1000

- NOTE: (1) N.D. = Not Detected (<MDL)
 (2) ppm = mg/kg
 (3) MDL = Method Detection Limit
 (4) Decabromobiphenyl ether (DecaBDE) in polymeric applications is exempted by Commission Decision of 13 Oct 2005 amending Directive 2002/95/EC notified under document 2005/717/EC.
 (5) PBBEs=PBDEs=Polybrominated Diphenyl Ethers=PBDOs=PBBOs.
 (6) " - " = Not Regulation
 (7) " --- " = Not Applicable

Test Report

CORNING INC.
ONE RIVERFRONT PLAZA, CORNING, N.Y.14831, USA

Report No. : CE/2006/68130B
Date : 2006/07/04
Page : 4 of 4



** End of Report **