CORNING

Behind the Base Understanding the Numbers of Connectivity



Have you ever wondered about the **differences between Base-2, Base-24**, and all the numbers in between? This overview will introduce you to the **basics of cabling solutions** — and where each is most applicable.

Base-2	3
Base-8	4
Base-12	6
Base-16	7

Base-24	8
Optical Transceiver Road map & Structured Cabling	9
How to Plan for Migration/Footer)

Base-2 Backbone





Terminated with splice boxes, breakout boxes, or preterminated low-fiber-count solutions





LC duplex is the dominant interface up to 10G and still widely used to breakout from higherfiber-count transceivers



Links are based on **two-fiber** increments and common in LC duplex or SC duplex connections



Used in LAN environments or entry-level data center applications supporting 10G to 100G applications



SAMPLE LINK **COMPONENTS**















Transceiver with LC Duplex Interface LC Duplex Patch Cord

Fiber Optic Housing with LC Duplex Adapters

Preterminated LC Duplex to LC Duplex Backbone Trunk

Fiber Optic Housing with LC Duplex Adapters

LC Duplex Patch Cord

Transceiver with LC Duplex Interface

Base-8 Backbone



Using **preterminated trunks** and **high-density patch panels** infrastructures

Capable to integrate 8F MPO-12, MPO-16 (one row), 24F MPO-12 DD, SN, MDC, CS, LC duplex



Dominant for 40G supporting 10G to 1.6T applications and is widely believed to be the **most flexible option** to accommodate **future industry trends**

Links are based on **8-fiber** increments, with 8-fiber MPO-MTP° connectors supporting port breakout without changing the installed backbone and full fiber utilization



Allows data centers to migrate to new transceiver technologies with minimal to no change in existing cabling infrastructure



SAMPLE LINK COMPONENTS







and the second s

MPO-8 Trunk

MPO-8 to LC Module

C Duplex

Patch Cord

Option

LC Duplex to VSFF Patch Cord







Transceiver with LC Duplex Interface

terface

MPO-8 Patch Cord MPO-8 Ac

MPO-8 Adapter Panel


3 Trunk MP

BASE-8 is widely believed to be the most flexible and most granular option to accommodate future trends and connectivity needs

Major equipment manufacturers assert **Base-8** and **Base-2** transceiver types will be used for Ethernet transmission ranging from **40G** to **1.6T speed**.



Ethernet Transceiver Shipments by Data Rate, Historical Data and Forecast



Source: Lightcounting High-Speed Ethernet Optics – March 2023

Base-12 Backbone



Trunk cables are used in the network backbone and two-fiber cables are used for connectivity to server, switch, and storage unit ports



Used by small-to-large data centers and MTDCs using duplex transceivers in a high-density infrastructure supporting 10G to 1.6T



Links are based on 12-fiber increments, with 12-fiber MPO/MTP[®] connectors

MDC to LC uniboot patch cords for increased density while maintaining MPO-12 backbone



Provides fast, easy installation with preterminated multifiber solutions and traditional telecom compatibility

Compatibility with 8-fiber transceivers by using conversion modules











MPO-12 Adapter Panel





MPO-12 Adapter Panel





MPO-12 to LC Duplex

Harness



LC Duplex Interface





MPO-LC Module


Preterminated MPO-12 to MPO-12 Backbone Trunk

MPO – LC Module

LC Duplex Patch Cord



Base-16 Backbone





Using preterminated trunks and high-density patch panels, port breakout to lower speeds must be supported with 2-fiber LC duplex or 8-fiber MPO-12 components

Links are based on **16-fiber** increments, with 16-fiber MPO/MTP[®] (one-row) connectors, not typical in MM applications



Suitable for medium to 00

large data centers planning to standardize MPO-16 APC (one-row) connectors (e.g., 400G-SR8), supporting 10G to 1.6T speed



SAMPLE LINK **COMPONENTS**

Transceiver with MPO-16 APC Interface

MPO-16 Patch Cord

MPO-16 Adapter Panel


MPO-16 Trunk

MPO-16 Adapter Panel

MPO-16 Patch Cord Patch Cord

Transceiver with MPO-16 **APC** Interface

Base-24 Backbone





Developed for 100GBASE-SR10 applications (20-fiber MPO-12 DD), however **LC duplex and MPO-8** at the switch are the most common connector interfaces used with **Base-24 backbone**



Links are based on **24-fiber** increments, with 24-fiber MPO/MTP connectors Offers some level of compatibility with existing Base-8 and Base-12



Used in small to medium data centers to help reduce the number of connector pairs on transmission channels, supporting 10G to 100G applications




SAMPLE LINK COMPONENTS

architectures















SR10 Transceiver

MPO-12 DD Patch Cord

MPO-12 Adapter Panel

Preterminated MPO-12 DD MPO-12 A to MPO-12 DD Backbone

010

MPO-12 Adapter Panel MPO

MPO-12 DD Patch Cord

SR10 Transceiver

Trunk

OPTICAL TRANSCEIVER ROAD MAP & STRUCTURED CABLING

Transceiver Speed	10G	25G	40	G	50G	100G			200G			400G						1.6T		
Pluggable Module	SFP	SFP	SFP /	QSFP	SFP / QSFP	SFP / SFP-DD / QSFP / QSFP-DD / OSFP			QSFP / QSFP-DD / SFP-DD			QSFP / QSFP-DD / OSFP				QSFP / QSFP-DD / OSFP				QSFP / QSFP-DD / OSFP / OSFP-XD
SMF	LR	LR	LR4, FR4	PLR4	LR, FR	LR, FR, DR LR4, CWDM4	N/A	PSM4	LR4, FR4, FR, DR	N/A	DR4	LR8, FR8, FR4, LR4-6, LR4-10	2FR4	DR4, DR2, DR4-2	N/A	LR8, FR8	2L42 2FR4, FR4	DR4, DR4-2	2DR4, 2PLR4 8FR, DR8, DR8-2	DR8 DR8-2
MMF	SR	SR	BiDiS, WDM4	SR4, eSR4	SR	BiDi, SWDM4, VR, SR	SR2	SR4	N/A	VR2, SR2	SR4	N/A	N/A	SR4.2, VR4, SR4	SR8	N/A	N/A	VR4.2, SR4.2	SR8, VR8 2VR4, 2SR4	VR8.2 SR8.2
Fibers per transceiver	2	2	2	8	2	2	4 (2×2)	8	2	4 (2x2)	8	2	4 (2×2)	8	16 (16x1)	2	4 (2×2)	8	16 (8x2 or 16x1)	16 (8x2 or 16x1)
Base-2	•	•	•	0	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Base-8	•	•	•	•	•	•	•	•	•		•	•	•	•	•		•	٠	•	•
Base-12	•	•	•	0	•	•	•	0	•	•	0	•	•	0	0	•	•	0	0	0
Base-16	0	0	0	0	0	0	0	0	0	0	0	0	0	0	٠	0	0	0	•	•
Base-24	•	•	•	0	•	•	•	0	0	0	0	0	0	0	0	0	0	0	0	0

• Allow full scalability, 100% fiber utilization and migration

O Scalability and migration complexity in some degree (base conversion components, partial fiber utilization)

O Allow scalability and migration. Limited backward compatibility with existing Base-8 and Base-12 backbones / installations

– Not recommended due to scalability limitations and high complexity



The path to higher speeds will always depend on your unique needs. You may be happy with 40G now but planning to upgrade to 100G four years from now. Or maybe you're working with 400G and have your eyes set on 800G in five years. Migration will always vary based on your timeline and the available technologies in the market. But in most cases, Base-8 will provide the ideal level of flexibility to meet your needs throughout your transition all the way to 1.6T.

Need help choosing the right solution for your data center?

Whether you need help with your current implementation or planning for the future, we can help. Visit **www.corning.com/emea/en/data-centre**

Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, GERMANY +00 800 2676 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea

CORNING

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2022, 2023 Corning Optical Communications. All rights reserved. LAN-3093-A4-BEN / November 2023