



# POLARCOR™ Glass Polarizers

## Product Information

### Specialty Materials



*Corning® Polarcor™ is a high performance glass polarizer, featuring excellent optical performance, compact size and unmatched durability, that meets the most stringent requirements of the telecommunications, aerospace and defense, medical and many other markets.*

Polarcor is a keystone optical element in polarization-dependent isolators, optical modulators, polarimetry systems, ellipsometers, shutters and many other polarization-based devices. Polarcor is characterized by high extinction and low insertion loss throughout the 600 nm to 2300 nm wavelengths. The polarization mechanism (resonant absorption by elongated silver crystals within the glass material) ensures the elimination of stray light, by absorbing the unwanted polarization. Since Polarcor is a solid glass product it is extremely resistant to chemical, physical and thermal damage, while exhibiting excellent optical properties. Polarcor products are Telecordia, Military Spec and ROHS compliant, are radiation resistant and have been qualified for space applications.

#### **Polarcor can be used to:**

- Create or block polarized light
- Reduce glare and suppress reflections
- Enhance contrast of images
- Modulate energy
- Control intensity and color
- Improve signal to noise ratio

#### **Applications:**

- Polarization-dependent optical isolators
- Infrared sensors
- Instrument filters
- Modulators
- Fiber polarizers
- Magnetic anomaly detectors
- Various fiber optic devices

## Reliability

Polarcor has served the telecommunications market since 1984 and has been used in millions of optical isolators without any reported failures.


## Typical Polarcor Performance

The table below shows typical performance for nominal wavelengths of 633 nm – 2100 nm.

$\lambda_{\text{Nominal}}$ (nm)	633	800	900	1060	1310	1480	1550	2100
<b>Polarization Bandwidth (nm)</b>	630 - 700	740 - 860	840 - 960	960 - 1160	1275 - 1345	1460 - 1500	1510 - 1590	2000 - 2100
<b>Contrast Extinction Ratio (dB)</b>	> 10,000:1 > 40	> 10,000:1 > 40	> 10,000:1 > 40	> 10,000:1 > 40	> 100,000:1 > 50	> 100,000:1 > 50	> 100,000:1 > 50	> 10,000:1 > 40
<b>Transmittance (%) Insertion Loss (dB) without AR-Coating</b>	> 76.5 < 1.16	> 84.0 < .76	> 87.0 < 0.60	> 88.5 < 0.53	> 90.5 < 0.43	> 90.5 < 0.43	> 90.5 < 0.43	> 90.5 < 0.43
<b>Transmittance (%) Insertion Loss (dB) for 2 sides AR-Coated</b>	> 83.9 < 0.76	> 91.3 < 0.39	> 94.3 < 0.25	95.7 < 0.19	> 98.5 < 0.06	> 98.5 < 0.06	> 98.5 < 0.06	- -
<b>Refractive Index @ <math>\lambda_{\text{Nominal}}</math></b>	1.5210	1.5161	1.5138	1.5123	1.5088	1.5061	1.5051	1.5020
<b>Reflectance R (%) per each side*</b>	< 0.4	< 0.4	< 0.4	< 0.4	< 0.25	< 0.25	< 0.25	-
<b>Thickness (mm)</b>	0.50	0.50	0.50	0.50	0.50 & 0.20	0.50 & 0.20	0.50, 0.20 & 0.15	0.50
<b>Thickness Tolerances</b>	±0.05 mm for product with 0.5 mm thickness and ±0.03 mm for products with 0.2 mm and 0.15 mm thickness.							

\* This is the measured reflectance of a witness sample at  $0^\circ \pm 5^\circ$  AOI (Angle of Incidence) with randomly polarized light and where the incident media is air. The witness sample is a substrate such as BK7 material coated along with Polarcor™ parts and it is used for spectral and durability tests.

Wavelength Bandwidth (nm)	Polarcor™ W I D E B a n d™	
<b>Polarization Bandwidth (nm)</b>	600 - 1100	1275 - 1635
<b>Contrast Extinction Ratio (dB)</b>	> 10,000:1 > 40	> 100,000:1 > 50
<b>Transmittance (%) Insertion Loss (dB) without AR-Coating</b>	> 60.0 < 2.20	- -
<b>Transmittance (%) Insertion Loss (dB) for 2 sides AR-Coated</b>	> 66.0 < 1.8	> 98.5 < 0.06
<b>Refractive Index @ Wavelength Bandwidth</b>	1.5218 – 1.5107	1.5083 – 1.5034
<b>Reflectance R (%) per each side*</b>	< 1.0	< 0.2
<b>Thickness (mm)</b>	0.50	0.50 & 0.2
<b>Thickness Tolerances (mm)</b>	±0.05 mm for product with 0.5 mm thickness and ±0.03 mm for products with 0.2 mm and 0.15 mm thickness.	



## Typical key specifications for Polarcor™ UltraThin™


$\lambda_{\text{Nominal}}$ (nm)	1060	1310	1550
<b>Polarization Bandwidth (nm)</b>	960 - 1160	1275 - 1345	1510 - 1590
<b>Contrast</b>	> 200:1	> 200:1	> 200:1
<b>Extinction Ratio (dB)</b>	> 23	> 23	> 23
<b>Transmittance (%)</b>	> 88.5	> 88.5	> 88.5
<b>Insertion Loss (dB) without AR-Coating</b>	< 0.53	< 0.53	< 0.53
<b>Thickness (<math>\mu\text{m}</math>)</b>	30 $\pm$ 10	30 $\pm$ 10	30 $\pm$ 10

All Polarcor™ UltraThin™ products are offered without AR-Coating.

Thermal Properties	Value	Unit
Coefficient of Thermal Expansion	65 x 10 <sup>-7</sup>	/°C or /°K
Mechanical Properties		
Young's Modulus	58.6	GPa
Poisson's Ratio	0.21	
Knoop Hardness	480	Kg/mm <sup>2</sup>

## Key Benefits

- Low insertion loss in polarization-dependent isolators
- High isolation
- Performance durability and stability in harsh environments
- Ability to handle high power applications
- Flexible designs:
  - As small as 1.0 mm x 1.0 mm and up to 34 mm x 45 mm for 0.2 mm thickness; up to 34 mm x 74 mm for 0.5 mm thickness (34 mm is parallel to the polarization axis)
  - Square, rectangle, hexagon and round shapes
- With or without anti-reflective coatings
- Variety of Polarization Axis Angles relative to the edge of the part (such as +45°, -45°, +30°, -30°, etc)
- Wavelength ranges from 600 nm to 2300 nm
- Large acceptance angles allow customers greater packaging design flexibility



The graph at the left shows typical reflectance spectrum for Polarcor at nominal wavelengths of 1310 nm and 1550 nm, and for Polarcor™ W I D E Band™.

**Corning Incorporated**  
Technical Materials  
HP-CB-08  
Corning, NY 14831 USA  
Tel: +1 607 974 5746  
Fax: +1 607 974 6718  
Email: thin@corning.com  
Web: www.corning.com

**Corning China Ltd.**  
34<sup>th</sup> Floor, Manulife Tower  
169 Electric Road  
North Point  
Hong Kong  
Tel: 852 2807 2723  
Fax: 852 2807 2152

**Corning (China) Ltd.**  
Shanghai Representative Office  
31/F The Center  
989 Chang Le Road  
Shanghai 200031  
China  
Tel: 86 21 5467 4666  
Fax: 86 21 5407 5899

**Corning Korea Company Ltd.**  
10<sup>th</sup> Floor, Kukje Center Building  
191, Hangang-Ro 2-Ka  
Yongsan-Ku, Seoul, 140-702  
Korea  
Tel: 82 2 796 9500  
Fax: 82 2 796 9300

**Corning International K.K.**  
Akasaka Intercity 6th Floor  
1-11-44 Akasaka, Minato-ku,  
Tokyo, 107-0052  
Japan  
Tel: 81 3 3586 1052  
Fax: 81 3 3587 0906

**Corning International Taiwan Co., Ltd.**  
Room #1203, 12F, No. 205  
Tun Hua North Road  
Taipei, 105, Taiwan  
Taiwan  
Tel: 886 2 2716 0338  
Fax: 886 2 2716 0339

**Corning GmbH-Corning International**  
Abraham-Lincoln Strasse 30  
D65189 Wiesbaden  
Germany  
Tel: 49 611 7366 100  
Fax: 49 611 7366 143