

NEW FROM CORNING

PYREX® Slim Line Storage Bottles

The bottle you have been waiting for!

PYREX®

A Corning Brand

New!



New PYREX Slim Line media storage bottles provide easier handling and more efficient storage of media, biologicals, and other aqueous solutions.

Features

- ▶ Indented gripping zones along the sides of bottle allow easier and safer handling
- ▶ New cap design permits faster opening and closing. The caps are fully compatible with all standard “GL45” (45 mm neck size) Pyrex bottles
- ▶ Widely-spaced knurls (ridges and grooves) provide comfortable and ergonomic cap handling
- ▶ Narrow bottle diameter allows more efficient storage on shelves, refrigerators, autoclaves.
- ▶ Bottles are graduated to their full working volumes
- ▶ Available in four sizes: 125 mL, 250 mL, 500 mL, and 1L

Pyrex Slim Line bottles are made from the same Type 1 Class A (ASTM E-438) borosilicate glass as standard Pyrex media bottles for chemical and heat resistance.

Cat. No.	Description	Capacity (mL)	Approx. O.D. x Height (mm)	Thread Finish	Qty/Cs
1399-125	Storage Bottle	125	55 x 124	GL45	4
1399-250	Storage Bottle	250	66 x 158	GL45	4
1399-500	Storage Bottle	500	78 x 193	GL45	4
1399-1L	Storage Bottle	1000	93 x 253	GL45	4

Related PYREX Glassware Products

1395 PYREX Bottle, Media Storage, Screw Cap



Cat. No.	Description	Capacity (mL)	Thread Finish	Approx. O.D. x Height (mm)	Grad. Range (mL)	Grad. Interval (mL)	Qty/Cs
1395-100	Storage Bottle	100	GL45	56 x 100	40-80	20	10
1395-150	Storage Bottle	150	GL45	50 x 125	62-110	25	10
1395-250	Storage Bottle	250	GL45	70 x 138	50-200	50	10
1395-500	Storage Bottle	500	GL45	86 x 176	100-400	100	10
1395-750	Storage Bottle	750	GL45	95-203	100-600	100	10
1395-1L	Storage Bottle	1000	GL45	101 x 225	100-900	100	10
1395-2L	Storage Bottle	2000	GL45	136 x 262	400-1800	200	10
1395-3X	Storage Bottle	3500	GL45	160 x 295	500-3000	500	10
1395-5L	Storage Bottle	5000	GL45	186 x 335	500-4500	500	1
1395-10L	Storage Bottle	10000	GL45	234 x 410	2000-9000	1000	1

5640 PYREX Flask, Volumetric, Class A, PYREX Standard Taper (⌘) Stopper



Cat. No.	Capacity (mL)	Tol. (± mL)	Approx. O.D. x Height (mm)	⌘ Stopper No.	Qty/Pk	Qty/Cs
5640-50	50	0.05	50 x 151	9	6	12
5640-100	100	0.08	60 x 181	13	6	12
5640-200	200	0.10	74 x 214	13	6	12
5640-250	250	0.12	78 x 252	16	6	12
5640-500	500	0.20	99 x 287	19	6	12
5640-1L	1000	0.30	127 x 346	22	1	6
5640-2L	2000	0.50	180 x 440	27	1	4



3022 PYREX® Cylinder, Single Metric Scale, Graduated, To Contain (TC)

Cat. No.	Capacity (mL)	Grad. Interval (mL)	ASTM Tol. (± mL)	Approx. O.D. x Height (mm)	Qty/Pk	Qty/Cs
3022-25	25	0.2	0.3	18 x 192	1	18
3022-50	50	1.0	0.5	24 x 225	1	18
3022-100	100	1.0	1.0	29 x 254	1	12
3022-250	250	2.0	2.0	39 x 340	1	12
3022-500	500	5.0	4.0	50 x 392	1	8
3022-1L	1000	10.0	6.0	64 x 465	1	1
3022-2L	2000	20.0	12.0	83 x 520	1	1




3024 PYREX Cylinder, Single Metric Scale, Graduated, To Deliver (TD)

Cat. No.	Capacity (mL)	Grad. Interval (mL)	ASTM Tol. (± mL)	Approx. O.D. x Height (mm)	Qty/Pk	Qty/Cs
3024-25	25	0.2	0.3	18 x 192	1	18
3024-50	50	1.0	0.5	24 x 225	1	18
3024-100	100	1.0	1.0	29 x 254	1	12
3024-250	250	2.0	2.0	39 x 340	1	12
3024-500	500	5.0	4.0	50 x 390	1	8
3024-1L	1000	10.0	6.0	64 x 465	1	1
3024-2L	2000	20.0	12.0	83 x 520	1	1
3024-PACK*					Assortment Pack	

*The assortment pack includes one each of the 10 mL, 25 mL, 50 mL, 100 mL, and 250 mL sizes.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.



www.corning.com/lifesciences/solutions

Because it is so fundamental to our world, chemistry plays a role in everyone's lives and touches almost every aspect of our existence in some way. In chemistry, research can take many forms, from synthesizing compounds to building computational models or gathering and analyzing data using a wide variety of instruments and techniques.

Corning has been a valued supplier to chemists for nearly a century since the introduction of PYREX® low expansion borosilicate glass that is the quality standard for labware because of its clarity, strength, heat and chemical resistance.

For additional product or technical information, please visit www.corning.com/lifesciences or call 800.492.1110. Customers outside the United States, please call +1.978.442.2200 or contact your local Corning sales office.

Corning Incorporated
Life Sciences
836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476
www.corning.com/lifesciences

Worldwide Support Offices

ASIA/PACIFIC

Australia/New Zealand
t 0402-794-347

China
t 86 21 2215 2888
f 86 21 6215 2988

India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291

Korea
t 82 2-796-9500
f 82 2-796-9300

Singapore
t 65 6733-6511
f 65 6861-2913

Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France
t 0800 916 882
f 0800 918 636

Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries
t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA
Brasil
t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico
t (52-81) 8158-8400
f (52-81) 8313-8589

CORNING | **FALCON** | **AXYGEN** | **GOSELIN** | **PYREX**

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks. All other trademarks are the property of their respective owners.