

Glass designation :

BX 15

Code

82516

Color :

Brown

Filter category :

Dark

Application :

**100 % UV absorbing glass suited for general or special purpose
 sunglass lenses**

PHYSICAL PROPERTIES

Density : 2.56 g/cm³
 Linear Exp. Coef. : 90 10⁻⁷ / °C
 Viscosity : Soft. Pt 687 °C
 Ann. Pt 487 °C
 Strain Pt 440 °C

REFRACTIVE INDEX

Line		λ (nm)	Value
F'	Cadmium	480.0	1.52500
F	Hydrogen	486.1	
e	Mercury	546.1	
d	Helium	587.6	
C'	Cadmium	643.8	
C	Hydrogen	656.3	
Abbe Number		ve	
		vd	

TRANSMISSION PROPERTIES (1,9 mm)

VISIBLE 380 - 780 nm

Luminous transmission factor 14.5%
 Transmission category ISO 8980-3 3

ULTRAVIOLET

UV - B tλ(max) 280 - 315 nm < 0.1 %
 t(avg) 280 - 315 nm < 0.1 %
 Solar UV-B transmission factor < 0.1 %

UV - A tλ(max) 315 - 350 nm < 0.1 %
 t(moy) 315 - 380 nm < 0.1 %
 Solar UV-A transmission factor < 0.1 %

BLUE LIGHT 380 - 500 nm
 Blue light transmission factor 4%


TRAFFIC SIGNAL RECOGNITION

ISO 14889 *Pass*
 ANSI Z80-3 *Pass*
 AS 1067.1 *Pass*

COATING & TEMPERING

(See also notes below)

Vacuum coating **YES**
 Chemical tempering **YES**
 Air tempering **YES**



Glass designation :	BX 15	Code	82516
Color :	Brown		
Glass type :	Dark		
Application :	100 % UV absorbing glass suited for general or special purpose sunglasses lenses		

Chemtempering :	Recommended bath and cycle (no preheating nor postcooling) :		
Bath :	Potassium Nitrate	99.5 % (Sodium nitrate 0,5% max)	Time : 16 Hr
	Silicic Acid	0.5 %	θ °C : 420 °C

Air tempering :
Air tempering using conventional processes for standard crown glasses. Minimum lens thickness for normal air tempered lenses is 2 mm.

Coatings :
Vacuum coatings for coloring, antireflexion or mirror are possible.

Compatible Bariums :
This glass can not be used to manufacture fused multifocal lenses.
There is no compatible bariums to be fused with this glass

Properties according to ISO 14889

ISO 14889 Chapter 4.3.1 *Physiological compatibility*

The above glass products are not known to be physiologically incompatible, nor known to create a significant number of allergic reactions, when the lenses made out of these materials are used as intended by the manufacturer

ISO 14889 Chapter 4.3.2 *Flammability*

The above glass products are not flammable, and when tested as described in chapter 5.1 of ISO 14889, there is no continued combustion after withdrawal of the test rod.