

# Corning® Gentest™ Hepatocytes

## Frequently Asked Questions

The logo consists of the word "CORNING" in a white, uppercase, sans-serif font, centered within a solid orange square.

### **How do I obtain human hepatocytes from Corning Life Sciences?**

Register through Corning's HepatoLink® online notification system at [www.corning.com/lifesciences/hepatolink](http://www.corning.com/lifesciences/hepatolink), or contact [hepatocytes@corning.com](mailto:hepatocytes@corning.com).

### **What information is available regarding the human donors?**

The donor information typically available includes: age, gender, race, social, over the counter and prescription drug use, significant medical history, and cause of death. In addition, serologies for a variety of pathogens are available.

### **Are Corning Gentest human hepatocyte products tested for biohazardous agents? Does Corning take any special safety precautions?**

All human hepatocytes are derived from human tissue which is a potentially biohazardous material. Universal Precautions should be used when handling which means the material should be handled as if it were capable of transmitting disease. Due to the need to process and ship fresh hepatocytes quickly, only the donor serologies are available at the time of shipment. For cryopreserved hepatocytes, additional testing using FDA-approved methods and found negative for Human Immunodeficiency Virus (HIV-1/HIV-2), Human T Cell Leukemia Virus (HTLV-1/HTLV-2), Hepatitis B Virus (HBV), Hepatitis C virus (HCV) and Cytomegalovirus (CMV). However, no known test method can provide complete assurance that specimens of human origin will not transmit infectious disease. When handling or disposing, follow precautions described in CDC and FDA recommendations and OSHA blood-borne pathogen recommendations.

### **Can cryopreserved hepatocytes be thawed and refrozen?**

We do not recommend refreezing hepatocytes. This process typically results in a significant loss of cell viability and yield.

### **When are hepatocytes to be used in drug discovery?**

Hepatocytes can be used at any stage of drug discovery. They are the best *in vitro* model to determine toxicity, metabolic stability, enzyme induction, drug-drug interaction and screening drug candidates.

### **How do hepatocytes compare to Human Liver Microsomes (HLMs) or Corning Supersomes™ enzymes?**

Hepatocytes are whole cells whereas microsomes and Corning Supersomes enzymes are subcellular fractions. Therefore hepatocytes contain a complete phase I and phase II metabolism system while subcellular fractions do not. With hepatocytes, one can observe oxidative metabolites, glucuronide and sulfate conjugates directly. With HLMs, one can observe oxidative metabolism upon fortification with NADPH. To observe conjugation reactions, one needs to further fortify UDPGA for UGTs and other cofactors for other pathways. Generally, UGTs appear to be quantitatively less active in microsomes relative to hepatocytes. Corning Supersomes enzymes behave similarly to liver microsomes except the enzyme complement is more limited but highly defined.

### **How do hepatocytes compare to *in vivo* studies?**

Hepatocytes are generally considered to be the closest thing to *in vivo* metabolism studies, although there is no standard for comparison.

### **Does Corning Life Sciences use hepatocytes for *in vitro* metabolism and/or induction studies?**

Yes. Corning® Gentest™ inducible-qualified cryohepatocytes and fresh plated hepatocytes are ideal for studying induction of metabolic enzymes. Corning Gentest metabolism-qualified cryohepatocytes are ideal for the study of metabolism of drugs or drug candidate compounds.

### **What is 7-HFC (7-hydroxy 4-trifluoromethyl-coumarin) metabolic activity specific for; glucuronidation or sulfation?**

In human hepatocytes, 7-HFC is primarily a substrate to measure UGT glucuronidation activity; there is some sulfation activity occurring but it is minimal compared to glucuronidation in human hepatocytes.

### **Do I need to add cofactors or cytosol to hepatocytes?**

No, hepatocytes contain all the necessary co-factors (e.g. NADPH and UDPGA) for both phase I and phase II drug metabolism.

### **What is the recommended density of (cryo)hepatocytes in a metabolism assay?**

The recommended density of cryohepatocytes is  $0.5 \times 10^6$  -  $1.0 \times 10^6$  cells/mL. Refer to the accompanying protocol for additional information.

### **Which solvents should be used with test compounds?**

Dimethyl Sulfoxide (DMSO) is the preferred solvent and should be used in concentrations less than 0.2%. For induction experiments, the final DMSO concentration in the culture media should be less than 0.1%.

### **What is the density of human hepatocytes on plated flasks and multiwell plates?**

Hepatocytes are seeded at  $2.0 \times 10^5$  cells/cm<sup>2</sup>. We recommend total protein quantitation of individual monolayers for the purpose of calibrating data of induction/enzyme studies.

### **Are Corning Gentest human hepatocytes always available from stock?**

Cryopreserved human hepatocytes are in stock and can be purchased at any time. Fresh human hepatocytes are available upon receipt of fresh tissue. On average, we receive a fresh liver every week, so product is available on a consistent and convenient basis.

### **Do Corning Gentest plated hepatocytes come with gel stabilizers to prevent the media from sloshing during shipment?**

No. Corning Gentest plated hepatocytes come with a special sealing gasket lid to minimize leakage of media during shipment, therefore the use of gel stabilizers is not necessary. Once delivered, the cardboard lid sealer can be cut open and the gasket lid can be replaced with the standard Falcon® microplate lid enclosed with each shipment. Corning Gentest plated hepatocytes in T-flasks do not require any special gaskets for shipment.

### **How are Corning Gentest plated hepatocytes shipped to me? Do you use standard overnight delivery like Federal Express or Airborne?**

Each shipment of Corning Gentest plated hepatocytes are custom couriered to each account to ensure proper temperature control and rapid delivery. Most shipments are delivered using Sterling Couriers and World Couriers to ensure maximum viability upon receipt.

## Will Corning ever ship hepatocytes on Saturdays or Sundays? Do I need to be prepared for unusual deliveries on weekends?

Corning® Gentest™ plated hepatocytes are grown in Corning Hepatocyte Culture Media for maximum viability and longevity. It is generally not necessary to ship plated hepatocytes over weekends. Customers who register with Corning at [www.corning.com/lifesciences/hepatolink](http://www.corning.com/lifesciences/hepatolink) or by emailing [hepatocytes@corning.com](mailto:hepatocytes@corning.com) will be notified of any impending shipments.

## Is it expensive to custom courier plated hepatocytes to me? What sort of delivery charges can I expect?

All Corning Gentest plated hepatocytes are shipped FOB Woburn, Massachusetts. Shipment charges vary with distance. To obtain a reasonable estimate for your location, contact [hepatocytes@corning.com](mailto:hepatocytes@corning.com) and be sure to give your site location. Typical courier charges vary from approximately \$250-300/shipment in the US and approximately \$1,000/shipment outside the US.

## How are enzyme activities in Corning Gentest hepatocytes characterized?

We have three categories of cryopreserved hepatocytes—metabolism-qualified, transporter-qualified and inducible-qualified hepatocytes. The characterization assays are listed below:

### Human CryoHepatocytes, Metabolism-Qualified:

Phenacetin O-deethylase (CYP1A2), bupropion hydroxylase (CYP2B6), amodiaquine N-demethylase (CYP2C8), diclofenac 4'-hydroxylase (CYP2C9), bufuralol 1'-hydroxylase (CYP2D6), testosterone 6 $\beta$ -hydroxylase (CYP3A), AZT-glucuronidation (UGT2B7) and 7-hydroxycoumarin-glucuronidation (non-selective UGT substrate).

### Human CryoHepatocytes, Transporter-Qualified:

All the assays used for metabolism-qualified hepatocytes PLUS estrone-3-sulfate uptake (OATP), tetraethylammonium bromide uptake (OCT1) and taurocholate uptake (NTCP).

### Human CryoHepatocytes, Inducible-Qualified:

All the assays used for metabolism-qualified PLUS induction of testosterone 6 $\beta$ -hydroxylase activity (CYP3A) by 20  $\mu$ M rifampicin and induction of phenacetin O-deethylase activity (CYP1A2) by 20  $\mu$ M  $\beta$ -naphthoflavone.

### Enzyme Activities in Fresh Plated Human Hepatocytes:

Testosterone; (measuring CYP3A4 activity):

7-Methoxy-4-(trifluoromethyl)-coumarin (7-MFC);  
measuring multiple CYP isoform activities

7-Hydroxy-4-(trifluoromethyl)-coumarin (7-HFC);  
measuring multiple UGT glucuronidation isoforms

### Enzyme Activities in Cryopreserved Animal CryoHepatocytes:

#### Rat and Mouse:

Testosterone 6 $\beta$ -hydroxylase, 7-hydroxycoumarin sulfation and glucuronidation.

#### Dog:

The same assays as Rat and Mouse PLUS testosterone 16 $\beta$ -hydroxylase, phenacetin O-deethylase, bufuralol 1'-hydroxylase and chlorzoxazone 6-hydroxylase.

#### Cynomolgus Monkey:

The same assays as Rat and Mouse PLUS testosterone 16 $\beta$ -hydroxylase, testosterone 16 $\beta$ -hydroxylase, phenacetin O-deethylase, bufuralol 1'-hydroxylase and p-nitrophenol hydroxylase.

**Corning acquired the Falcon<sup>®</sup>, Gentest<sup>™</sup>, Hepatolink<sup>®</sup>, and Supersomes<sup>™</sup> brands.**

For additional Corning product, technical, or distributor information, please e-mail us at [CLSTechServ@corning.com](mailto:CLSTechServ@corning.com), visit our website [www.corning.com/lifesciences](http://www.corning.com/lifesciences) or call 800.492.1110. Outside the United States, call 978.442.2200.

For information on the acquisition, visit [www.corning.com/discoverylabware](http://www.corning.com/discoverylabware).

**Corning Incorporated**  
*Life Sciences*

836 North St.  
Building 300, Suite 3401  
Tewksbury, MA 01876  
t 800.492.1110  
t 978.442.2200  
f 978.442.2476

[www.corning.com/lifesciences](http://www.corning.com/lifesciences)

**Worldwide  
Support Offices**

**ASIA/PACIFIC**

**Australia/New Zealand**  
t 0402-794-347

**China**  
t 86 21 2215 2888  
f 86 21 6215 2988

**India**  
t 91 124 4604000  
f 91 124 4604099

**Japan**

t 81 3-3586 1996  
f 81 3-3586 1291

**Korea**

t 82 2-796-9500  
f 82 2-796-9300

**Singapore**

t 65 6733-6511  
f 65 6861-2913

**Taiwan**

t 886 2-2716-0338  
f 886 2-2516-7500

**EUROPE**

**France**

t 0800 916 882  
f 0800 918 636

**Germany**

t 0800 101 1153  
f 0800 101 2427

**The Netherlands**

t 31 20 655 79 28  
f 31 20 659 76 73

**United Kingdom**

t 0800 376 8660  
f 0800 279 1117

**All Other European  
Countries**

t 31 (0) 20 659 60 51  
f 31 (0) 20 659 76 73

**LATIN AMERICA**

**Brasil**

t (55-11) 3089-7419  
f (55-11) 3167-0700

**Mexico**

t (52-81) 8158-8400  
f (52-81) 8313-8589

**CORNING** | **FALCON<sup>®</sup>** **cellgro<sup>®</sup>** **ALXYGEN<sup>®</sup>** **PYREX<sup>®</sup>** **GOSSSELIN<sup>™</sup>**

For Research Use Only. Not for use in diagnostic or therapeutic procedures.

For a listing of trademarks, visit us at [www.corning.com/lifesciences/trademarks](http://www.corning.com/lifesciences/trademarks).

Corning Incorporated, One Riverfront Plaza, Corning, NY 14831-0001