

Corning® NutriStem® hPSC XF Media

References

CORNING

1. Menasché P., et al. Human embryonic stem cell-derived cardiac progenitors for severe heart failure treatment: first clinical case report. *Eur. heart J.* (2015) doi:10.1093/eurheartj/ehv189
2. Jacquet L., et al. Three Huntington's disease specific mutation-carrying human embryonic stem cell lines have stable number of CAG repeats upon in vitro differentiation into cardiomyocytes. *PLOS ONE* (2015) e0126860
3. Rajasingh S., et al. Generation of functional cardiomyocytes from efficiently generated human iPSCs and a novel method of measuring contractility. *PLOS ONE* (2015) e0134093
4. Siqin W., et al. Spider silk for xeno-free long-term self-renewal and differentiation of human pluripotent stem cells. *Biomaterials* (2014) 35:8496-8502
5. Pasquale E., Di et al. Generation of human cardiomyocytes: a differentiation protocol from feeder-free human induced pluripotent stem cells. *J Vis. Exp.* (2013) 76:e50429
6. Földes G., and Mioulane M. High-content imaging and analysis of pluripotent stem cell-derived cardiomyocytes. *Methods Mol. Biol.* (2013) 1052:29-39
7. Burridge P.W., and Zambidis E.T. Highly efficient directed differentiation of human induced pluripotent stem cells into cardiomyocytes. *Methods Mol. Biol.* (2013) 997:149-61
8. Song R.S. et al. Generation, expansion, and differentiation of human induced pluripotent stem cells (hPSC) derived from the umbilical cords of newborns. *Curr. Protoc. Stem Cell Biol.* (2014) 29:1C.16.1-13
9. Warren L., et al. Highly efficient reprogramming to pluripotency and directed differentiation of human cells with synthetic modified mRNA. *Cell Stem Cell* (2010) 7:618-630
10. Reyes A.P., et al. Xeno-Free and defined human embryonic stem cell-derived retinal pigment epithelial cells functionally integrate in a large-eyed preclinical model. *Stem Cell Reports* (2016) 6:9-17
11. Krivega M.V., et al. Cyclin E1 plays a key role in balancing between totipotency and differentiation in human embryonic cells. *Mol. Hum. Reprod.* (2015) 21:942-5
12. Lenzi J., et al. Differentiation of control and ALS mutant human iPSCs into functional skeletal muscle cells, a tool for the study of neuromuscular diseases. *Stem Cell Res.* (2016) 17:140-147
13. Alessandri K., et al. A 3D printed microfluidic device for production of functionalized hydrogel microcapsules for culture and differentiation of human Neuronal Stem Cells (hNSC). *Lab Chip* (2016) 16:1593-1604
14. Lipsitz Y.Y. and Zandstra P.W. Human pluripotent stem cell process parameter optimization in a small scale suspension bioreactor. *BMC Proc.* (2015) 9 (Suppl. 9):O10
15. Wu S., et al. Efficient passage of human pluripotent stem cells on spider silk matrices under xeno-free conditions. *Cell Mol. Life Sci.* (2016) 73:1479-88
16. Gregory S., et al. Autophagic response to cell culture stress in pluripotent stem cells. *Biochem. Biophys. Res. Commun.* (2016) 473:758-763
17. Lenzi J., et al. ALS mutant FUS proteins are recruited into stress granules in induced pluripotent stem cell-derived motoneurons. *Dis. Model Mech.* (2015) 8:755-66
18. Desai N., et al. Human embryonic stem cell cultivation: historical perspective and evolution of xeno-free culture systems. *Reprod. Biol. Endocrinol.* (2015) 13:9
19. Yokobori T., et al. Intestinal epithelial culture under an air-liquid interface: a tool for studying human and mouse esophagi. *Dis. Esophagus* (2015) DOI: 10.1111/dote.12346
20. Cerbini T., et al. Transfection, selection, and colony-picking of human induced pluripotent stem cells TALEN-targeted with a GFP gene into the AAVS1 safe harbor. *J. Vis. Exp.* (2015) 96:e52504
21. Healy L. and Ruban L. Derivation of induced pluripotent stem cells. *Atlas of Human Pluripotent Stem Cells in Culture* (2015) Springer Science + Business Media New York (ISBN 978-1-4899-7507-2) DOI 10.1007/978-1-4899-7507-2_9
22. Thakar N.Y., et al. TRAF2 recruitment via T61 in CD30 drives NFkB activation and enhances hESC survival and proliferation. *Mol. Biol. Cell* (2015) 26:993-1006
23. Bellamy V., et al. Long-term functional benefits of human embryonic stem cell-derived cardiac progenitors embedded into a fibrin scaffold. *J. Heart Lung Transplant* (2015) 34:1198-207
24. Schwab J. and Ebert A.D. Sensory neurons do not induce motor neuron loss in a human stem cell model of spinal muscular atrophy. *PLOS ONE* (2014) 9:e103112
25. Finesilver G., et al. Kidney-specific micro-scaffolds and kidney derived serum free conditioned media support in vitro expansion, differentiation, and organization of human embryonic stem cells. *Tissue Eng. Part C Methods* (2014) 20:1003-15
26. Amit M and Itskovitz-Eldor J. *Atlas of Human Pluripotent Stem Cells: Derivation and Culturing.* Stem Cell Biology and Regenerative Medicine (2012) Springer Science + Business Media, LLC 2012 (ISBN 978-1-61779-548-0) DOI 10.1007/978-1-61779-548-0_1
27. Bergström R., et al. Xeno-free culture of human pluripotent stem cells. *Methods Mol. Biol.* (2011) 767:125-36

28. Sugii S., et al. Human and mouse adipose-derived cells support feeder-independent induction of pluripotent stem cells. *Proc. Natl. Acad. Sci. USA.* (2010) 107:3558-3563
29. Brouwer M., et al. Choices for induction of pluripotency: recent developments in human induced pluripotent stem cell reprogramming strategies. *Stem Cell Rev.* (2016) 12:54-72
30. Nguyen H.X., et al. Induction of early neural precursors and derivation of tripotent neural stem cells from human pluripotent stem cells under xeno-free conditions. *J. Comparative Neurol.* (2014) 522:2767-2783
31. Rodin S., et al. Monolayer culturing and cloning of human pluripotent stem cells on laminin-521-based matrices under xeno-free and chemically defined conditions. *Nat. Protocols* (2014) 9:2354-2368
32. Rodin S., et al. Clonal culturing of human embryonic stem cells on laminin-521/E-cadherin matrix in defined and xeno-free environment. *Nat. Commun.* (2014) 5:3195
33. Jacobs K., et al. Higher-density culture in human embryonic stem cells results in DNA damage and genome instability. *Stem Cell Reports* (2016) 6:330-341
34. Salvio M. Di, et al. Pur-alpha functionally interacts with FUS carrying ALS-associated mutations. *Cell Death Dis.* (2015) 6:e1943
35. Oñate L., de et al. Research on skeletal muscle diseases using pluripotent stem cells. *Muscle cell and tissue.* (2015) InTech publisher (ISBN 978-953-51-2156-5) DOI:10.5772/60902
36. Menasché P., et al. Towards a clinical use of human embryonic stem cell-derived cardiac progenitors: a translational experience. *Eur. Heart J.* (2015) 36:743-50
37. Seki T. and Fukuda K. Methods of induced pluripotent stem cells for clinical application. *World J. Stem Cells* (2015) 7:116-125
38. Abbasalizadeh S. and Baharvand H. Technologies progress and challenges towards cGMP manufacturing of human pluripotent stem cells based therapeutic products for allogeneic and autologous cell therapies. *Biotechnol. Adv.* (2013) 31:1600-23
39. Luo Y., et al. Stable Enhanced green fluorescent protein expression after differentiation and transplantation of reporter human induced pluripotent stem cells generated by AAVS1 transcription activator-like effector nucleases. *Stem Cell Transl. Med.* (2014) 3:821-35
40. Durruthy-Durruthy J. et al. Rapid and efficient conversion of integration-free human induced pluripotent stem cells to GMP-grade culture conditions. *PLOS ONE* 9:e94231
41. Tateno H., et al. A medium hyperglycosylated podocalyxin enables noninvasive and quantitative detection of tumorigenic human pluripotent stem cells. *Sci. Rep.* (2014) 4:4069
42. Awe J.P., et al. Generation and characterization of transgene-free human induced pluripotent stem cells and conversion to putative clinical-grade status. *Stem Cell Res. Ther.* (2013) 4:87
43. Hovatta O. Infectious problems associated with transplantation of cells differentiated from pluripotent stem cells. *Seminars Immunopathol.* (2011) 33:627-630
44. Ye Z., et al. Differential sensitivity to JAK inhibitory drugs by isogenic human erythroblasts and hematopoietic progenitors generated from patient iPSCs. *Stem Cells* (2014) 32:269-278

For more specific information on claims, visit the Certificates page at www.corning.com/lifesciences.

Warranty/Disclaimer: NutriStem is for research use or further manufacturing use only. Unless otherwise specified, all other products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110. Outside the United States, call +1.978.442.2200 or contact your local Corning sales office.

Corning Incorporated
Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476
www.corning.com/lifesciences

Worldwide
Support Offices

ASIA/PACIFIC
Australia/New Zealand
t 61 427286832
China
t 86 21 3338 4338
f 86 21 3338 4300
India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291
Korea
t 82 2-796-9500
f 82 2-796-9300
Singapore
t 65 6572-9740
f 65 6861-2913
Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France
t 0800 916 882
f 0800 918 636
Germany
t 0800 101 1153
f 0800 101 2427
The Netherlands
t 31 20 655 79 28
f 31 20 659 76 73
United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European
Countries
t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA
grupoLA@corning.com
Brasil
t (55-11) 3089-7400
Mexico
t (52-81) 8158-8400

